

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866950

Luminaire Tested: PRLX-2002-L-927-32L-L-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866950
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-82)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-L-927-32L-L-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2461.7 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.27
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866950

CATALOG NUMBER: PRLX-2002-L-927-32L-L-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P866950

CATALOG NUMBER: PRLX-2002-L-927-32L-L-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90
2	104	97	92	87	101	95	91	86	92	88	84	89	86	83	86	83	81	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	69
4	89	79	72	66	87	78	71	66	75	70	65	73	68	64	71	67	63	61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	48
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	43
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	50	45	41	39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36
10	59	47	39	35	58	46	39	34	45	39	34	44	38	34	43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6180
5°	6161
10°	6093
15°	5995
20°	5886
25°	5756
30°	5595
35°	5396
40°	5138
45°	4821
50°	4443
55°	3532
60°	1663
65°	600
70°	231
75°	255
80°	293
85°	351

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4821 cd/sqm

TEST NUMBER: P866950

CATALOG NUMBER: PRLX-2002-L-927-32L-L-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.9	4.8
10°-20°	330.8	13.4
20°-30°	486.5	19.8
30°-40°	559.0	22.7
40°-50°	532.4	21.6
50°-60°	350.1	14.2
60°-70°	64.6	2.6
70°-80°	14.1	0.6
80°-90°	6.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	935.2	38.0
0°-40°	1494.1	60.7
0°-60°	2376.6	96.5
0°-90°	2461.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2461.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1253	
5°	1244	118
15°	1174	331
25°	1057	487
35°	896	559
45°	691	532
55°	411	350
65°	51	65
75°	13	14
85°	6	6
90°	0	

TEST NUMBER: P866950

CATALOG NUMBER: PRLX-2002-L-927-32L-L-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	1252.6
2.5°	1251.3
5°	1244.0
7.5°	1232.4
10°	1216.1
12.5°	1196.2
15°	1173.7
17.5°	1148.4
20°	1121.0
22.5°	1090.5
25°	1057.4
27.5°	1021.3
30°	982.0
32.5°	939.9
35°	895.9
37.5°	847.9
40°	797.7
42.5°	746.3
45°	691.0
47.5°	636.2
50°	578.9
52.5°	511.7
55°	410.6
57.5°	281.4
60°	168.5
62.5°	94.8
65°	51.4
67.5°	25.8
70°	16.0
72.5°	14.7
75°	13.4
77.5°	12.1
80°	10.3
82.5°	8.5
85°	6.2
87.5°	3.4
90°	0.0

TEST NUMBER: P866950
 CATALOG NUMBER: PRLX-2002-L-927-32L-L-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.32	15.72	14.69	16.04	16.35	14.32	15.72	14.69	16.04	16.35
	3H	14.24	15.47	14.62	15.80	16.16	14.24	15.47	14.62	15.80	16.16
	4H	14.19	15.34	14.59	15.69	16.07	14.19	15.34	14.59	15.69	16.07
	6H	14.14	15.19	14.56	15.56	15.96	14.14	15.19	14.56	15.56	15.96
	8H	14.12	15.11	14.54	15.50	15.91	14.12	15.11	14.54	15.50	15.91
	12H	14.09	15.04	14.52	15.42	15.85	14.09	15.04	14.52	15.42	15.85
4H	2H	14.19	15.34	14.60	15.69	16.07	14.19	15.34	14.60	15.69	16.07
	3H	14.13	15.05	14.54	15.45	15.86	14.13	15.05	14.54	15.45	15.86
	4H	14.07	14.90	14.51	15.31	15.76	14.07	14.90	14.51	15.31	15.76
	6H	14.04	14.75	14.50	15.20	15.66	14.04	14.75	14.50	15.20	15.66
	8H	14.01	14.68	14.48	15.12	15.59	14.01	14.68	14.48	15.12	15.59
	12H	14.00	14.58	14.48	15.07	15.54	14.00	14.58	14.48	15.07	15.54
8H	4H	13.96	14.62	14.43	15.07	15.54	13.96	14.62	14.43	15.07	15.54
	6H	13.92	14.47	14.42	14.96	15.44	13.92	14.47	14.42	14.96	15.44
	8H	13.90	14.39	14.42	14.91	15.40	13.90	14.39	14.42	14.91	15.40
	12H	13.90	14.34	14.41	14.83	15.40	13.90	14.34	14.41	14.83	15.40
12H	4H	13.92	14.51	14.41	14.99	15.46	13.92	14.51	14.41	14.99	15.46
	6H	13.87	14.36	14.39	14.88	15.37	13.87	14.36	14.39	14.88	15.37
	8H	13.87	14.31	14.38	14.81	15.38	13.87	14.31	14.38	14.81	15.38