

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867027

Luminaire Tested: PRLX-2002-L-930-48L-G-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867027
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-68)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-L-930-48L-G-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS, TRUNCATED DOME WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 3
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3141.4 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 1.35 / 1.35 / 1.49
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 37.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867027

CATALOG NUMBER: PRLX-2002-L-930-48L-G-X-X-WHHR-X

Luminous Intensity Polar Plot



TEST NUMBER: P867027

CATALOG NUMBER: PRLX-2002-L-930-48L-G-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	99	95	106	101	97	93	97	94	90		93	90	88		89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74		81	76	72		78	74	71	68
3	89	78	70	63	87	77	69	63	74	67	62		71	65	60		68	64	59	57
4	81	69	60	53	79	68	59	53	65	58	52		63	56	51		61	55	51	48
5	75	62	52	45	73	60	52	45	58	51	45		56	49	44		54	48	44	42
6	69	55	46	39	67	54	46	39	52	45	39		51	44	39		49	43	38	36
7	64	50	41	35	62	49	41	34	47	40	34		46	39	34		45	38	34	32
8	59	45	37	31	58	45	36	31	43	36	30		42	35	30		41	35	30	28
9	55	42	33	27	54	41	33	27	40	32	27		39	32	27		38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25		36	29	24		35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4816
5°	4835
10°	4834
15°	4840
20°	4866
25°	4919
30°	5003
35°	5127
40°	5272
45°	5364
50°	5333
55°	5191
60°	4975
65°	4721
70°	4439
75°	4140
80°	3841
85°	3419

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5364 cd/sqm

TEST NUMBER: P867027

CATALOG NUMBER: PRLX-2002-L-930-48L-G-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.8	3.0
10°-20°	267.9	8.5
20°-30°	417.4	13.3
30°-40°	533.4	17.0
40°-50°	590.6	18.8
50°-60°	538.2	17.1
60°-70°	401.0	12.8
70°-80°	231.5	7.4
80°-90°	68.6	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	778.1	24.8
0°-40°	1311.5	41.7
0°-60°	2440.3	77.7
0°-90°	3141.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3141.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	976	
5°	976	93
15°	948	268
25°	904	417
35°	851	533
45°	769	591
55°	604	538
65°	404	401
75°	217	231
85°	60	69
90°	0	

TEST NUMBER: P867027

CATALOG NUMBER: PRLX-2002-L-930-48L-G-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	976.2
2.5°	976.7
5°	976.2
7.5°	972.9
10°	964.8
12.5°	956.8
15°	947.5
17.5°	937.4
20°	926.8
22.5°	915.4
25°	903.6
27.5°	891.3
30°	878.2
32.5°	865.1
35°	851.2
37.5°	836.4
40°	818.6
42.5°	797.5
45°	768.7
47.5°	734.1
50°	694.8
52.5°	650.4
55°	603.5
57.5°	553.6
60°	504.2
62.5°	454.3
65°	404.4
67.5°	356.3
70°	307.7
72.5°	262.4
75°	217.2
77.5°	176.7
80°	135.2
82.5°	96.4
85°	60.4
87.5°	27.9
90°	0.0



TEST NUMBER: P867027
 CATALOG NUMBER: PRLX-2002-L-930-48L-G-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.99	19.67	18.35	19.98	20.30	17.99	19.67	18.35	19.98	20.30
	3H	19.74	21.26	20.12	21.58	21.94	19.74	21.26	20.12	21.58	21.94
	4H	20.40	21.84	20.80	22.18	22.56	20.40	21.84	20.80	22.18	22.56
	6H	20.92	22.25	21.33	22.62	23.01	20.92	22.25	21.33	22.62	23.01
	8H	21.10	22.37	21.52	22.76	23.15	21.10	22.37	21.52	22.76	23.15
	12H	21.22	22.44	21.65	22.82	23.25	21.22	22.44	21.65	22.82	23.25
4H	2H	18.61	20.04	19.01	20.39	20.76	18.61	20.04	19.01	20.39	20.76
	3H	20.58	21.79	20.99	22.18	22.58	20.58	21.79	20.99	22.18	22.58
	4H	21.38	22.47	21.81	22.88	23.32	21.38	22.47	21.81	22.88	23.32
	6H	22.04	22.99	22.49	23.43	23.89	22.04	22.99	22.49	23.43	23.89
	8H	22.26	23.16	22.72	23.60	24.06	22.26	23.16	22.72	23.60	24.06
	12H	22.44	23.24	22.92	23.72	24.18	22.44	23.24	22.92	23.72	24.18
8H	4H	21.71	22.60	22.16	23.04	23.51	21.71	22.60	22.16	23.04	23.51
	6H	22.49	23.23	22.98	23.72	24.20	22.49	23.23	22.98	23.72	24.20
	8H	22.79	23.46	23.30	23.97	24.45	22.79	23.46	23.30	23.97	24.45
	12H	23.05	23.64	23.55	24.13	24.69	23.05	23.64	23.55	24.13	24.69
12H	4H	21.75	22.55	22.22	23.03	23.49	21.75	22.55	22.22	23.03	23.49
	6H	22.55	23.23	23.06	23.73	24.21	22.55	23.23	23.06	23.73	24.21
	8H	22.92	23.51	23.43	24.00	24.56	22.92	23.51	23.43	24.00	24.56