

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867060

Luminaire Tested: PRLX-2002-L-935-133L-L-X-X-BLAK-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P867060  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-83)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Pentalux  
Catalog Number: PRLX-2002-L-935-133L-L-X-X-BLAK-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH BLACK INTERIOR SHADE.  
LIGHT LEVEL 8  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10506.2 lumens  
Efficiency: N/A  
Efficacy: 94.0 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.27  
Luminous Opening: Circular (Dia: 1.67' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 111.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P867060

CATALOG NUMBER: PRLX-2002-L-935-133L-L-X-X-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P867060

CATALOG NUMBER: PRLX-2002-L-935-133L-L-X-X-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	105	103	109	106	104	101	102	100	98		98	97	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	82	77	95	87	81	77	84	79	75		82	78	74		79	76	73	71
4	90	80	73	68	88	79	72	67	77	71	66		75	70	66		73	68	65	63
5	84	73	65	60	82	72	65	60	70	64	59		68	63	58		66	62	58	56
6	78	66	59	53	76	66	58	53	64	57	53		62	57	52		61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	47		57	51	47		56	51	47	45
8	68	56	48	43	66	55	48	43	54	47	43		53	47	43		52	46	42	41
9	64	52	44	39	62	51	44	39	50	43	39		49	43	39		48	43	39	37
10	60	48	41	36	59	47	40	36	46	40	36		45	40	35		45	39	35	34

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	27407
5°	27328
10°	27036
15°	26633
20°	26169
25°	25635
30°	24940
35°	24042
40°	22846
45°	21392
50°	19498
55°	13037
60°	4633
65°	1071
70°	172
75°	181
80°	236
85°	272

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 21392 cd/sqm

TEST NUMBER: P867060

CATALOG NUMBER: PRLX-2002-L-935-133L-L-X-X-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	522.8	5.0
10°-20°	1469.5	14.0
20°-30°	2166.9	20.6
30°-40°	2490.1	23.7
40°-50°	2357.5	22.4
50°-60°	1342.2	12.8
60°-70°	142.3	1.4
70°-80°	10.2	0.1
80°-90°	4.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4159.2	39.6
0°-40°	6649.4	63.3
0°-60°	10349.0	98.5
0°-90°	10506.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10506.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5555	
5°	5518	523
15°	5214	1469
25°	4709	2167
35°	3992	2490
45°	3066	2357
55°	1516	1342
65°	92	142
75°	10	10
85°	5	5
90°	0	

TEST NUMBER: P867060

CATALOG NUMBER: PRLX-2002-L-935-133L-L-X-X-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5554.9
2.5°	5548.9
5°	5517.9
7.5°	5466.7
10°	5396.4
12.5°	5310.6
15°	5214.1
17.5°	5104.5
20°	4984.1
22.5°	4853.1
25°	4708.9
27.5°	4554.0
30°	4377.7
32.5°	4191.8
35°	3991.6
37.5°	3774.7
40°	3547.2
42.5°	3317.2
45°	3065.8
47.5°	2804.8
50°	2540.3
52.5°	2144.7
55°	1515.6
57.5°	904.4
60°	469.5
62.5°	234.7
65°	91.7
67.5°	17.9
70°	11.9
72.5°	10.7
75°	9.5
77.5°	8.3
80°	8.3
82.5°	6.0
85°	4.8
87.5°	2.4
90°	0.0



TEST NUMBER: P867060  
 CATALOG NUMBER: PRLX-2002-L-935-133L-L-X-X-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.40	18.76	17.76	19.07	19.39	17.40	18.76	17.76	19.07	19.39
	3H	17.27	18.47	17.65	18.80	19.16	17.27	18.47	17.65	18.80	19.16
	4H	17.20	18.31	17.61	18.66	19.05	17.20	18.31	17.61	18.66	19.05
	6H	17.13	18.14	17.54	18.51	18.91	17.13	18.14	17.54	18.51	18.91
	8H	17.09	18.05	17.52	18.44	18.84	17.09	18.05	17.52	18.44	18.84
	12H	17.05	17.96	17.48	18.35	18.78	17.05	17.96	17.48	18.35	18.78
4H	2H	17.23	18.33	17.63	18.68	19.07	17.23	18.33	17.63	18.68	19.07
	3H	17.10	17.99	17.52	18.39	18.80	17.10	17.99	17.52	18.39	18.80
	4H	17.02	17.80	17.45	18.22	18.67	17.02	17.80	17.45	18.22	18.67
	6H	16.94	17.62	17.40	18.06	18.53	16.94	17.62	17.40	18.06	18.53
	8H	16.88	17.51	17.35	17.96	18.43	16.88	17.51	17.35	17.96	18.43
	12H	16.83	17.39	17.32	17.88	18.35	16.83	17.39	17.32	17.88	18.35
8H	4H	16.88	17.51	17.35	17.96	18.43	16.88	17.51	17.35	17.96	18.43
	6H	16.77	17.30	17.28	17.79	18.27	16.77	17.30	17.28	17.79	18.27
	8H	16.71	17.18	17.23	17.70	18.19	16.71	17.18	17.23	17.70	18.19
	12H	16.66	17.08	17.17	17.58	18.15	16.66	17.08	17.17	17.58	18.15
12H	4H	16.83	17.39	17.32	17.87	18.35	16.83	17.39	17.32	17.87	18.35
	6H	16.70	17.18	17.23	17.69	18.19	16.70	17.18	17.23	17.69	18.19
	8H	16.65	17.08	17.17	17.58	18.15	16.65	17.08	17.17	17.58	18.15