

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867071

Luminaire Tested: PRLX-2002-L-935-15L-L-X-X-WHHR-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P867071  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-80)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2002-L-935-15L-L-X-X-WHHR-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH WHITE INTERIOR SHADE.  
LIGHT LEVEL 1  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1523.0 lumens  
Efficiency: N/A  
Efficacy: 92.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.3  
Luminous Opening: Circular (Dia: 1.67' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 16.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P867071

CATALOG NUMBER: PRLX-2002-L-935-15L-L-X-X-WHHR-X

### Luminous Intensity Polar Plot



TEST NUMBER: P867071

CATALOG NUMBER: PRLX-2002-L-935-15L-L-X-X-WHHR-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	101	99	101	98	96	97	95	93	93	91	90	88
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67
4	88	77	69	64	85	76	69	63	73	67	62	71	66	62	69	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52
6	75	63	55	49	74	62	55	49	61	54	49	59	53	48	58	52	48	46
7	70	58	50	44	69	57	49	44	56	49	44	54	48	43	53	47	43	41
8	66	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	36	32	31

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3557
5°	3544
10°	3507
15°	3466
20°	3419
25°	3365
30°	3294
35°	3204
40°	3084
45°	2932
50°	2743
55°	2009
60°	1050
65°	700
70°	626
75°	665
80°	727
85°	798

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2932 cd/sqm

TEST NUMBER: P867071

CATALOG NUMBER: PRLX-2002-L-935-15L-L-X-X-WHHR-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	67.8	4.5
10°-20°	191.4	12.6
20°-30°	284.6	18.7
30°-40°	332.2	21.8
40°-50°	323.6	21.2
50°-60°	207.3	13.6
60°-70°	64.6	4.2
70°-80°	36.8	2.4
80°-90°	14.9	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	543.7	35.7
0°-40°	875.9	57.5
0°-60°	1406.8	92.4
0°-90°	1523.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1523.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	721	
5°	716	68
15°	678	191
25°	618	285
35°	532	332
45°	420	324
55°	234	207
65°	60	65
75°	35	37
85°	14	15
90°	0	

TEST NUMBER: P867071

CATALOG NUMBER: PRLX-2002-L-935-15L-L-X-X-WHHR-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	721.0
2.5°	719.9
5°	715.6
7.5°	708.9
10°	700.1
12.5°	690.3
15°	678.5
17.5°	665.8
20°	651.1
22.5°	635.3
25°	618.2
27.5°	599.4
30°	578.2
32.5°	555.7
35°	532.0
37.5°	506.4
40°	478.9
42.5°	450.5
45°	420.2
47.5°	389.2
50°	357.4
52.5°	311.1
55°	233.6
57.5°	158.2
60°	106.4
62.5°	79.4
65°	60.0
67.5°	47.6
70°	43.4
72.5°	39.5
75°	34.9
77.5°	30.4
80°	25.6
82.5°	20.2
85°	14.1
87.5°	7.5
90°	0.0



TEST NUMBER: P867071

CATALOG NUMBER: PRLX-2002-L-935-15L-L-X-X-WHHR-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.96	13.42	12.33	13.73	14.04	11.96	13.42	12.33	13.73	14.04
	3H	12.38	13.67	12.76	14.00	14.36	12.38	13.67	12.76	14.00	14.36
	4H	12.66	13.87	13.06	14.22	14.60	12.66	13.87	13.06	14.22	14.60
	6H	12.98	14.09	13.39	14.46	14.85	12.98	14.09	13.39	14.46	14.85
	8H	13.13	14.18	13.55	14.57	14.97	13.13	14.18	13.55	14.57	14.97
	12H	13.25	14.26	13.68	14.64	15.07	13.25	14.26	13.68	14.64	15.07
4H	2H	12.02	13.22	12.42	13.57	13.95	12.02	13.22	12.42	13.57	13.95
	3H	12.64	13.62	13.05	14.02	14.42	12.64	13.62	13.05	14.02	14.42
	4H	13.06	13.94	13.49	14.36	14.80	13.06	13.94	13.49	14.36	14.80
	6H	13.55	14.31	14.01	14.76	15.22	13.55	14.31	14.01	14.76	15.22
	8H	13.77	14.48	14.24	14.93	15.40	13.77	14.48	14.24	14.93	15.40
	12H	13.97	14.61	14.45	15.09	15.56	13.97	14.61	14.45	15.09	15.56
8H	4H	13.20	13.92	13.67	14.36	14.83	13.20	13.92	13.67	14.36	14.83
	6H	13.83	14.43	14.33	14.92	15.40	13.83	14.43	14.33	14.92	15.40
	8H	14.15	14.69	14.67	15.20	15.69	14.15	14.69	14.67	15.20	15.69
	12H	14.46	14.94	14.97	15.43	16.00	14.46	14.94	14.97	15.43	16.00
12H	4H	13.22	13.85	13.70	14.33	14.81	13.22	13.85	13.70	14.33	14.81
	6H	13.88	14.42	14.40	14.93	15.42	13.88	14.42	14.40	14.93	15.42
	8H	14.26	14.74	14.77	15.24	15.80	14.26	14.74	14.77	15.24	15.80