

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250618

Luminaire Tested: **LD8B90D010 ER8B909730 8LBM0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250618  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13928)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B90D010 ER8B909730 8LBM0B  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4427.0 lumens  
Efficiency: N/A  
Efficacy: 51.4 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.87  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 86.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250618

CATALOG NUMBER: LD8B90D010 ER8B909730 8LBM0B

### Luminous Intensity Polar Plot





TEST NUMBER: P250618

CATALOG NUMBER: LD8B90D010 ER8B909730 8LBM0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	99	96	106	102	98	95	98	95	93		95	93	91		93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86		90	87	84		88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79		85	81	78		83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74		80	76	73		79	75	72	71
6	88	79	74	69	87	79	73	69	77	72	69		76	71	68		74	71	68	66
7	84	75	69	65	83	74	68	64	73	68	64		72	67	64		70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60		68	63	60		67	63	60	58
9	76	66	61	57	75	66	60	57	65	60	56		64	60	56		63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53		61	56	53		60	56	53	51

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P250618

CATALOG NUMBER: LD8B90D010 ER8B909730 8LBM0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	504.5	11.4
10°-20°	1171.7	26.5
20°-30°	1486.5	33.6
30°-40°	1018.4	23.0
40°-50°	232.1	5.2
50°-60°	11.6	0.3
60°-70°	0.5	0.0
70°-80°	0.8	0.0
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3162.7	71.4
0°-40°	4181.1	94.4
0°-60°	4424.7	100.0
0°-90°	4427.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4427.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5744	
5°	5547	505
15°	4159	1172
25°	3292	1486
35°	1645	1018
45°	250	232
55°	4	12
65°	2	1
75°	0	1
85°	0	1
90°	0	



TEST NUMBER: P250618

CATALOG NUMBER: LD8B90D010 ER8B909730 8LBM0B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	5744.2
1°	5774.1
2°	5763.4
3°	5720.6
4°	5647.9
5°	5547.4
6°	5425.4
7°	5284.2
8°	5128.0
9°	4961.1
10°	4802.8
11°	4657.4
12°	4501.2
13°	4387.8
14°	4268.0
15°	4158.9
16°	4060.5
17°	3964.2
18°	3874.4
19°	3786.6
20°	3707.5
21°	3626.2
22°	3542.8
23°	3470.0
24°	3388.8
25°	3292.5
26°	3185.5
27°	3061.4
28°	2928.8
29°	2781.2
30°	2618.6
31°	2434.6
32°	2244.2
33°	2045.2
34°	1842.0
35°	1645.1
37.5°	1161.7
40°	748.8
42.5°	440.7
45°	250.3
47.5°	134.8
50°	68.5
52.5°	12.8
55°	4.3
57.5°	2.1



TEST NUMBER: P250618

CATALOG NUMBER: LD8B90D010 ER8B909730 8LBM0B

**CANDELA DISTRIBUTION (continued):**

	0°
60°	0.0
62.5°	0.0
65°	2.1
67.5°	0.0
70°	0.0
72.5°	2.1
75°	0.0
77.5°	0.0
80°	2.1
82.5°	0.0
85°	0.0
87.5°	2.1
90°	0.0

(END OF REPORT)