

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867076

Luminaire Tested: PRLX-2002-L-935-32L-L-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867076
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-83)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Pentalux
Catalog Number: PRLX-2002-L-935-32L-L-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2519.1 lumens
Efficiency: N/A
Efficacy: 96.5 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.27
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867076

CATALOG NUMBER: PRLX-2002-L-935-32L-L-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P867076

CATALOG NUMBER: PRLX-2002-L-935-32L-L-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	105	103	109	106	104	101	102	100	98		98	97	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	82	77	95	87	81	77	84	79	75		82	78	74		79	76	73	71
4	90	80	73	68	88	79	72	67	77	71	66		75	70	66		73	68	65	63
5	84	73	65	60	82	72	65	60	70	64	59		68	63	58		66	62	58	56
6	78	66	59	53	76	66	58	53	64	57	53		62	57	52		61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	47		57	51	47		56	51	47	45
8	68	56	48	43	66	55	48	43	54	47	43		53	47	43		52	46	42	41
9	64	52	44	39	62	51	44	39	50	43	39		49	43	39		48	43	39	37
10	60	48	41	36	59	47	40	36	46	40	36		45	40	35		45	39	35	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6571
5°	6552
10°	6482
15°	6386
20°	6274
25°	6147
30°	5980
35°	5765
40°	5478
45°	5129
50°	4675
55°	3126
60°	1111
65°	257
70°	42
75°	44
80°	57
85°	62

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5129 cd/sqm

TEST NUMBER: P867076

CATALOG NUMBER: PRLX-2002-L-935-32L-L-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.4	5.0
10°-20°	352.3	14.0
20°-30°	519.6	20.6
30°-40°	597.1	23.7
40°-50°	565.3	22.4
50°-60°	321.8	12.8
60°-70°	34.1	1.4
70°-80°	2.5	0.1
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	997.3	39.6
0°-40°	1594.3	63.3
0°-60°	2481.4	98.5
0°-90°	2519.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2519.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1332	
5°	1323	125
15°	1250	352
25°	1129	520
35°	957	597
45°	735	565
55°	363	322
65°	22	34
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P867076

CATALOG NUMBER: PRLX-2002-L-935-32L-L-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1331.9
2.5°	1330.5
5°	1323.0
7.5°	1310.8
10°	1293.9
12.5°	1273.3
15°	1250.2
17.5°	1223.9
20°	1195.0
22.5°	1163.6
25°	1129.1
27.5°	1091.9
30°	1049.6
32.5°	1005.1
35°	957.1
37.5°	905.1
40°	850.5
42.5°	795.4
45°	735.1
47.5°	672.5
50°	609.1
52.5°	514.2
55°	363.4
57.5°	216.8
60°	112.6
62.5°	56.3
65°	22.0
67.5°	4.3
70°	2.9
72.5°	2.6
75°	2.3
77.5°	2.0
80°	2.0
82.5°	1.4
85°	1.1
87.5°	0.6
90°	0.0



TEST NUMBER: P867076
 CATALOG NUMBER: PRLX-2002-L-935-32L-L-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.43	13.80	12.80	14.11	14.43	12.43	13.80	12.80	14.11	14.43
	3H	12.31	13.51	12.69	13.84	14.20	12.31	13.51	12.69	13.84	14.20
	4H	12.24	13.35	12.64	13.70	14.08	12.24	13.35	12.64	13.70	14.08
	6H	12.17	13.18	12.58	13.55	13.94	12.17	13.18	12.58	13.55	13.94
	8H	12.12	13.08	12.55	13.48	13.88	12.12	13.08	12.55	13.48	13.88
	12H	12.08	13.00	12.52	13.38	13.81	12.08	13.00	12.52	13.38	13.81
4H	2H	12.26	13.37	12.66	13.72	14.10	12.26	13.37	12.66	13.72	14.10
	3H	12.14	13.03	12.55	13.43	13.83	12.14	13.03	12.55	13.43	13.83
	4H	12.05	12.84	12.49	13.26	13.70	12.05	12.84	12.49	13.26	13.70
	6H	11.98	12.65	12.44	13.10	13.57	11.98	12.65	12.44	13.10	13.57
	8H	11.92	12.55	12.39	13.00	13.47	11.92	12.55	12.39	13.00	13.47
	12H	11.87	12.43	12.36	12.91	13.39	11.87	12.43	12.36	12.91	13.39
8H	4H	11.92	12.55	12.38	13.00	13.47	11.92	12.55	12.38	13.00	13.47
	6H	11.81	12.33	12.31	12.83	13.31	11.81	12.33	12.31	12.83	13.31
	8H	11.74	12.22	12.26	12.73	13.22	11.74	12.22	12.26	12.73	13.22
	12H	11.69	12.12	12.21	12.61	13.18	11.69	12.12	12.21	12.61	13.18
12H	4H	11.87	12.43	12.35	12.91	13.38	11.87	12.43	12.35	12.91	13.38
	6H	11.74	12.22	12.26	12.73	13.22	11.74	12.22	12.26	12.73	13.22
	8H	11.69	12.12	12.21	12.61	13.18	11.69	12.12	12.21	12.61	13.18