

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866217

Luminaire Tested: PRLX-2002-M-930-07L-L-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866217
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-51)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-M-930-07L-L-U-S-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 576.1 lumens
Efficiency: N/A
Efficacy: 70.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 8.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866217

CATALOG NUMBER: PRLX-2002-M-930-07L-L-U-S-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P866217

CATALOG NUMBER: PRLX-2002-M-930-07L-L-U-S-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	105	102	109	106	103	100	101	99	97		98	96	94		94	93	91	89
2	103	97	91	87	101	95	90	86	92	88	84		89	85	82		86	83	80	78
3	96	87	80	75	93	86	79	74	83	77	73		80	76	72		78	74	71	69
4	89	78	71	65	86	77	70	65	75	69	64		73	67	63		71	66	62	60
5	82	71	63	57	80	70	62	57	68	61	56		66	60	56		64	59	55	53
6	76	64	56	51	74	63	56	51	62	55	50		60	54	50		59	53	49	48
7	71	59	51	45	69	58	51	45	57	50	45		55	49	45		54	48	44	43
8	66	54	46	41	65	53	46	41	52	45	40		51	45	40		50	44	40	38
9	62	50	42	37	61	49	42	37	48	41	37		47	41	37		46	40	36	35
10	58	46	39	34	57	45	38	34	44	38	34		44	38	33		43	37	33	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2283
5°	2274
10°	2242
15°	2199
20°	2148
25°	2092
30°	2032
35°	1964
40°	1891
45°	1810
50°	1718
55°	1480
60°	816
65°	230
70°	91
75°	98
80°	110
85°	137

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1810 cd/sqm

TEST NUMBER: P866217

CATALOG NUMBER: PRLX-2002-M-930-07L-L-U-S-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	26.9	4.7
10°-20°	75.2	13.0
20°-30°	109.7	19.0
30°-40°	126.4	21.9
40°-50°	124.1	21.5
50°-60°	91.0	15.8
60°-70°	17.8	3.1
70°-80°	3.4	0.6
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	211.8	36.8
0°-40°	338.2	58.7
0°-60°	553.4	96.1
0°-90°	576.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	576.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	287	
5°	285	27
15°	267	75
25°	238	110
35°	202	126
45°	161	124
55°	107	91
65°	12	18
75°	3	3
85°	2	2
90°	0	

TEST NUMBER: P866217

CATALOG NUMBER: PRLX-2002-M-930-07L-L-U-S-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	286.9
2.5°	286.5
5°	284.7
7.5°	281.5
10°	277.5
12.5°	272.8
15°	267.0
17.5°	260.4
20°	253.7
22.5°	246.2
25°	238.3
27.5°	230.0
30°	221.2
32.5°	211.8
35°	202.2
37.5°	192.3
40°	182.1
42.5°	171.8
45°	160.9
47.5°	150.2
50°	138.8
52.5°	125.8
55°	106.7
57.5°	81.7
60°	51.3
62.5°	27.6
65°	12.2
67.5°	5.6
70°	3.9
72.5°	3.6
75°	3.2
77.5°	2.8
80°	2.4
82.5°	2.1
85°	1.5
87.5°	0.8
90°	0.0



TEST NUMBER: P866217
 CATALOG NUMBER: PRLX-2002-M-930-07L-L-U-S-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.41	13.84	12.78	14.16	14.47	12.41	13.84	12.78	14.16	14.47
	3H	12.32	13.58	12.70	13.91	14.27	12.32	13.58	12.70	13.91	14.27
	4H	12.27	13.44	12.67	13.79	14.17	12.27	13.44	12.67	13.79	14.17
	6H	12.21	13.28	12.63	13.65	14.05	12.21	13.28	12.63	13.65	14.05
	8H	12.18	13.20	12.61	13.59	13.99	12.18	13.20	12.61	13.59	13.99
	12H	12.15	13.13	12.59	13.51	13.94	12.15	13.13	12.59	13.51	13.94
4H	2H	12.28	13.45	12.68	13.80	14.18	12.28	13.45	12.68	13.80	14.18
	3H	12.19	13.14	12.60	13.54	13.94	12.19	13.14	12.60	13.54	13.94
	4H	12.13	12.97	12.57	13.39	13.83	12.13	12.97	12.57	13.39	13.83
	6H	12.09	12.81	12.55	13.26	13.72	12.09	12.81	12.55	13.26	13.72
	8H	12.05	12.73	12.52	13.18	13.65	12.05	12.73	12.52	13.18	13.65
	12H	12.03	12.63	12.51	13.11	13.58	12.03	12.63	12.51	13.11	13.58
8H	4H	12.02	12.69	12.48	13.14	13.61	12.02	12.69	12.48	13.14	13.61
	6H	11.96	12.52	12.46	13.01	13.49	11.96	12.52	12.46	13.01	13.49
	8H	11.92	12.43	12.44	12.94	13.43	11.92	12.43	12.44	12.94	13.43
	12H	11.91	12.36	12.42	12.86	13.43	11.91	12.36	12.42	12.86	13.43
12H	4H	11.98	12.58	12.46	13.06	13.53	11.98	12.58	12.46	13.06	13.53
	6H	11.90	12.41	12.42	12.92	13.41	11.90	12.41	12.42	12.92	13.41
	8H	11.89	12.34	12.40	12.84	13.41	11.89	12.34	12.40	12.84	13.41