

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246553

Luminaire Tested: **LD8B15D010 ER8B15840 8LBW0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246553
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-48)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15840 8LBW0MW
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1556.0 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246553

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBW0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246553

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBW0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66	74	69	65	72	68	64	62
5	84	73	66	60	82	72	65	60	70	64	59	68	63	59	67	62	58	56
6	79	67	60	54	77	66	59	54	65	58	54	63	58	53	62	57	53	51
7	74	62	55	49	72	61	54	49	60	54	49	59	53	49	57	52	48	47
8	69	58	50	45	68	57	50	45	56	50	45	55	49	45	54	48	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	31792
5°	31254
10°	30272
15°	29571
20°	29150
25°	28580
30°	26833
35°	21905
40°	13570
45°	9188
50°	8098
55°	7640
60°	7580
65°	7348
70°	6582
75°	5707
80°	4812
85°	3856



TEST NUMBER: P246553

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBW0MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.0	6.1
10°-20°	261.6	16.8
20°-30°	383.7	24.7
30°-40°	350.7	22.5
40°-50°	173.6	11.2
50°-60°	128.4	8.3
60°-70°	98.7	6.3
70°-80°	51.4	3.3
80°-90°	12.8	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	740.3	47.6
0°-40°	1091.0	70.1
0°-60°	1393.0	89.5
0°-90°	1556.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1556.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1031	
5°	1010	95
15°	926	262
25°	840	384
35°	582	351
45°	211	174
55°	142	128
65°	101	99
75°	48	51
85°	11	13
90°	0	



TEST NUMBER: P246553

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBW0MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1031.0
2.5°	1025.5
5°	1009.7
7.5°	988.5
10°	966.8
12.5°	945.6
15°	926.3
17.5°	908.1
20°	888.3
22.5°	866.1
25°	840.0
27.5°	803.9
30°	753.6
32.5°	683.0
35°	581.9
37.5°	456.5
40°	337.1
42.5°	255.1
45°	210.7
47.5°	186.5
50°	168.8
52.5°	154.5
55°	142.1
57.5°	131.8
60°	122.9
62.5°	113.5
65°	100.7
67.5°	86.9
70°	73.0
72.5°	60.2
75°	47.9
77.5°	37.0
80°	27.1
82.5°	18.8
85°	10.9
87.5°	3.9
90°	0.0

(END OF REPORT)