

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866240

Luminaire Tested: PRLX-2002-M-930-35L-L-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866240
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-53)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-M-930-35L-L-U-S-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 4
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2685.7 lumens
Efficiency: N/A
Efficacy: 89.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 30
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866240

CATALOG NUMBER: PRLX-2002-M-930-35L-L-U-S-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P866240

CATALOG NUMBER: PRLX-2002-M-930-35L-L-U-S-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		95	93	92	90
2	104	97	92	88	101	96	91	87	92	88	85		89	86	83		86	83	81	79
3	96	88	81	76	94	86	80	75	83	78	74		81	76	73		78	75	71	69
4	89	79	72	66	87	78	71	66	75	69	65		73	68	64		71	67	63	61
5	83	71	64	58	81	70	63	58	68	62	57		67	61	57		65	60	56	54
6	77	65	57	51	75	64	57	51	62	56	51		61	55	50		59	54	50	48
7	71	59	51	46	70	58	51	46	57	50	45		56	50	45		54	49	45	43
8	67	54	47	41	65	54	46	41	52	46	41		51	45	41		50	45	41	39
9	62	50	43	37	61	49	42	37	48	42	37		47	41	37		46	41	37	35
10	59	46	39	34	57	46	39	34	45	38	34		44	38	34		43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	10739
5°	10697
10°	10566
15°	10381
20°	10151
25°	9912
30°	9646
35°	9339
40°	8981
45°	8609
50°	8158
55°	7063
60°	3614
65°	700
70°	65
75°	86
80°	87
85°	82

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8609 cd/sqm

TEST NUMBER: P866240

CATALOG NUMBER: PRLX-2002-M-930-35L-L-U-S-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.8	4.7
10°-20°	354.9	13.2
20°-30°	519.7	19.3
30°-40°	599.7	22.3
40°-50°	588.0	21.9
50°-60°	427.3	15.9
60°-70°	65.5	2.4
70°-80°	2.6	0.1
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1001.4	37.3
0°-40°	1601.1	59.6
0°-60°	2616.3	97.4
0°-90°	2685.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2685.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1350	
5°	1340	127
15°	1260	355
25°	1129	520
35°	962	600
45°	765	588
55°	509	427
65°	37	65
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P866240

CATALOG NUMBER: PRLX-2002-M-930-35L-L-U-S-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	1349.8
2.5°	1347.9
5°	1339.5
7.5°	1325.6
10°	1307.9
12.5°	1285.5
15°	1260.4
17.5°	1230.6
20°	1199.0
22.5°	1164.5
25°	1129.2
27.5°	1090.1
30°	1050.0
32.5°	1003.5
35°	961.6
37.5°	910.4
40°	864.8
42.5°	812.7
45°	765.2
47.5°	708.4
50°	659.1
52.5°	593.0
55°	509.2
57.5°	376.1
60°	227.1
62.5°	108.0
65°	37.2
67.5°	9.3
70°	2.8
72.5°	2.8
75°	2.8
77.5°	1.9
80°	1.9
82.5°	1.9
85°	0.9
87.5°	0.9
90°	0.0



TEST NUMBER: P866240
 CATALOG NUMBER: PRLX-2002-M-930-35L-L-U-S-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.68	19.10	18.05	19.41	19.72	17.68	19.10	18.05	19.41	19.72
	3H	17.57	18.81	17.94	19.14	19.50	17.57	18.81	17.94	19.14	19.50
	4H	17.50	18.65	17.90	19.00	19.38	17.50	18.65	17.90	19.00	19.38
	6H	17.43	18.48	17.84	18.85	19.25	17.43	18.48	17.84	18.85	19.25
	8H	17.39	18.39	17.82	18.78	19.18	17.39	18.39	17.82	18.78	19.18
	12H	17.35	18.30	17.78	18.69	19.12	17.35	18.30	17.78	18.69	19.12
4H	2H	17.52	18.67	17.92	19.02	19.40	17.52	18.67	17.92	19.02	19.40
	3H	17.41	18.33	17.82	18.73	19.14	17.41	18.33	17.82	18.73	19.14
	4H	17.32	18.15	17.76	18.56	19.01	17.32	18.15	17.76	18.56	19.01
	6H	17.25	17.96	17.71	18.40	18.87	17.25	17.96	17.71	18.40	18.87
	8H	17.19	17.86	17.66	18.30	18.77	17.19	17.86	17.66	18.30	18.77
	12H	17.15	17.73	17.63	18.22	18.69	17.15	17.73	17.63	18.22	18.69
8H	4H	17.19	17.85	17.66	18.30	18.77	17.19	17.85	17.66	18.30	18.77
	6H	17.09	17.64	17.59	18.13	18.61	17.09	17.64	17.59	18.13	18.61
	8H	17.02	17.52	17.54	18.03	18.52	17.02	17.52	17.54	18.03	18.52
	12H	16.97	17.42	17.49	17.91	18.48	16.97	17.42	17.49	17.91	18.48
12H	4H	17.15	17.73	17.63	18.22	18.69	17.15	17.73	17.63	18.22	18.69
	6H	17.02	17.52	17.54	18.03	18.52	17.02	17.52	17.54	18.03	18.52
	8H	16.97	17.42	17.49	17.91	18.48	16.97	17.42	17.49	17.91	18.48