

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866290

Luminaire Tested: PRLX-2002-M-935-15L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866290
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-52)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-M-935-15L-L-U-S-X-X-GREY-X
Description: PRENATALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1248.8 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.27
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866290

CATALOG NUMBER: PRLX-2002-M-935-15L-L-U-S-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P866290

CATALOG NUMBER: PRLX-2002-M-935-15L-L-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69
4	89	78	71	65	86	77	70	65	75	69	64	73	67	63	71	66	62	60
5	82	71	63	57	80	70	63	57	68	61	56	66	60	56	64	59	55	53
6	76	64	56	51	74	64	56	51	62	55	50	60	54	50	59	53	49	48
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	48	44	43
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	40	36	35
10	58	46	39	34	57	45	38	34	45	38	34	44	38	33	43	37	33	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4961
5°	4941
10°	4873
15°	4774
20°	4662
25°	4537
30°	4405
35°	4258
40°	4096
45°	3929
50°	3723
55°	3280
60°	1749
65°	459
70°	188
75°	212
80°	243
85°	301

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3929 cd/sqm

TEST NUMBER: P866290

CATALOG NUMBER: PRLX-2002-M-935-15L-L-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.6	4.7
10°-20°	163.2	13.1
20°-30°	238.0	19.1
30°-40°	273.9	21.9
40°-50°	268.8	21.5
50°-60°	199.1	15.9
60°-70°	36.7	2.9
70°-80°	7.2	0.6
80°-90°	3.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	459.8	36.8
0°-40°	733.7	58.8
0°-60°	1201.5	96.2
0°-90°	1248.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1248.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	624	
5°	619	59
15°	580	163
25°	517	238
35°	438	274
45°	349	269
55°	236	199
65°	24	37
75°	7	7
85°	3	3
90°	0	

TEST NUMBER: P866290

CATALOG NUMBER: PRLX-2002-M-935-15L-L-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	623.6
2.5°	622.8
5°	618.7
7.5°	612.2
10°	603.2
12.5°	592.2
15°	579.6
17.5°	565.4
20°	550.7
22.5°	534.4
25°	516.9
27.5°	498.6
30°	479.5
32.5°	459.1
35°	438.4
37.5°	416.4
40°	394.4
42.5°	371.6
45°	349.2
47.5°	324.8
50°	300.8
52.5°	274.3
55°	236.5
57.5°	178.7
60°	109.9
62.5°	56.6
65°	24.4
67.5°	10.6
70°	8.1
72.5°	7.7
75°	6.9
77.5°	6.1
80°	5.3
82.5°	4.5
85°	3.3
87.5°	1.6
90°	0.0



TEST NUMBER: P866290
 CATALOG NUMBER: PRLX-2002-M-935-15L-L-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.16	16.59	15.52	16.90	17.22	15.16	16.59	15.52	16.90	17.22
	3H	15.06	16.32	15.44	16.65	17.01	15.06	16.32	15.44	16.65	17.01
	4H	15.01	16.17	15.41	16.52	16.91	15.01	16.17	15.41	16.52	16.91
	6H	14.95	16.02	15.36	16.39	16.79	14.95	16.02	15.36	16.39	16.79
	8H	14.92	15.94	15.35	16.33	16.73	14.92	15.94	15.35	16.33	16.73
	12H	14.89	15.86	15.32	16.25	16.68	14.89	15.86	15.32	16.25	16.68
4H	2H	15.01	16.18	15.41	16.53	16.91	15.01	16.18	15.41	16.53	16.91
	3H	14.92	15.87	15.34	16.27	16.67	14.92	15.87	15.34	16.27	16.67
	4H	14.86	15.70	15.30	16.12	16.56	14.86	15.70	15.30	16.12	16.56
	6H	14.82	15.54	15.28	15.99	16.45	14.82	15.54	15.28	15.99	16.45
	8H	14.78	15.46	15.25	15.91	16.38	14.78	15.46	15.25	15.91	16.38
	12H	14.76	15.36	15.24	15.84	16.31	14.76	15.36	15.24	15.84	16.31
8H	4H	14.75	15.42	15.22	15.87	16.34	14.75	15.42	15.22	15.87	16.34
	6H	14.69	15.25	15.19	15.74	16.22	14.69	15.25	15.19	15.74	16.22
	8H	14.65	15.16	15.17	15.67	16.16	14.65	15.16	15.17	15.67	16.16
	12H	14.64	15.09	15.15	15.59	16.16	14.64	15.09	15.15	15.59	16.16
12H	4H	14.71	15.31	15.19	15.79	16.26	14.71	15.31	15.19	15.79	16.26
	6H	14.63	15.14	15.15	15.65	16.14	14.63	15.14	15.15	15.65	16.14
	8H	14.62	15.07	15.13	15.57	16.14	14.62	15.07	15.13	15.57	16.14