

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866329

Luminaire Tested: PRLX-2002-M-935-65L-L-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866329
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-51)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Pentalux
Catalog Number: PRLX-2002-M-935-65L-L-U-S-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 7
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5411.5 lumens
Efficiency: N/A
Efficacy: 92.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 58.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866329

CATALOG NUMBER: PRLX-2002-M-935-65L-L-U-S-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P866329

CATALOG NUMBER: PRLX-2002-M-935-65L-L-U-S-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	101	99	97	98	96	94	94	93	91	89
2	103	97	91	87	101	95	90	86	92	88	84	89	85	82	86	83	80	78
3	96	87	80	75	93	86	79	74	83	77	73	80	76	72	78	74	71	69
4	89	78	71	65	86	77	70	65	75	69	64	73	67	63	71	66	62	60
5	82	71	63	57	80	70	62	57	68	61	56	66	60	56	64	59	55	53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	48
7	71	59	51	45	69	58	51	45	57	50	45	55	49	45	54	48	44	43
8	66	54	46	41	65	53	46	41	52	45	40	51	45	40	50	44	40	38
9	62	50	42	37	61	49	42	37	48	41	37	47	41	37	46	40	36	35
10	58	46	39	34	57	45	38	34	44	38	34	44	38	33	43	37	33	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	21442
5°	21354
10°	21060
15°	20658
20°	20174
25°	19648
30°	19088
35°	18449
40°	17769
45°	17007
50°	16133
55°	13895
60°	7661
65°	2157
70°	861
75°	922
80°	1049
85°	1287

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 17007 cd/sqm

TEST NUMBER: P866329

CATALOG NUMBER: PRLX-2002-M-935-65L-L-U-S-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	253.0	4.7
10°-20°	706.2	13.1
20°-30°	1030.6	19.0
30°-40°	1187.5	21.9
40°-50°	1165.8	21.5
50°-60°	855.0	15.8
60°-70°	167.5	3.1
70°-80°	31.7	0.6
80°-90°	14.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1989.9	36.8
0°-40°	3177.3	58.7
0°-60°	5198.2	96.1
0°-90°	5411.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5411.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2695	
5°	2674	253
15°	2508	706
25°	2238	1031
35°	1900	1187
45°	1512	1166
55°	1002	855
65°	115	167
75°	30	32
85°	14	14
90°	0	

TEST NUMBER: P866329

CATALOG NUMBER: PRLX-2002-M-935-65L-L-U-S-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	2695.1
2.5°	2691.6
5°	2673.9
7.5°	2644.0
10°	2606.9
12.5°	2562.8
15°	2508.1
17.5°	2446.4
20°	2382.9
22.5°	2312.4
25°	2238.3
27.5°	2160.7
30°	2077.8
32.5°	1989.6
35°	1899.6
37.5°	1806.1
40°	1710.9
42.5°	1613.9
45°	1511.6
47.5°	1411.0
50°	1303.5
52.5°	1181.8
55°	1001.8
57.5°	767.3
60°	481.5
62.5°	259.3
65°	114.6
67.5°	52.9
70°	37.0
72.5°	33.5
75°	30.0
77.5°	26.5
80°	22.9
82.5°	19.4
85°	14.1
87.5°	7.1
90°	0.0



TEST NUMBER: P866329

CATALOG NUMBER: PRLX-2002-M-935-65L-L-U-S-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.20	21.62	20.56	21.94	22.25	20.20	21.62	20.56	21.94	22.25
	3H	20.10	21.36	20.48	21.69	22.05	20.10	21.36	20.48	21.69	22.05
	4H	20.05	21.22	20.45	21.57	21.95	20.05	21.22	20.45	21.57	21.95
	6H	19.99	21.07	20.41	21.44	21.83	19.99	21.07	20.41	21.44	21.83
	8H	19.96	20.98	20.39	21.37	21.78	19.96	20.98	20.39	21.37	21.78
	12H	19.94	20.91	20.37	21.29	21.72	19.94	20.91	20.37	21.29	21.72
4H	2H	20.06	21.23	20.46	21.58	21.96	20.06	21.23	20.46	21.58	21.96
	3H	19.97	20.92	20.39	21.32	21.72	19.97	20.92	20.39	21.32	21.72
	4H	19.91	20.75	20.35	21.17	21.61	19.91	20.75	20.35	21.17	21.61
	6H	19.87	20.59	20.33	21.04	21.50	19.87	20.59	20.33	21.04	21.50
	8H	19.83	20.51	20.30	20.96	21.43	19.83	20.51	20.30	20.96	21.43
	12H	19.81	20.41	20.29	20.89	21.37	19.81	20.41	20.29	20.89	21.37
8H	4H	19.80	20.48	20.27	20.92	21.39	19.80	20.48	20.27	20.92	21.39
	6H	19.74	20.30	20.24	20.79	21.27	19.74	20.30	20.24	20.79	21.27
	8H	19.71	20.21	20.22	20.73	21.22	19.71	20.21	20.22	20.73	21.22
	12H	19.69	20.15	20.20	20.64	21.21	19.69	20.15	20.20	20.64	21.21
12H	4H	19.76	20.36	20.24	20.84	21.31	19.76	20.36	20.24	20.84	21.31
	6H	19.68	20.19	20.20	20.70	21.19	19.68	20.19	20.20	20.70	21.19
	8H	19.67	20.13	20.18	20.62	21.19	19.67	20.13	20.18	20.62	21.19