

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865586

Luminaire Tested: PRLX-2002-S-927-10L-L-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865586
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-S-927-10L-L-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, TRUNCATED DOME WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 720.9 lumens
Efficiency: N/A
Efficacy: 68.7 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Circular (Dia: 0.85' x H: 0')
CIE Type: Direct

Input Watts (W): 10.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865586

CATALOG NUMBER: PRLX-2002-S-927-10L-L-U-S-X-X-GREY-X

Luminous Intensity Polar Plot



TEST NUMBER: P865586

CATALOG NUMBER: PRLX-2002-S-927-10L-L-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	89
2	104	97	92	87	101	95	90	86	92	88	84	89	85	82	86	83	81	79
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69
4	89	79	71	66	87	77	71	65	75	69	64	73	68	64	71	66	63	61
5	82	71	63	58	80	70	63	57	68	62	57	66	61	56	65	60	56	54
6	76	65	57	51	75	64	56	51	62	55	51	61	55	50	59	54	50	48
7	71	59	51	46	70	58	51	46	57	50	45	55	49	45	54	49	45	43
8	66	54	46	41	65	54	46	41	52	46	41	51	45	41	50	45	40	39
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35
10	58	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6819
5°	6784
10°	6695
15°	6561
20°	6409
25°	6247
30°	6069
35°	5868
40°	5667
45°	5459
50°	5164
55°	4189
60°	1984
65°	604
70°	308
75°	348
80°	346
85°	517

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5459 cd/sqm

TEST NUMBER: P865586

CATALOG NUMBER: PRLX-2002-S-927-10L-L-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.1	4.7
10°-20°	95.0	13.2
20°-30°	138.7	19.2
30°-40°	160.2	22.2
40°-50°	158.0	21.9
50°-60°	109.3	15.2
60°-70°	18.7	2.6
70°-80°	4.8	0.7
80°-90°	2.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	267.8	37.2
0°-40°	428.0	59.4
0°-60°	695.3	96.4
0°-90°	720.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	720.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	363	
5°	360	34
15°	337	95
25°	301	139
35°	256	160
45°	206	158
55°	128	109
65°	14	19
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P865586

CATALOG NUMBER: PRLX-2002-S-927-10L-L-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	363.0
2.5°	363.0
5°	359.8
7.5°	355.8
10°	351.0
12.5°	344.6
15°	337.4
17.5°	329.4
20°	320.6
22.5°	311.0
25°	301.4
27.5°	291.0
30°	279.8
32.5°	268.7
35°	255.9
37.5°	243.9
40°	231.1
42.5°	218.3
45°	205.5
47.5°	191.1
50°	176.7
52.5°	158.3
55°	127.9
57.5°	91.2
60°	52.8
62.5°	27.2
65°	13.6
67.5°	6.4
70°	5.6
72.5°	4.8
75°	4.8
77.5°	4.0
80°	3.2
82.5°	3.2
85°	2.4
87.5°	0.8
90°	0.0



TEST NUMBER: P865586
 CATALOG NUMBER: PRLX-2002-S-927-10L-L-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.37	16.79	15.74	17.10	17.42	15.37	16.79	15.74	17.10	17.42
	3H	15.28	16.53	15.66	16.86	17.22	15.28	16.53	15.66	16.86	17.22
	4H	15.24	16.40	15.64	16.75	17.13	15.24	16.40	15.64	16.75	17.13
	6H	15.19	16.26	15.60	16.62	17.02	15.19	16.26	15.60	16.62	17.02
	8H	15.17	16.18	15.60	16.57	16.97	15.17	16.18	15.60	16.57	16.97
	12H	15.15	16.11	15.58	16.50	16.93	15.15	16.11	15.58	16.50	16.93
4H	2H	15.23	16.39	15.63	16.74	17.12	15.23	16.39	15.63	16.74	17.12
	3H	15.15	16.09	15.57	16.49	16.90	15.15	16.09	15.57	16.49	16.90
	4H	15.11	15.94	15.54	16.36	16.80	15.11	15.94	15.54	16.36	16.80
	6H	15.08	15.80	15.54	16.24	16.71	15.08	15.80	15.54	16.24	16.71
	8H	15.06	15.73	15.53	16.18	16.65	15.06	15.73	15.53	16.18	16.65
	12H	15.05	15.65	15.54	16.13	16.60	15.05	15.65	15.54	16.13	16.60
8H	4H	15.00	15.67	15.47	16.12	16.59	15.00	15.67	15.47	16.12	16.59
	6H	14.96	15.52	15.46	16.01	16.49	14.96	15.52	15.46	16.01	16.49
	8H	14.95	15.45	15.47	15.97	16.46	14.95	15.45	15.47	15.97	16.46
	12H	14.97	15.42	15.48	15.91	16.48	14.97	15.42	15.48	15.91	16.48
12H	4H	14.96	15.56	15.45	16.04	16.51	14.96	15.56	15.45	16.04	16.51
	6H	14.91	15.41	15.43	15.93	16.42	14.91	15.41	15.43	15.93	16.42
	8H	14.92	15.38	15.44	15.87	16.44	14.92	15.38	15.44	15.87	16.44