

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865629

Luminaire Tested: PRLX-2002-S-930-15L-G-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865629  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Pentalux  
Catalog Number: PRLX-2002-S-930-15L-G-U-S-X-X-BRSS-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS, TRUNCATED DOME WITH BRASS INTERIOR SHADE.  
LIGHT LEVEL 3  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 494.0 lumens  
Efficiency: N/A  
Efficacy: 31.7 lumens/watt  
Spacing Criteria (0/90/45): 1.36 / 1.36 / 1.52  
Luminous Opening: Circular (Dia: 0.85' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865629

CATALOG NUMBER: PRLX-2002-S-930-15L-G-U-S-X-X-BRSS-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865629

CATALOG NUMBER: PRLX-2002-S-930-15L-G-U-S-X-X-BRSS-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	99	95	105	101	97	93	97	93	90		93	90	87		89	87	85	83
2	98	89	82	76	95	87	81	75	84	78	73		80	76	72		77	74	70	68
3	89	78	69	63	86	76	68	62	73	66	61		70	65	60		68	63	59	56
4	81	69	59	52	79	67	59	52	65	57	51		62	56	51		60	54	50	48
5	74	61	52	45	72	60	51	44	58	50	44		56	49	43		54	48	43	41
6	68	55	45	39	66	54	45	38	52	44	38		50	43	38		48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33		45	38	33		44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30		41	35	29		40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27		38	31	26		37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24		35	29	24		34	28	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	2761
5°	2770
10°	2789
15°	2802
20°	2823
25°	2854
30°	2898
35°	2970
40°	3070
45°	3185
50°	3235
55°	3200
60°	3107
65°	2969
70°	2796
75°	2598
80°	2337
85°	2091

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 50°  
 Luminance: 3235 cd/sqm

TEST NUMBER: P865629

CATALOG NUMBER: PRLX-2002-S-930-15L-G-U-S-X-X-BRSS-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	14.0	2.8
10°-20°	40.7	8.2
20°-30°	63.6	12.9
30°-40°	81.2	16.4
40°-50°	92.2	18.7
50°-60°	87.0	17.6
60°-70°	66.2	13.4
70°-80°	38.0	7.7
80°-90°	11.2	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	118.3	23.9
0°-40°	199.5	40.4
0°-60°	378.7	76.7
0°-90°	494.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	494.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	147	
5°	147	14
15°	144	41
25°	138	64
35°	130	81
45°	120	92
55°	98	87
65°	67	66
75°	36	38
85°	10	11
90°	0	

TEST NUMBER: P865629

CATALOG NUMBER: PRLX-2002-S-930-15L-G-U-S-X-X-BRSS-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	147.0
2.5°	147.0
5°	146.9
7.5°	146.7
10°	146.2
12.5°	145.3
15°	144.1
17.5°	142.7
20°	141.2
22.5°	139.5
25°	137.7
27.5°	135.6
30°	133.6
32.5°	131.7
35°	129.5
37.5°	127.4
40°	125.2
42.5°	122.9
45°	119.9
47.5°	116.0
50°	110.7
52.5°	104.5
55°	97.7
57.5°	90.2
60°	82.7
62.5°	74.8
65°	66.8
67.5°	59.0
70°	50.9
72.5°	43.4
75°	35.8
77.5°	28.6
80°	21.6
82.5°	15.4
85°	9.7
87.5°	5.1
90°	0.0



TEST NUMBER: P865629

CATALOG NUMBER: PRLX-2002-S-930-15L-G-U-S-X-X-BRSS-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.43	18.13	16.80	18.44	18.76	16.43	18.13	16.80	18.44	18.76
	3H	18.23	19.77	18.61	20.09	20.45	18.23	19.77	18.61	20.09	20.45
	4H	18.90	20.35	19.30	20.70	21.07	18.90	20.35	19.30	20.70	21.07
	6H	19.40	20.75	19.81	21.11	21.50	19.40	20.75	19.81	21.11	21.50
	8H	19.57	20.86	19.99	21.24	21.64	19.57	20.86	19.99	21.24	21.64
	12H	19.69	20.92	20.11	21.30	21.73	19.69	20.92	20.11	21.30	21.73
4H	2H	17.07	18.52	17.47	18.87	19.24	17.07	18.52	17.47	18.87	19.24
	3H	19.09	20.31	19.50	20.71	21.11	19.09	20.31	19.50	20.71	21.11
	4H	19.89	21.00	20.32	21.41	21.85	19.89	21.00	20.32	21.41	21.85
	6H	20.52	21.49	20.97	21.93	22.38	20.52	21.49	20.97	21.93	22.38
	8H	20.74	21.65	21.20	22.09	22.55	20.74	21.65	21.20	22.09	22.55
	12H	20.90	21.72	21.38	22.20	22.66	20.90	21.72	21.38	22.20	22.66
8H	4H	20.22	21.12	20.67	21.56	22.03	20.22	21.12	20.67	21.56	22.03
	6H	20.97	21.73	21.46	22.21	22.68	20.97	21.73	21.46	22.21	22.68
	8H	21.26	21.94	21.77	22.44	22.93	21.26	21.94	21.77	22.44	22.93
	12H	21.50	22.11	22.01	22.60	23.15	21.50	22.11	22.01	22.60	23.15
12H	4H	20.25	21.07	20.73	21.55	22.01	20.25	21.07	20.73	21.55	22.01
	6H	21.03	21.71	21.53	22.21	22.70	21.03	21.71	21.53	22.21	22.70
	8H	21.38	21.98	21.89	22.47	23.03	21.38	21.98	21.89	22.47	23.03