

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865652

Luminaire Tested: PRLX-2002-S-935-05L-G-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865652  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-10)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Pentalux  
Catalog Number: PRLX-2002-S-935-05L-G-U-S-X-X-BLAK-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS, TRUNCATED DOME WITH BLACK INTERIOR SHADE.  
LIGHT LEVEL 1  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 141.4 lumens  
Efficiency: N/A  
Efficacy: 22.8 lumens/watt  
Spacing Criteria (0/90/45): 1.5 / 1.5 / 1.65  
Luminous Opening: Circular (Dia: 0.85' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 6.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865652

CATALOG NUMBER: PRLX-2002-S-935-05L-G-U-S-X-X-BLAK-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865652

CATALOG NUMBER: PRLX-2002-S-935-05L-G-U-S-X-X-BLAK-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	98	94	105	100	96	92	96	93	89		92	89	87		89	86	84	82
2	97	88	81	75	95	87	80	74	83	77	72		80	75	71		77	73	69	67
3	88	77	68	61	86	75	67	61	72	65	59		69	63	58		67	62	57	55
4	80	67	58	51	78	66	57	51	63	56	50		61	54	49		59	53	48	46
5	73	60	50	43	71	59	50	43	56	48	42		54	47	42		52	46	41	39
6	67	53	44	37	65	52	43	37	50	42	37		49	42	36		47	41	36	34
7	62	48	39	32	60	47	38	32	46	38	32		44	37	32		43	36	31	29
8	58	43	35	28	56	43	34	28	41	34	28		40	33	28		39	33	28	26
9	54	40	31	25	52	39	31	25	38	30	25		37	30	25		36	29	25	23
10	50	36	28	23	49	36	28	23	35	28	23		34	27	22		33	27	22	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	686
5°	690
10°	702
15°	716
20°	732
25°	757
30°	785
35°	823
40°	873
45°	927
50°	961
55°	963
60°	943
65°	907
70°	857
75°	791
80°	714
85°	625

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 52.5°  
 Luminance: 963 cd/sqm

TEST NUMBER: P865652

CATALOG NUMBER: PRLX-2002-S-935-05L-G-U-S-X-X-BLAK-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	3.5	2.5
10°-20°	10.4	7.4
20°-30°	16.9	11.9
30°-40°	22.5	15.9
40°-50°	26.8	19.0
50°-60°	26.2	18.5
60°-70°	20.2	14.3
70°-80°	11.5	8.2
80°-90°	3.3	2.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	30.8	21.8
0°-40°	53.3	37.7
0°-60°	106.3	75.2
0°-90°	141.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	141.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	36	
5°	37	3
15°	37	10
25°	36	17
35°	36	23
45°	35	27
55°	29	26
65°	20	20
75°	11	12
85°	3	3
90°	0	

TEST NUMBER: P865652

CATALOG NUMBER: PRLX-2002-S-935-05L-G-U-S-X-X-BLAK-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	36.5
2.5°	36.5
5°	36.6
7.5°	36.7
10°	36.8
12.5°	36.8
15°	36.8
17.5°	36.7
20°	36.6
22.5°	36.6
25°	36.5
27.5°	36.3
30°	36.2
32.5°	36.1
35°	35.9
37.5°	35.7
40°	35.6
42.5°	35.4
45°	34.9
47.5°	34.2
50°	32.9
52.5°	31.2
55°	29.4
57.5°	27.3
60°	25.1
62.5°	22.8
65°	20.4
67.5°	18.0
70°	15.6
72.5°	13.2
75°	10.9
77.5°	8.6
80°	6.6
82.5°	4.6
85°	2.9
87.5°	1.5
90°	0.0

TEST NUMBER: P865652  
 CATALOG NUMBER: PRLX-2002-S-935-05L-G-U-S-X-X-BLAK-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.44	14.16	12.80	14.48	14.79	12.44	14.16	12.80	14.48	14.79
	3H	14.26	15.83	14.64	16.16	16.51	14.26	15.83	14.64	16.16	16.51
	4H	14.94	16.42	15.33	16.77	17.14	14.94	16.42	15.33	16.77	17.14
	6H	15.43	16.81	15.84	17.17	17.56	15.43	16.81	15.84	17.17	17.56
	8H	15.60	16.91	16.02	17.30	17.70	15.60	16.91	16.02	17.30	17.70
	12H	15.71	16.98	16.14	17.36	17.79	15.71	16.98	16.14	17.36	17.79
4H	2H	13.09	14.57	13.49	14.92	15.29	13.09	14.57	13.49	14.92	15.29
	3H	15.14	16.38	15.54	16.78	17.18	15.14	16.38	15.54	16.78	17.18
	4H	15.94	17.07	16.37	17.49	17.92	15.94	17.07	16.37	17.49	17.92
	6H	16.57	17.56	17.02	18.00	18.45	16.57	17.56	17.02	18.00	18.45
	8H	16.78	17.71	17.24	18.15	18.61	16.78	17.71	17.24	18.15	18.61
	12H	16.94	17.78	17.42	18.26	18.72	16.94	17.78	17.42	18.26	18.72
8H	4H	16.27	17.20	16.72	17.64	18.10	16.27	17.20	16.72	17.64	18.10
	6H	17.02	17.79	17.51	18.28	18.75	17.02	17.79	17.51	18.28	18.75
	8H	17.30	18.00	17.81	18.50	18.99	17.30	18.00	17.81	18.50	18.99
	12H	17.54	18.16	18.05	18.65	19.21	17.54	18.16	18.05	18.65	19.21
12H	4H	16.31	17.15	16.78	17.62	18.09	16.31	17.15	16.78	17.62	18.09
	6H	17.08	17.78	17.58	18.28	18.76	17.08	17.78	17.58	18.28	18.76
	8H	17.42	18.04	17.93	18.53	19.09	17.42	18.04	17.93	18.53	19.09