

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865701

Luminaire Tested: PRLX-2002-S-940-10L-G-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865701  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-8)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2002-S-940-10L-G-U-S-X-X-BRSS-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS, TRUNCATED DOME WITH BRASS INTERIOR SHADE.  
LIGHT LEVEL 2  
Light Source: 4000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 356.6 lumens  
Efficiency: N/A  
Efficacy: 34.0 lumens/watt  
Spacing Criteria (0/90/45): 1.36 / 1.36 / 1.52  
Luminous Opening: Circular (Dia: 0.85' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 10.5  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865701

CATALOG NUMBER: PRLX-2002-S-940-10L-G-U-S-X-X-BRSS-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865701

CATALOG NUMBER: PRLX-2002-S-940-10L-G-U-S-X-X-BRSS-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	99	95	105	101	97	93	97	93	90		93	90	87		89	87	85	83
2	98	89	82	76	95	87	81	75	84	78	73		80	76	72		77	74	70	68
3	89	78	69	63	86	76	68	62	73	66	61		70	65	60		68	63	59	56
4	81	69	59	52	79	67	59	52	65	57	51		62	56	51		60	54	50	48
5	74	61	52	45	72	60	51	44	58	50	44		56	49	43		54	48	43	41
6	68	55	45	39	66	54	45	38	52	44	38		50	43	38		48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33		45	38	33		44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30		41	35	29		40	34	29	27
9	55	41	33	27	53	40	32	27	39	32	27		38	31	26		37	31	26	24
10	51	38	30	24	50	37	29	24	36	29	24		35	29	24		34	28	24	22

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1993
5°	1999
10°	2014
15°	2024
20°	2037
25°	2060
30°	2093
35°	2144
40°	2217
45°	2301
50°	2335
55°	2312
60°	2243
65°	2142
70°	2021
75°	1872
80°	1688
85°	1509

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 50°  
 Luminance: 2335 cd/sqm

TEST NUMBER: P865701

CATALOG NUMBER: PRLX-2002-S-940-10L-G-U-S-X-X-BRSS-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	10.1	2.8
10°-20°	29.4	8.2
20°-30°	45.9	12.9
30°-40°	58.7	16.5
40°-50°	66.5	18.7
50°-60°	62.8	17.6
60°-70°	47.8	13.4
70°-80°	27.4	7.7
80°-90°	8.0	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	85.4	23.9
0°-40°	144.1	40.4
0°-60°	273.4	76.7
0°-90°	356.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	356.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	106	
5°	106	10
15°	104	29
25°	99	46
35°	94	59
45°	87	67
55°	71	63
65°	48	48
75°	26	27
85°	7	8
90°	0	

TEST NUMBER: P865701

CATALOG NUMBER: PRLX-2002-S-940-10L-G-U-S-X-X-BRSS-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	106.1
2.5°	106.1
5°	106.0
7.5°	105.9
10°	105.6
12.5°	104.9
15°	104.1
17.5°	103.0
20°	101.9
22.5°	100.7
25°	99.4
27.5°	97.9
30°	96.5
32.5°	95.1
35°	93.5
37.5°	92.0
40°	90.4
42.5°	88.7
45°	86.6
47.5°	83.7
50°	79.9
52.5°	75.4
55°	70.6
57.5°	65.1
60°	59.7
62.5°	54.0
65°	48.2
67.5°	42.6
70°	36.8
72.5°	31.3
75°	25.8
77.5°	20.7
80°	15.6
82.5°	11.1
85°	7.0
87.5°	3.6
90°	0.0



TEST NUMBER: P865701  
 CATALOG NUMBER: PRLX-2002-S-940-10L-G-U-S-X-X-BRSS-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	15.30	16.99	15.67	17.31	17.62	15.30	16.99	15.67	17.31	17.62
	3H	17.10	18.64	17.47	18.96	19.32	17.10	18.64	17.47	18.96	19.32
	4H	17.77	19.22	18.17	19.57	19.94	17.77	19.22	18.17	19.57	19.94
	6H	18.27	19.62	18.68	19.98	20.37	18.27	19.62	18.68	19.98	20.37
	8H	18.44	19.72	18.86	20.11	20.51	18.44	19.72	18.86	20.11	20.51
	12H	18.55	19.79	18.98	20.17	20.60	18.55	19.79	18.98	20.17	20.60
4H	2H	15.94	17.39	16.34	17.74	18.11	15.94	17.39	16.34	17.74	18.11
	3H	17.96	19.18	18.37	19.57	19.97	17.96	19.18	18.37	19.57	19.97
	4H	18.76	19.87	19.19	20.28	20.71	18.76	19.87	19.19	20.28	20.71
	6H	19.39	20.36	19.84	20.80	21.25	19.39	20.36	19.84	20.80	21.25
	8H	19.61	20.51	20.07	20.96	21.42	19.61	20.51	20.07	20.96	21.42
	12H	19.77	20.59	20.25	21.06	21.53	19.77	20.59	20.25	21.06	21.53
8H	4H	19.08	19.99	19.54	20.43	20.89	19.08	19.99	19.54	20.43	20.89
	6H	19.84	20.59	20.33	21.08	21.55	19.84	20.59	20.33	21.08	21.55
	8H	20.13	20.81	20.63	21.31	21.80	20.13	20.81	20.63	21.31	21.80
	12H	20.37	20.97	20.88	21.46	22.02	20.37	20.97	20.88	21.46	22.02
12H	4H	19.12	19.94	19.60	20.41	20.88	19.12	19.94	19.60	20.41	20.88
	6H	19.90	20.58	20.40	21.08	21.57	19.90	20.58	20.40	21.08	21.57
	8H	20.25	20.85	20.75	21.34	21.90	20.25	20.85	20.75	21.34	21.90