

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865710

Luminaire Tested: PRLX-2002-S-940-15L-G-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865710
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-9)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2002-S-940-15L-G-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, GLOBE LENS, TRUNCATED DOME WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 3
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 531.4 lumens
Efficiency: N/A
Efficacy: 34.1 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.53
Luminous Opening: Circular (Dia: 0.85' x H: 0')
CIE Type: Direct

Input Watts (W): 15.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865710

CATALOG NUMBER: PRLX-2002-S-940-15L-G-U-S-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P865710

CATALOG NUMBER: PRLX-2002-S-940-15L-G-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	108	103	99	95	105	101	97	93	97	93	90	93	90	87	89	87	85	83
2	98	89	82	76	95	87	81	75	84	78	73	80	76	72	77	73	70	68
3	89	78	69	62	86	76	68	62	73	66	61	70	65	60	68	63	59	56
4	81	68	59	52	79	67	59	52	65	57	51	62	56	50	60	54	50	47
5	74	61	51	45	72	60	51	44	57	50	44	55	49	43	54	48	43	41
6	68	54	45	39	66	54	45	38	52	44	38	50	43	38	48	42	37	35
7	63	49	40	34	61	48	40	34	47	39	33	45	38	33	44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30	41	34	29	40	34	29	27
9	55	41	32	27	53	40	32	27	39	32	26	38	31	26	37	31	26	24
10	51	38	29	24	50	37	29	24	36	29	24	35	28	24	34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2947
5°	2959
10°	2979
15°	2997
20°	3018
25°	3057
30°	3108
35°	3190
40°	3301
45°	3427
50°	3486
55°	3442
60°	3355
65°	3205
70°	3032
75°	2801
80°	2531
85°	2306

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 50°
 Luminance: 3486 cd/sqm

TEST NUMBER: P865710

CATALOG NUMBER: PRLX-2002-S-940-15L-G-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	15.0	2.8
10°-20°	43.6	8.2
20°-30°	68.1	12.8
30°-40°	87.3	16.4
40°-50°	99.2	18.7
50°-60°	93.8	17.7
60°-70°	71.4	13.4
70°-80°	41.1	7.7
80°-90°	12.1	2.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	126.6	23.8
0°-40°	213.9	40.2
0°-60°	406.8	76.6
0°-90°	531.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	531.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	157	
5°	157	15
15°	154	44
25°	148	68
35°	139	87
45°	129	99
55°	105	94
65°	72	71
75°	39	41
85°	11	12
90°	0	

TEST NUMBER: P865710

CATALOG NUMBER: PRLX-2002-S-940-15L-G-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	156.9
2.5°	156.9
5°	156.9
7.5°	156.8
10°	156.2
12.5°	155.4
15°	154.1
17.5°	152.6
20°	151.0
22.5°	149.3
25°	147.5
27.5°	145.4
30°	143.3
32.5°	141.3
35°	139.1
37.5°	137.0
40°	134.6
42.5°	132.1
45°	129.0
47.5°	124.9
50°	119.3
52.5°	112.7
55°	105.1
57.5°	97.3
60°	89.3
62.5°	80.7
65°	72.1
67.5°	63.7
70°	55.2
72.5°	46.9
75°	38.6
77.5°	30.9
80°	23.4
82.5°	16.6
85°	10.7
87.5°	5.5
90°	0.0

TEST NUMBER: P865710
 CATALOG NUMBER: PRLX-2002-S-940-15L-G-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.70	18.40	17.07	18.72	19.03	16.70	18.40	17.07	18.72	19.03
	3H	18.51	20.05	18.88	20.37	20.73	18.51	20.05	18.88	20.37	20.73
	4H	19.18	20.63	19.58	20.98	21.35	19.18	20.63	19.58	20.98	21.35
	6H	19.68	21.03	20.09	21.39	21.78	19.68	21.03	20.09	21.39	21.78
	8H	19.85	21.14	20.27	21.52	21.92	19.85	21.14	20.27	21.52	21.92
	12H	19.97	21.20	20.40	21.59	22.01	19.97	21.20	20.40	21.59	22.01
4H	2H	17.35	18.80	17.74	19.14	19.52	17.35	18.80	17.74	19.14	19.52
	3H	19.37	20.59	19.78	20.99	21.39	19.37	20.59	19.78	20.99	21.39
	4H	20.17	21.28	20.60	21.69	22.13	20.17	21.28	20.60	21.69	22.13
	6H	20.80	21.77	21.26	22.21	22.67	20.80	21.77	21.26	22.21	22.67
	8H	21.02	21.93	21.48	22.37	22.83	21.02	21.93	21.48	22.37	22.83
	12H	21.19	22.01	21.67	22.48	22.95	21.19	22.01	21.67	22.48	22.95
8H	4H	20.49	21.40	20.95	21.85	22.31	20.49	21.40	20.95	21.85	22.31
	6H	21.25	22.01	21.74	22.49	22.97	21.25	22.01	21.74	22.49	22.97
	8H	21.54	22.22	22.05	22.73	23.21	21.54	22.22	22.05	22.73	23.21
	12H	21.79	22.40	22.30	22.88	23.44	21.79	22.40	22.30	22.88	23.44
12H	4H	20.53	21.35	21.01	21.83	22.30	20.53	21.35	21.01	21.83	22.30
	6H	21.31	21.99	21.82	22.50	22.98	21.31	21.99	21.82	22.50	22.98
	8H	21.66	22.27	22.17	22.76	23.31	21.66	22.27	22.17	22.76	23.31