

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866693

Luminaire Tested: PRLX-2001-L-927-32L-L-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866693
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-77)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-L-927-32L-L-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2399.2 lumens
Efficiency: N/A
Efficacy: 91.9 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.26
Luminous Opening: Circular (Dia: 1.58' x H: 0')
CIE Type: Direct

Input Watts (W): 26.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866693

CATALOG NUMBER: PRLX-2001-L-927-32L-L-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P866693

CATALOG NUMBER: PRLX-2001-L-927-32L-L-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95	93	92	90
2	104	98	92	88	102	96	91	87	92	88	85		89	86	83		87	84	81	80
3	97	88	82	76	94	87	81	76	84	79	75		81	77	73		79	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66		74	69	65		72	68	64	62
5	83	72	65	59	81	71	64	59	69	63	58		68	62	58		66	61	57	55
6	78	66	58	53	76	65	58	53	63	57	52		62	56	52		60	55	51	50
7	72	60	53	47	71	60	52	47	58	52	47		57	51	47		56	50	46	45
8	68	56	48	43	66	55	48	43	54	47	42		52	47	42		51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39		49	43	38		48	42	38	37
10	59	47	40	35	58	47	40	35	46	40	35		45	39	35		44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	6919
5°	6887
10°	6792
15°	6678
20°	6550
25°	6405
30°	6228
35°	6004
40°	5723
45°	5355
50°	4895
55°	3106
60°	1232
65°	471
70°	285
75°	310
80°	349
85°	389

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5355 cd/sqm

TEST NUMBER: P866693

CATALOG NUMBER: PRLX-2001-L-927-32L-L-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	118.8	5.0
10°-20°	332.5	13.9
20°-30°	488.7	20.4
30°-40°	561.6	23.4
40°-50°	533.6	22.2
50°-60°	295.9	12.3
60°-70°	46.2	1.9
70°-80°	15.5	0.6
80°-90°	6.4	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	940.1	39.2
0°-40°	1501.7	62.6
0°-60°	2331.1	97.2
0°-90°	2399.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2399.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1266	
5°	1255	119
15°	1180	333
25°	1062	489
35°	900	562
45°	693	534
55°	326	296
65°	36	46
75°	15	15
85°	6	6
90°	0	

TEST NUMBER: P866693

CATALOG NUMBER: PRLX-2001-L-927-32L-L-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	1265.7
2.5°	1263.7
5°	1254.9
7.5°	1241.7
10°	1223.6
12.5°	1203.7
15°	1179.9
17.5°	1153.8
20°	1125.9
22.5°	1095.7
25°	1061.8
27.5°	1026.2
30°	986.6
32.5°	944.3
35°	899.6
37.5°	852.3
40°	801.9
42.5°	749.4
45°	692.6
47.5°	637.5
50°	575.5
52.5°	469.8
55°	325.9
57.5°	198.2
60°	112.7
62.5°	66.9
65°	36.4
67.5°	19.9
70°	17.8
72.5°	16.3
75°	14.7
77.5°	13.2
80°	11.1
82.5°	8.8
85°	6.2
87.5°	3.1
90°	0.0



TEST NUMBER: P866693
 CATALOG NUMBER: PRLX-2001-L-927-32L-L-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.35	13.72	12.71	14.04	14.35	12.35	13.72	12.71	14.04	14.35
	3H	12.29	13.49	12.66	13.82	14.19	12.29	13.49	12.66	13.82	14.19
	4H	12.26	13.39	12.66	13.74	14.12	12.26	13.39	12.66	13.74	14.12
	6H	12.25	13.28	12.66	13.65	14.04	12.25	13.28	12.66	13.65	14.04
	8H	12.24	13.21	12.67	13.60	14.01	12.24	13.21	12.67	13.60	14.01
	12H	12.23	13.16	12.66	13.54	13.97	12.23	13.16	12.66	13.54	13.97
4H	2H	12.22	13.34	12.62	13.69	14.07	12.22	13.34	12.62	13.69	14.07
	3H	12.19	13.09	12.60	13.49	13.90	12.19	13.09	12.60	13.49	13.90
	4H	12.18	12.98	12.61	13.40	13.84	12.18	12.98	12.61	13.40	13.84
	6H	12.20	12.90	12.66	13.34	13.81	12.20	12.90	12.66	13.34	13.81
	8H	12.20	12.85	12.67	13.30	13.77	12.20	12.85	12.67	13.30	13.77
	12H	12.21	12.78	12.69	13.27	13.74	12.21	12.78	12.69	13.27	13.74
8H	4H	12.09	12.73	12.56	13.18	13.65	12.09	12.73	12.56	13.18	13.65
	6H	12.13	12.66	12.63	13.16	13.64	12.13	12.66	12.63	13.16	13.64
	8H	12.15	12.63	12.67	13.15	13.64	12.15	12.63	12.67	13.15	13.64
	12H	12.19	12.62	12.70	13.12	13.69	12.19	12.62	12.70	13.12	13.69
12H	4H	12.05	12.62	12.54	13.11	13.58	12.05	12.62	12.54	13.11	13.58
	6H	12.08	12.57	12.60	13.08	13.58	12.08	12.57	12.60	13.08	13.58
	8H	12.13	12.57	12.65	13.07	13.64	12.13	12.57	12.65	13.07	13.64