

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866707

Luminaire Tested: PRLX-2001-L-927-48L-G-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866707
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-62)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-L-927-48L-G-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS,
TAPERED DRUM WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 3
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2895.9 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 1.35 / 1.35 / 1.48
Luminous Opening: Circular (Dia: 1.58' x H: 0')
CIE Type: Direct

Input Watts (W): 37.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866707

CATALOG NUMBER: PRLX-2001-L-927-48L-G-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P866707

CATALOG NUMBER: PRLX-2001-L-927-48L-G-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90		93	90	88		89	87	85	83
2	98	90	83	77	96	88	81	76	84	79	74		81	76	72		78	74	71	68
3	89	78	70	63	87	77	69	63	74	67	62		71	65	60		68	64	59	57
4	81	69	60	53	79	68	59	53	65	58	52		63	56	51		61	55	51	48
5	75	62	52	45	73	60	52	45	58	51	45		56	49	44		54	48	44	42
6	69	55	46	39	67	54	46	39	52	45	39		51	44	39		49	43	38	36
7	64	50	41	35	62	49	41	34	47	40	34		46	39	34		45	38	34	32
8	59	45	37	31	58	45	36	31	43	36	30		42	35	30		41	35	30	28
9	55	42	33	28	54	41	33	27	40	32	27		39	32	27		38	31	27	25
10	52	38	30	25	50	38	30	25	37	30	25		36	29	25		35	29	24	23

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4932
5°	4950
10°	4949
15°	4956
20°	4984
25°	5039
30°	5121
35°	5246
40°	5387
45°	5447
50°	5405
55°	5252
60°	5052
65°	4824
70°	4565
75°	4288
80°	3992
85°	3569

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5447 cd/sqm

TEST NUMBER: P866707

CATALOG NUMBER: PRLX-2001-L-927-48L-G-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.8	3.0
10°-20°	247.5	8.5
20°-30°	385.8	13.3
30°-40°	492.4	17.0
40°-50°	542.0	18.7
50°-60°	492.4	17.0
60°-70°	369.4	12.8
70°-80°	215.9	7.5
80°-90°	64.6	2.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	719.1	24.8
0°-40°	1211.5	41.8
0°-60°	2245.9	77.6
0°-90°	2895.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2895.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	902	
5°	902	86
15°	876	248
25°	835	386
35°	786	492
45°	705	542
55°	551	492
65°	373	369
75°	203	216
85°	57	65
90°	0	

TEST NUMBER: P866707

CATALOG NUMBER: PRLX-2001-L-927-48L-G-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	902.1
2.5°	902.5
5°	902.1
7.5°	899.0
10°	891.5
12.5°	884.0
15°	875.7
17.5°	866.2
20°	856.7
22.5°	846.4
25°	835.4
27.5°	823.5
30°	811.3
32.5°	799.0
35°	786.0
37.5°	771.4
40°	754.8
42.5°	733.5
45°	704.6
47.5°	672.6
50°	635.5
52.5°	595.2
55°	551.0
57.5°	507.2
60°	462.1
62.5°	418.3
65°	372.9
67.5°	328.2
70°	285.6
72.5°	244.5
75°	203.0
77.5°	165.1
80°	126.8
82.5°	90.8
85°	56.9
87.5°	26.5
90°	0.0



TEST NUMBER: P866707
 CATALOG NUMBER: PRLX-2001-L-927-48L-G-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.02	19.70	18.39	20.01	20.33	18.02	19.70	18.39	20.01	20.33
	3H	19.80	21.31	20.17	21.64	22.00	19.80	21.31	20.17	21.64	22.00
	4H	20.48	21.91	20.88	22.26	22.63	20.48	21.91	20.88	22.26	22.63
	6H	21.01	22.34	21.42	22.71	23.10	21.01	22.34	21.42	22.71	23.10
	8H	21.20	22.47	21.62	22.86	23.25	21.20	22.47	21.62	22.86	23.25
	12H	21.32	22.54	21.75	22.92	23.35	21.32	22.54	21.75	22.92	23.35
4H	2H	18.65	20.08	19.05	20.43	20.80	18.65	20.08	19.05	20.43	20.80
	3H	20.65	21.86	21.06	22.25	22.65	20.65	21.86	21.06	22.25	22.65
	4H	21.47	22.56	21.90	22.97	23.41	21.47	22.56	21.90	22.97	23.41
	6H	22.14	23.10	22.59	23.54	23.99	22.14	23.10	22.59	23.54	23.99
	8H	22.38	23.27	22.84	23.71	24.18	22.38	23.27	22.84	23.71	24.18
	12H	22.56	23.36	23.03	23.84	24.30	22.56	23.36	23.03	23.84	24.30
8H	4H	21.80	22.70	22.26	23.14	23.60	21.80	22.70	22.26	23.14	23.60
	6H	22.60	23.35	23.10	23.84	24.31	22.60	23.35	23.10	23.84	24.31
	8H	22.92	23.59	23.43	24.09	24.58	22.92	23.59	23.43	24.09	24.58
	12H	23.18	23.77	23.68	24.26	24.82	23.18	23.77	23.68	24.26	24.82
12H	4H	21.84	22.65	22.32	23.13	23.59	21.84	22.65	22.32	23.13	23.59
	6H	22.67	23.34	23.18	23.85	24.33	22.67	23.34	23.18	23.85	24.33
	8H	23.05	23.64	23.55	24.13	24.69	23.05	23.64	23.55	24.13	24.69