

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867190

Luminaire Tested: PRLX-2004-L-927-133L-L-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867190
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-86)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-927-133L-L-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,
BELL WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 8
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6330.7 lumens
Efficiency: N/A
Efficacy: 56.6 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.98
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 111.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867190

CATALOG NUMBER: PRLX-2004-L-927-133L-L-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P867190

CATALOG NUMBER: PRLX-2004-L-927-133L-L-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	101	94	88	84	99	92	87	83	89	85	82	87	83	80	85	82	79	77
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	68	64	71	67	63	70	66	63	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53
9	72	62	56	51	71	62	55	51	61	55	51	60	55	51	59	54	51	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29954
5°	28979
10°	27462
15°	26270
20°	25227
25°	24244
30°	23148
35°	16216
40°	5102
45°	2474
50°	1844
55°	1780
60°	1659
65°	1535
70°	1431
75°	1336
80°	1256
85°	1160

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2474 cd/sqm

TEST NUMBER: P867190

CATALOG NUMBER: PRLX-2004-L-927-133L-L-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	546.6	8.6
10°-20°	1448.7	22.9
20°-30°	2049.0	32.4
30°-40°	1560.3	24.6
40°-50°	313.7	5.0
50°-60°	183.9	2.9
60°-70°	130.9	2.1
70°-80°	74.6	1.2
80°-90°	23.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4044.2	63.9
0°-40°	5604.5	88.5
0°-60°	6102.1	96.4
0°-90°	6330.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6330.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6071	
5°	5851	547
15°	5143	1449
25°	4453	2049
35°	2692	1560
45°	355	314
55°	207	184
65°	132	131
75°	70	75
85°	20	23
90°	0	

TEST NUMBER: P867190

CATALOG NUMBER: PRLX-2004-L-927-133L-L-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	6071.1
2.5°	6025.8
5°	5851.2
7.5°	5655.1
10°	5481.6
12.5°	5314.5
15°	5143.1
17.5°	4979.3
20°	4804.7
22.5°	4628.0
25°	4453.4
27.5°	4276.6
30°	4063.2
32.5°	3611.6
35°	2692.3
37.5°	1488.4
40°	792.2
42.5°	523.8
45°	354.6
47.5°	255.4
50°	240.3
52.5°	225.3
55°	206.9
57.5°	186.5
60°	168.1
62.5°	148.7
65°	131.5
67.5°	115.3
70°	99.2
72.5°	84.1
75°	70.1
77.5°	57.1
80°	44.2
82.5°	32.3
85°	20.5
87.5°	9.7
90°	0.0

TEST NUMBER: P867190
 CATALOG NUMBER: PRLX-2004-L-927-133L-L-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.79	9.84	9.15	10.15	10.46	8.79	9.84	9.15	10.15	10.46
	3H	10.35	11.28	10.73	11.61	11.98	10.35	11.28	10.73	11.61	11.98
	4H	10.94	11.80	11.35	12.16	12.54	10.94	11.80	11.35	12.16	12.54
	6H	11.40	12.18	11.81	12.56	12.96	11.40	12.18	11.81	12.56	12.96
	8H	11.55	12.29	11.99	12.69	13.10	11.55	12.29	11.99	12.69	13.10
	12H	11.65	12.36	12.09	12.74	13.18	11.65	12.36	12.09	12.74	13.18
4H	2H	9.25	10.11	9.66	10.46	10.85	9.25	10.11	9.66	10.46	10.85
	3H	11.02	11.73	11.44	12.14	12.54	11.02	11.73	11.44	12.14	12.54
	4H	11.74	12.37	12.18	12.79	13.24	11.74	12.37	12.18	12.79	13.24
	6H	12.33	12.87	12.79	13.32	13.79	12.33	12.87	12.79	13.32	13.79
	8H	12.53	13.03	13.00	13.48	13.96	12.53	13.03	13.00	13.48	13.96
	12H	12.67	13.11	13.16	13.60	14.07	12.67	13.11	13.16	13.60	14.07
8H	4H	11.96	12.46	12.43	12.91	13.39	11.96	12.46	12.43	12.91	13.39
	6H	12.68	13.09	13.19	13.59	14.07	12.68	13.09	13.19	13.59	14.07
	8H	12.97	13.33	13.50	13.85	14.35	12.97	13.33	13.50	13.85	14.35
	12H	13.21	13.52	13.73	14.02	14.60	13.21	13.52	13.73	14.02	14.60
12H	4H	11.96	12.40	12.45	12.89	13.36	11.96	12.40	12.45	12.89	13.36
	6H	12.72	13.08	13.25	13.60	14.10	12.72	13.08	13.25	13.60	14.10
	8H	13.07	13.38	13.59	13.88	14.46	13.07	13.38	13.59	13.88	14.46