

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866750

Luminaire Tested: PRLX-2001-L-930-15L-L-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866750  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-78)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-L-930-15L-L-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,  
TAPERED DRUM WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 1  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1240.0 lumens  
Efficiency: N/A  
Efficacy: 75.6 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.27  
Luminous Opening: Circular (Dia: 1.58' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 16.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866750

CATALOG NUMBER: PRLX-2001-L-930-15L-L-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866750

CATALOG NUMBER: PRLX-2001-L-930-15L-L-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94	93	91	90
2	104	97	92	87	101	95	91	86	92	88	84		89	86	83		86	83	81	79
3	96	88	81	76	94	86	80	75	83	78	74		81	76	73		78	75	71	69
4	89	79	72	66	87	78	71	66	75	70	65		73	68	64		71	67	63	61
5	83	72	64	58	81	71	63	58	69	62	57		67	61	57		65	60	56	54
6	77	65	57	52	75	64	57	52	63	56	51		61	55	51		60	54	50	49
7	72	60	52	46	70	59	51	46	57	51	46		56	50	46		55	49	45	44
8	67	55	47	42	65	54	47	42	53	46	41		52	46	41		51	45	41	39
9	63	50	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	39	35	58	46	39	35	45	39	34		44	38	34		44	38	34	33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3451
5°	3442
10°	3404
15°	3352
20°	3290
25°	3218
30°	3128
35°	3013
40°	2872
45°	2697
50°	2478
55°	1914
60°	925
65°	349
70°	137
75°	152
80°	173
85°	194

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2697 cd/sqm

TEST NUMBER: P866750

CATALOG NUMBER: PRLX-2001-L-930-15L-L-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	59.4	4.8
10°-20°	166.9	13.5
20°-30°	245.5	19.8
30°-40°	281.9	22.7
40°-50°	268.7	21.7
50°-60°	173.5	14.0
60°-70°	33.3	2.7
70°-80°	7.5	0.6
80°-90°	3.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	471.8	38.0
0°-40°	753.7	60.8
0°-60°	1195.9	96.4
0°-90°	1240.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1240.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	631	
5°	627	59
15°	592	167
25°	534	245
35°	451	282
45°	349	269
55°	201	173
65°	27	33
75°	7	8
85°	3	3
90°	0	

TEST NUMBER: P866750

CATALOG NUMBER: PRLX-2001-L-930-15L-L-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	631.3
2.5°	630.5
5°	627.2
7.5°	621.4
10°	613.2
12.5°	603.4
15°	592.3
17.5°	579.6
20°	565.5
22.5°	550.0
25°	533.5
27.5°	515.4
30°	495.5
32.5°	474.1
35°	451.4
37.5°	427.8
40°	402.5
42.5°	377.1
45°	348.9
47.5°	321.1
50°	291.4
52.5°	252.9
55°	200.8
57.5°	139.9
60°	84.6
62.5°	48.5
65°	27.0
67.5°	14.1
70°	8.6
72.5°	7.8
75°	7.2
77.5°	6.4
80°	5.5
82.5°	4.4
85°	3.1
87.5°	1.6
90°	0.0



TEST NUMBER: P866750  
 CATALOG NUMBER: PRLX-2001-L-930-15L-L-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.21	13.61	12.57	13.92	14.24	12.21	13.61	12.57	13.92	14.24
	3H	12.13	13.37	12.51	13.70	14.06	12.13	13.37	12.51	13.70	14.06
	4H	12.09	13.23	12.49	13.58	13.96	12.09	13.23	12.49	13.58	13.96
	6H	12.04	13.09	12.46	13.46	13.86	12.04	13.09	12.46	13.46	13.86
	8H	12.02	13.01	12.45	13.40	13.81	12.02	13.01	12.45	13.40	13.81
	12H	11.99	12.95	12.43	13.33	13.76	11.99	12.95	12.43	13.33	13.76
4H	2H	12.09	13.23	12.49	13.58	13.97	12.09	13.23	12.49	13.58	13.97
	3H	12.03	12.95	12.44	13.36	13.76	12.03	12.95	12.44	13.36	13.76
	4H	11.98	12.80	12.42	13.22	13.67	11.98	12.80	12.42	13.22	13.67
	6H	11.96	12.67	12.42	13.11	13.58	11.96	12.67	12.42	13.11	13.58
	8H	11.93	12.59	12.40	13.04	13.51	11.93	12.59	12.40	13.04	13.51
	12H	11.91	12.50	12.40	12.98	13.46	11.91	12.50	12.40	12.98	13.46
8H	4H	11.87	12.53	12.34	12.98	13.45	11.87	12.53	12.34	12.98	13.45
	6H	11.84	12.39	12.34	12.88	13.36	11.84	12.39	12.34	12.88	13.36
	8H	11.82	12.32	12.34	12.83	13.32	11.82	12.32	12.34	12.83	13.32
	12H	11.82	12.26	12.33	12.76	13.33	11.82	12.26	12.33	12.76	13.33
12H	4H	11.83	12.42	12.32	12.90	13.37	11.83	12.42	12.32	12.90	13.37
	6H	11.79	12.28	12.31	12.80	13.29	11.79	12.28	12.31	12.80	13.29
	8H	11.79	12.24	12.31	12.73	13.30	11.79	12.24	12.31	12.73	13.30