

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867198

Luminaire Tested: PRLX-2004-L-927-15L-L-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P867198  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-86)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-L-927-15L-L-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,  
BELL WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 1  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 715.8 lumens  
Efficiency: N/A  
Efficacy: 43.6 lumens/watt  
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.98  
Luminous Opening: Circular (Dia: 1.67' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 16.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P867198

CATALOG NUMBER: PRLX-2004-L-927-15L-L-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P867198

CATALOG NUMBER: PRLX-2004-L-927-15L-L-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100		100	98	97		96	95	94	92
2	107	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	101	94	88	84	99	92	87	83	89	85	82		87	83	80		85	82	79	77
4	95	87	81	76	93	86	80	76	83	79	75		81	77	74		79	76	73	71
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	68	64		71	67	63		70	66	63	61
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66	62	58	57
8	76	66	60	55	75	65	59	55	64	59	55		63	58	55		62	58	54	53
9	72	62	56	51	71	62	55	51	61	55	51		60	55	51		59	54	51	49
10	69	58	52	48	68	58	52	48	57	52	48		56	51	48		56	51	48	46

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3387
5°	3277
10°	3105
15°	2970
20°	2852
25°	2741
30°	2617
35°	1833
40°	577
45°	280
50°	209
55°	201
60°	187
65°	174
70°	162
75°	151
80°	142
85°	130

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 280 cd/sqm

TEST NUMBER: P867198

CATALOG NUMBER: PRLX-2004-L-927-15L-L-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	61.8	8.6
10°-20°	163.8	22.9
20°-30°	231.7	32.4
30°-40°	176.4	24.6
40°-50°	35.5	5.0
50°-60°	20.8	2.9
60°-70°	14.8	2.1
70°-80°	8.4	1.2
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	457.3	63.9
0°-40°	633.7	88.5
0°-60°	690.0	96.4
0°-90°	715.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	715.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	686	
5°	662	62
15°	582	164
25°	504	232
35°	304	176
45°	40	35
55°	23	21
65°	15	15
75°	8	8
85°	2	3
90°	0	

TEST NUMBER: P867198

CATALOG NUMBER: PRLX-2004-L-927-15L-L-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	686.4
2.5°	681.3
5°	661.6
7.5°	639.4
10°	619.8
12.5°	600.9
15°	581.5
17.5°	563.0
20°	543.2
22.5°	523.3
25°	503.5
27.5°	483.5
30°	459.4
32.5°	408.4
35°	304.4
37.5°	168.3
40°	89.6
42.5°	59.2
45°	40.1
47.5°	28.9
50°	27.2
52.5°	25.5
55°	23.4
57.5°	21.1
60°	19.0
62.5°	16.8
65°	14.9
67.5°	13.0
70°	11.2
72.5°	9.5
75°	7.9
77.5°	6.5
80°	5.0
82.5°	3.7
85°	2.3
87.5°	1.1
90°	0.0

TEST NUMBER: P867198  
 CATALOG NUMBER: PRLX-2004-L-927-15L-L-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.22	2.27	1.58	2.58	2.89	1.22	2.27	1.58	2.58	2.89
	3H	2.77	3.70	3.15	4.03	4.40	2.77	3.70	3.15	4.03	4.40
	4H	3.36	4.22	3.77	4.58	4.96	3.36	4.22	3.77	4.58	4.96
	6H	3.82	4.61	4.24	4.99	5.38	3.82	4.61	4.24	4.99	5.38
	8H	3.98	4.72	4.42	5.12	5.52	3.98	4.72	4.42	5.12	5.52
	12H	4.08	4.79	4.52	5.17	5.61	4.08	4.79	4.52	5.17	5.61
4H	2H	1.68	2.54	2.09	2.90	3.28	1.68	2.54	2.09	2.90	3.28
	3H	3.45	4.15	3.86	4.56	4.97	3.45	4.15	3.86	4.56	4.97
	4H	4.16	4.79	4.60	5.21	5.66	4.16	4.79	4.60	5.21	5.66
	6H	4.75	5.29	5.22	5.74	6.22	4.75	5.29	5.22	5.74	6.22
	8H	4.96	5.46	5.43	5.91	6.39	4.96	5.46	5.43	5.91	6.39
	12H	5.10	5.54	5.59	6.03	6.51	5.10	5.54	5.59	6.03	6.51
8H	4H	4.38	4.89	4.86	5.34	5.81	4.38	4.89	4.86	5.34	5.81
	6H	5.11	5.52	5.62	6.02	6.50	5.11	5.52	5.62	6.02	6.50
	8H	5.41	5.77	5.94	6.29	6.78	5.41	5.77	5.94	6.29	6.78
	12H	5.65	5.95	6.17	6.45	7.03	5.65	5.95	6.17	6.45	7.03
12H	4H	4.38	4.82	4.87	5.31	5.79	4.38	4.82	4.87	5.31	5.79
	6H	5.15	5.51	5.68	6.03	6.53	5.15	5.51	5.68	6.03	6.53
	8H	5.51	5.82	6.03	6.32	6.89	5.51	5.82	6.03	6.32	6.89