

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866772

Luminaire Tested: PRLX-2001-L-930-67L-L-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866772
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-79)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-L-930-67L-L-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 4
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4994.3 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.27
Luminous Opening: Circular (Dia: 1.58' x H: 0')
CIE Type: Direct

Input Watts (W): 50.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866772

CATALOG NUMBER: PRLX-2001-L-930-67L-L-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P866772

CATALOG NUMBER: PRLX-2001-L-930-67L-L-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	105	103	109	106	104	101	102	100	98		98	97	95		95	94	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	82	77	95	87	81	77	84	79	75		82	78	74		80	76	73	71
4	90	80	73	68	88	79	73	67	77	71	67		75	70	66		73	68	65	63
5	84	73	66	60	82	72	65	60	70	64	59		68	63	59		66	62	58	56
6	78	67	59	53	76	66	58	53	64	58	53		62	57	52		61	56	52	50
7	73	61	53	48	71	60	53	48	59	52	48		57	52	47		56	51	47	45
8	68	56	48	43	67	55	48	43	54	48	43		53	47	43		52	47	43	41
9	64	52	44	39	62	51	44	39	50	44	39		49	43	39		48	43	39	37
10	60	48	41	36	59	47	41	36	46	40	36		46	40	36		45	39	35	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	14489
5°	14448
10°	14289
15°	14086
20°	13844
25°	13565
30°	13194
35°	12719
40°	12107
45°	11327
50°	10366
55°	6576
60°	2282
65°	574
70°	101
75°	108
80°	126
85°	144

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11327 cd/sqm

TEST NUMBER: P866772

CATALOG NUMBER: PRLX-2001-L-930-67L-L-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	249.4	5.0
10°-20°	701.4	14.0
20°-30°	1034.4	20.7
30°-40°	1189.5	23.8
40°-50°	1127.7	22.6
50°-60°	618.6	12.4
60°-70°	65.5	1.3
70°-80°	5.4	0.1
80°-90°	2.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1985.3	39.8
0°-40°	3174.7	63.6
0°-60°	4921.0	98.5
0°-90°	4994.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4994.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2650	
5°	2633	249
15°	2489	701
25°	2249	1034
35°	1906	1189
45°	1465	1128
55°	690	619
65°	44	65
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P866772

CATALOG NUMBER: PRLX-2001-L-930-67L-L-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	2650.3
2.5°	2647.4
5°	2632.7
7.5°	2607.1
10°	2574.1
12.5°	2534.8
15°	2488.8
17.5°	2437.0
20°	2379.6
22.5°	2317.0
25°	2248.8
27.5°	2172.6
30°	2090.1
32.5°	2001.4
35°	1905.8
37.5°	1804.0
40°	1696.5
42.5°	1583.9
45°	1465.1
47.5°	1343.9
50°	1218.8
52.5°	1001.5
55°	689.9
57.5°	394.7
60°	208.7
62.5°	108.6
65°	44.4
67.5°	8.5
70°	6.3
72.5°	5.7
75°	5.1
77.5°	4.5
80°	4.0
82.5°	3.4
85°	2.3
87.5°	1.1
90°	0.0



TEST NUMBER: P866772
 CATALOG NUMBER: PRLX-2001-L-930-67L-L-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.59	15.95	14.95	16.26	16.57	14.59	15.95	14.95	16.26	16.57
	3H	14.46	15.65	14.84	15.98	16.35	14.46	15.65	14.84	15.98	16.35
	4H	14.39	15.50	14.80	15.85	16.23	14.39	15.50	14.80	15.85	16.23
	6H	14.32	15.33	14.73	15.70	16.09	14.32	15.33	14.73	15.70	16.09
	8H	14.28	15.23	14.71	15.63	16.03	14.28	15.23	14.71	15.63	16.03
	12H	14.24	15.15	14.67	15.53	15.96	14.24	15.15	14.67	15.53	15.96
4H	2H	14.42	15.52	14.82	15.87	16.26	14.42	15.52	14.82	15.87	16.26
	3H	14.30	15.18	14.71	15.58	15.99	14.30	15.18	14.71	15.58	15.99
	4H	14.21	15.00	14.65	15.42	15.86	14.21	15.00	14.65	15.42	15.86
	6H	14.13	14.81	14.60	15.25	15.72	14.13	14.81	14.60	15.25	15.72
	8H	14.08	14.71	14.55	15.15	15.63	14.08	14.71	14.55	15.15	15.63
	12H	14.03	14.59	14.52	15.07	15.55	14.03	14.59	14.52	15.07	15.55
8H	4H	14.07	14.70	14.54	15.15	15.62	14.07	14.70	14.54	15.15	15.62
	6H	13.97	14.49	14.47	14.98	15.47	13.97	14.49	14.47	14.98	15.47
	8H	13.90	14.37	14.42	14.89	15.38	13.90	14.37	14.42	14.89	15.38
	12H	13.85	14.28	14.37	14.77	15.34	13.85	14.28	14.37	14.77	15.34
12H	4H	14.02	14.58	14.51	15.07	15.54	14.02	14.58	14.51	15.07	15.54
	6H	13.90	14.37	14.42	14.89	15.38	13.90	14.37	14.42	14.89	15.38
	8H	13.85	14.28	14.36	14.77	15.34	13.85	14.28	14.36	14.77	15.34