

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867239

Luminaire Tested: PRLX-2004-L-930-100L-L-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867239
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-84)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-930-100L-L-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS, BELL WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 6
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9196.2 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.05
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 79.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867239

CATALOG NUMBER: PRLX-2004-L-930-100L-L-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P867239

CATALOG NUMBER: PRLX-2004-L-930-100L-L-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	103	100	108	105	101	98	100	98	95		97	94	92		93	91	90	88
2	103	96	90	85	100	94	89	84	91	86	82		87	84	81		85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	72		80	75	71		77	73	70	68
4	89	79	71	66	87	77	70	65	75	69	64		73	68	63		71	66	63	61
5	83	72	64	59	81	71	64	58	69	63	58		67	61	57		65	60	57	55
6	78	66	58	53	76	65	58	53	63	57	52		62	56	52		60	55	51	50
7	73	61	53	48	71	60	53	48	59	52	48		57	52	47		56	51	47	45
8	68	57	49	44	67	56	49	44	55	48	44		53	48	43		52	47	43	41
9	64	53	45	40	63	52	45	40	51	45	40		50	44	40		49	44	40	38
10	61	49	42	37	60	49	42	37	48	41	37		47	41	37		46	41	37	35

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	29021
5°	28531
10°	27541
15°	26852
20°	26255
25°	25689
30°	24878
35°	20369
40°	11828
45°	8945
50°	8129
55°	7991
60°	7706
65°	7398
70°	7105
75°	6794
80°	6507
85°	6238

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8945 cd/sqm

TEST NUMBER: P867239

CATALOG NUMBER: PRLX-2004-L-930-100L-L-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	541.0	5.9
10°-20°	1482.4	16.1
20°-30°	2170.8	23.6
30°-40°	2018.4	21.9
40°-50°	1028.3	11.2
50°-60°	827.3	9.0
60°-70°	628.1	6.8
70°-80°	378.3	4.1
80°-90°	121.6	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4194.2	45.6
0°-40°	6212.6	67.6
0°-60°	8068.2	87.7
0°-90°	9196.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9196.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5882	
5°	5761	541
15°	5257	1482
25°	4719	2171
35°	3382	2018
45°	1282	1028
55°	929	827
65°	634	628
75°	356	378
85°	110	122
90°	0	

TEST NUMBER: P867239

CATALOG NUMBER: PRLX-2004-L-930-100L-L-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	5882.1
2.5°	5864.9
5°	5760.7
7.5°	5621.2
10°	5497.2
12.5°	5379.3
15°	5257.0
17.5°	5133.1
20°	5000.5
22.5°	4866.2
25°	4718.9
27.5°	4564.0
30°	4366.8
32.5°	4042.2
35°	3381.9
37.5°	2538.1
40°	1836.4
42.5°	1476.5
45°	1282.0
47.5°	1145.1
50°	1059.0
52.5°	997.0
55°	929.0
57.5°	853.2
60°	780.9
62.5°	706.0
65°	633.7
67.5°	562.2
70°	492.5
72.5°	424.5
75°	356.4
77.5°	292.7
80°	229.0
82.5°	169.6
85°	110.2
87.5°	52.5
90°	0.0



TEST NUMBER: P867239
 CATALOG NUMBER: PRLX-2004-L-930-100L-L-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.68	19.04	18.05	19.35	19.66	17.68	19.04	18.05	19.35	19.66
	3H	19.48	20.69	19.86	21.02	21.39	19.48	20.69	19.86	21.02	21.39
	4H	20.19	21.32	20.59	21.67	22.06	20.19	21.32	20.59	21.67	22.06
	6H	20.75	21.79	21.16	22.16	22.56	20.75	21.79	21.16	22.16	22.56
	8H	20.95	21.94	21.38	22.33	22.74	20.95	21.94	21.38	22.33	22.74
	12H	21.09	22.04	21.52	22.43	22.86	21.09	22.04	21.52	22.43	22.86
4H	2H	18.27	19.40	18.67	19.75	20.14	18.27	19.40	18.67	19.75	20.14
	3H	20.29	21.23	20.70	21.64	22.04	20.29	21.23	20.70	21.64	22.04
	4H	21.13	21.98	21.56	22.40	22.84	21.13	21.98	21.56	22.40	22.84
	6H	21.83	22.57	22.29	23.01	23.47	21.83	22.57	22.29	23.01	23.47
	8H	22.08	22.77	22.55	23.22	23.69	22.08	22.77	22.55	23.22	23.69
	12H	22.28	22.89	22.76	23.37	23.85	22.28	22.89	22.76	23.37	23.85
8H	4H	21.43	22.12	21.90	22.57	23.04	21.43	22.12	21.90	22.57	23.04
	6H	22.28	22.84	22.78	23.34	23.82	22.28	22.84	22.78	23.34	23.82
	8H	22.62	23.13	23.14	23.64	24.13	22.62	23.13	23.14	23.64	24.13
	12H	22.92	23.36	23.43	23.86	24.43	22.92	23.36	23.43	23.86	24.43
12H	4H	21.46	22.07	21.95	22.56	23.03	21.46	22.07	21.95	22.56	23.03
	6H	22.34	22.85	22.86	23.36	23.85	22.34	22.85	22.86	23.36	23.85
	8H	22.75	23.20	23.27	23.69	24.26	22.75	23.20	23.27	23.69	24.26