

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866813

Luminaire Tested: PRLX-2001-L-935-15L-L-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866813
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-77)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Pentalux
Catalog Number: PRLX-2001-L-935-15L-L-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1250.8 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.26
Luminous Opening: Circular (Dia: 1.58' x H: 0')
CIE Type: Direct

Input Watts (W): 16.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866813

CATALOG NUMBER: PRLX-2001-L-935-15L-L-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P866813

CATALOG NUMBER: PRLX-2001-L-935-15L-L-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	94		95	93	92	90
2	104	98	92	88	102	96	91	87	92	88	85		89	86	83		87	84	81	80
3	97	88	82	76	94	87	81	76	84	79	75		81	77	73		79	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66		74	69	65		72	68	64	62
5	83	72	65	59	81	71	64	59	69	63	58		68	62	58		66	61	57	55
6	78	66	58	53	76	65	58	53	63	57	52		62	56	52		60	55	51	50
7	72	60	53	47	71	60	52	47	58	52	47		57	51	47		56	50	46	45
8	68	56	48	43	66	55	48	43	54	47	42		52	47	42		51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39		49	43	38		48	42	38	37
10	59	47	40	35	58	47	40	35	46	40	35		45	39	35		44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3608
5°	3590
10°	3541
15°	3481
20°	3415
25°	3339
30°	3247
35°	3130
40°	2983
45°	2791
50°	2551
55°	1619
60°	642
65°	246
70°	149
75°	163
80°	183
85°	201

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2791 cd/sqm

TEST NUMBER: P866813

CATALOG NUMBER: PRLX-2001-L-935-15L-L-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.9	5.0
10°-20°	173.3	13.9
20°-30°	254.8	20.4
30°-40°	292.8	23.4
40°-50°	278.2	22.2
50°-60°	154.2	12.3
60°-70°	24.1	1.9
70°-80°	8.1	0.6
80°-90°	3.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	490.1	39.2
0°-40°	782.9	62.6
0°-60°	1215.3	97.2
0°-90°	1250.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1250.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	660	
5°	654	62
15°	615	173
25°	554	255
35°	469	293
45°	361	278
55°	170	154
65°	19	24
75°	8	8
85°	3	3
90°	0	

TEST NUMBER: P866813

CATALOG NUMBER: PRLX-2001-L-935-15L-L-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	659.9
2.5°	658.8
5°	654.2
7.5°	647.3
10°	637.9
12.5°	627.5
15°	615.1
17.5°	601.5
20°	587.0
22.5°	571.2
25°	553.6
27.5°	535.0
30°	514.4
32.5°	492.3
35°	469.0
37.5°	444.3
40°	418.0
42.5°	390.7
45°	361.0
47.5°	332.4
50°	300.0
52.5°	244.9
55°	169.9
57.5°	103.3
60°	58.7
62.5°	34.9
65°	19.0
67.5°	10.4
70°	9.3
72.5°	8.5
75°	7.7
77.5°	6.9
80°	5.8
82.5°	4.6
85°	3.2
87.5°	1.6
90°	0.0



TEST NUMBER: P866813
 CATALOG NUMBER: PRLX-2001-L-935-15L-L-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.08	11.46	10.45	11.77	12.09	10.08	11.46	10.45	11.77	12.09
	3H	10.02	11.23	10.40	11.56	11.92	10.02	11.23	10.40	11.56	11.92
	4H	10.00	11.12	10.40	11.47	11.85	10.00	11.12	10.40	11.47	11.85
	6H	9.98	11.01	10.40	11.38	11.78	9.98	11.01	10.40	11.38	11.78
	8H	9.97	10.95	10.40	11.34	11.75	9.97	10.95	10.40	11.34	11.75
	12H	9.96	10.89	10.39	11.28	11.71	9.96	10.89	10.39	11.28	11.71
4H	2H	9.95	11.08	10.35	11.43	11.81	9.95	11.08	10.35	11.43	11.81
	3H	9.92	10.83	10.33	11.23	11.63	9.92	10.83	10.33	11.23	11.63
	4H	9.91	10.72	10.35	11.14	11.58	9.91	10.72	10.35	11.14	11.58
	6H	9.94	10.63	10.40	11.08	11.54	9.94	10.63	10.40	11.08	11.54
	8H	9.94	10.59	10.41	11.03	11.50	9.94	10.59	10.41	11.03	11.50
	12H	9.94	10.52	10.43	11.00	11.48	9.94	10.52	10.43	11.00	11.48
8H	4H	9.82	10.47	10.29	10.92	11.39	9.82	10.47	10.29	10.92	11.39
	6H	9.86	10.40	10.37	10.90	11.38	9.86	10.40	10.37	10.90	11.38
	8H	9.88	10.37	10.41	10.89	11.38	9.88	10.37	10.41	10.89	11.38
	12H	9.92	10.36	10.44	10.85	11.42	9.92	10.36	10.44	10.85	11.42
12H	4H	9.79	10.36	10.27	10.84	11.32	9.79	10.36	10.27	10.84	11.32
	6H	9.82	10.31	10.34	10.82	11.31	9.82	10.31	10.34	10.82	11.31
	8H	9.87	10.31	10.39	10.80	11.37	9.87	10.31	10.39	10.80	11.37