

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866814

Luminaire Tested: PRLX-2001-L-935-15L-L-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866814
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-78)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-L-935-15L-L-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1281.2 lumens
Efficiency: N/A
Efficacy: 78.1 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.27
Luminous Opening: Circular (Dia: 1.58' x H: 0')
CIE Type: Direct

Input Watts (W): 16.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866814

CATALOG NUMBER: PRLX-2001-L-935-15L-L-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P866814

CATALOG NUMBER: PRLX-2001-L-935-15L-L-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90
2	104	97	92	87	101	95	91	86	92	88	84	89	86	83	86	83	81	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	71	69
4	89	79	72	66	87	78	71	66	75	70	65	73	68	64	71	67	63	61
5	83	72	64	58	81	71	63	58	69	62	57	67	61	57	65	60	56	54
6	77	65	57	52	75	64	57	52	63	56	51	61	55	51	60	54	50	49
7	72	60	52	46	70	59	51	46	57	51	46	56	50	46	55	49	45	44
8	67	55	47	42	65	54	47	42	53	46	41	52	46	41	51	45	41	39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36
10	59	47	39	35	58	46	39	35	45	39	34	44	38	34	44	38	34	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3566
5°	3556
10°	3517
15°	3464
20°	3399
25°	3325
30°	3231
35°	3113
40°	2968
45°	2787
50°	2561
55°	1978
60°	956
65°	361
70°	142
75°	156
80°	179
85°	201

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2787 cd/sqm

TEST NUMBER: P866814

CATALOG NUMBER: PRLX-2001-L-935-15L-L-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.4	4.8
10°-20°	172.4	13.5
20°-30°	253.6	19.8
30°-40°	291.3	22.7
40°-50°	277.7	21.7
50°-60°	179.3	14.0
60°-70°	34.4	2.7
70°-80°	7.8	0.6
80°-90°	3.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	487.4	38.0
0°-40°	778.7	60.8
0°-60°	1235.6	96.4
0°-90°	1281.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1281.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	652	
5°	648	61
15°	612	172
25°	551	254
35°	466	291
45°	360	278
55°	208	179
65°	28	34
75°	7	8
85°	3	3
90°	0	

TEST NUMBER: P866814

CATALOG NUMBER: PRLX-2001-L-935-15L-L-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	652.3
2.5°	651.5
5°	648.0
7.5°	642.1
10°	633.6
12.5°	623.5
15°	612.0
17.5°	598.8
20°	584.3
22.5°	568.2
25°	551.3
27.5°	532.5
30°	511.9
32.5°	489.8
35°	466.4
37.5°	442.0
40°	415.9
42.5°	389.6
45°	360.5
47.5°	331.8
50°	301.1
52.5°	261.4
55°	207.5
57.5°	144.6
60°	87.4
62.5°	50.1
65°	27.9
67.5°	14.5
70°	8.9
72.5°	8.1
75°	7.4
77.5°	6.6
80°	5.7
82.5°	4.6
85°	3.2
87.5°	1.6
90°	0.0



TEST NUMBER: P866814
 CATALOG NUMBER: PRLX-2001-L-935-15L-L-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.32	13.73	12.69	14.04	14.35	12.32	13.73	12.69	14.04	14.35
	3H	12.25	13.48	12.63	13.81	14.17	12.25	13.48	12.63	13.81	14.17
	4H	12.20	13.35	12.60	13.70	14.08	12.20	13.35	12.60	13.70	14.08
	6H	12.16	13.21	12.57	13.58	13.97	12.16	13.21	12.57	13.58	13.97
	8H	12.13	13.13	12.56	13.52	13.92	12.13	13.13	12.56	13.52	13.92
	12H	12.11	13.06	12.54	13.44	13.87	12.11	13.06	12.54	13.44	13.87
4H	2H	12.20	13.35	12.61	13.70	14.08	12.20	13.35	12.61	13.70	14.08
	3H	12.14	13.07	12.56	13.47	13.87	12.14	13.07	12.56	13.47	13.87
	4H	12.10	12.92	12.53	13.34	13.78	12.10	12.92	12.53	13.34	13.78
	6H	12.07	12.78	12.53	13.23	13.69	12.07	12.78	12.53	13.23	13.69
	8H	12.05	12.71	12.51	13.16	13.63	12.05	12.71	12.51	13.16	13.63
	12H	12.03	12.62	12.51	13.10	13.57	12.03	12.62	12.51	13.10	13.57
8H	4H	11.99	12.65	12.46	13.10	13.57	11.99	12.65	12.46	13.10	13.57
	6H	11.96	12.50	12.46	13.00	13.48	11.96	12.50	12.46	13.00	13.48
	8H	11.94	12.43	12.46	12.95	13.44	11.94	12.43	12.46	12.95	13.44
	12H	11.94	12.38	12.45	12.88	13.44	11.94	12.38	12.45	12.88	13.44
12H	4H	11.95	12.53	12.43	13.02	13.49	11.95	12.53	12.43	13.02	13.49
	6H	11.90	12.40	12.42	12.91	13.40	11.90	12.40	12.42	12.91	13.40
	8H	11.91	12.35	12.42	12.85	13.42	11.91	12.35	12.42	12.85	13.42