

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866815

Luminaire Tested: PRLX-2001-L-935-15L-L-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866815
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-76)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-L-935-15L-L-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1517.0 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.3
Luminous Opening: Circular (Dia: 1.58' x H: 0')
CIE Type: Direct

Input Watts (W): 16.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866815

CATALOG NUMBER: PRLX-2001-L-935-15L-L-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P866815

CATALOG NUMBER: PRLX-2001-L-935-15L-L-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	101	99	101	98	96	97	95	93	93	91	90	88
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52
6	75	63	55	50	74	63	55	49	61	54	49	59	53	49	58	52	48	46
7	70	58	50	44	69	57	50	44	56	49	44	54	48	44	53	47	43	41
8	66	53	45	40	64	52	45	40	51	44	40	50	44	39	49	43	39	37
9	61	49	41	36	60	48	41	36	47	41	36	46	40	36	45	40	36	34
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	32	31

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	3944
5°	3930
10°	3890
15°	3842
20°	3788
25°	3725
30°	3647
35°	3546
40°	3416
45°	3246
50°	3029
55°	2127
60°	1152
65°	784
70°	713
75°	756
80°	815
85°	872

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3246 cd/sqm

TEST NUMBER: P866815

CATALOG NUMBER: PRLX-2001-L-935-15L-L-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.9	4.5
10°-20°	191.4	12.6
20°-30°	284.3	18.7
30°-40°	332.0	21.9
40°-50°	323.2	21.3
50°-60°	201.1	13.3
60°-70°	64.8	4.3
70°-80°	37.6	2.5
80°-90°	14.7	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	543.6	35.8
0°-40°	875.6	57.7
0°-60°	1399.9	92.3
0°-90°	1517.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1517.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	721	
5°	716	68
15°	679	191
25°	618	284
35°	531	332
45°	420	323
55°	223	201
65°	61	65
75°	36	38
85°	14	15
90°	0	

TEST NUMBER: P866815

CATALOG NUMBER: PRLX-2001-L-935-15L-L-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	721.4
2.5°	720.6
5°	716.2
7.5°	709.4
10°	700.7
12.5°	690.7
15°	678.9
17.5°	665.9
20°	651.1
22.5°	635.5
25°	617.6
27.5°	598.4
30°	577.7
32.5°	555.7
35°	531.3
37.5°	506.4
40°	478.7
42.5°	450.5
45°	419.9
47.5°	388.0
50°	356.2
52.5°	300.7
55°	223.2
57.5°	152.1
60°	105.4
62.5°	78.7
65°	60.6
67.5°	48.5
70°	44.6
72.5°	40.3
75°	35.8
77.5°	31.1
80°	25.9
82.5°	20.2
85°	13.9
87.5°	7.0
90°	0.0



TEST NUMBER: P866815
 CATALOG NUMBER: PRLX-2001-L-935-15L-L-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.07	13.52	12.44	13.84	14.15	12.07	13.52	12.44	13.84	14.15
	3H	12.55	13.84	12.93	14.17	14.53	12.55	13.84	12.93	14.17	14.53
	4H	12.87	14.07	13.27	14.42	14.80	12.87	14.07	13.27	14.42	14.80
	6H	13.22	14.33	13.64	14.70	15.09	13.22	14.33	13.64	14.70	15.09
	8H	13.38	14.43	13.80	14.82	15.22	13.38	14.43	13.80	14.82	15.22
	12H	13.50	14.51	13.93	14.89	15.32	13.50	14.51	13.93	14.89	15.32
4H	2H	12.15	13.35	12.55	13.70	14.08	12.15	13.35	12.55	13.70	14.08
	3H	12.85	13.83	13.26	14.23	14.63	12.85	13.83	13.26	14.23	14.63
	4H	13.32	14.20	13.75	14.61	15.05	13.32	14.20	13.75	14.61	15.05
	6H	13.84	14.61	14.30	15.05	15.51	13.84	14.61	14.30	15.05	15.51
	8H	14.07	14.79	14.54	15.23	15.70	14.07	14.79	14.54	15.23	15.70
	12H	14.27	14.91	14.76	15.39	15.86	14.27	14.91	14.76	15.39	15.86
8H	4H	13.48	14.20	13.95	14.64	15.11	13.48	14.20	13.95	14.64	15.11
	6H	14.15	14.74	14.65	15.24	15.72	14.15	14.74	14.65	15.24	15.72
	8H	14.48	15.01	14.99	15.52	16.01	14.48	15.01	14.99	15.52	16.01
	12H	14.78	15.26	15.29	15.75	16.32	14.78	15.26	15.29	15.75	16.32
12H	4H	13.50	14.14	13.98	14.62	15.09	13.50	14.14	13.98	14.62	15.09
	6H	14.20	14.74	14.72	15.25	15.74	14.20	14.74	14.72	15.25	15.74
	8H	14.59	15.07	15.10	15.57	16.13	14.59	15.07	15.10	15.57	16.13