

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867262

Luminaire Tested: PRLX-2004-L-930-15L-L-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867262
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-86)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-930-15L-L-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,
BELL WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 765.9 lumens
Efficiency: N/A
Efficacy: 46.7 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.98
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 16.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867262

CATALOG NUMBER: PRLX-2004-L-930-15L-L-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P867262

CATALOG NUMBER: PRLX-2004-L-930-15L-L-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 113 | 110 | 107 | 104 | 110 | 108 | 105 | 103 | 103 | 101 | 100 | | 100 | 98 | 97 | | 96 | 95 | 94 | 92 |
| 2 | 107 | 101 | 97 | 93 | 104 | 99 | 95 | 92 | 96 | 93 | 90 | | 93 | 90 | 88 | | 90 | 88 | 86 | 84 |
| 3 | 101 | 94 | 88 | 84 | 99 | 92 | 87 | 83 | 89 | 85 | 82 | | 87 | 83 | 80 | | 85 | 82 | 79 | 77 |
| 4 | 95 | 87 | 81 | 76 | 93 | 86 | 80 | 76 | 83 | 79 | 75 | | 81 | 77 | 74 | | 79 | 76 | 73 | 71 |
| 5 | 90 | 81 | 74 | 70 | 88 | 80 | 74 | 69 | 78 | 73 | 69 | | 76 | 72 | 68 | | 75 | 71 | 68 | 66 |
| 6 | 85 | 75 | 69 | 64 | 83 | 74 | 68 | 64 | 73 | 68 | 64 | | 71 | 67 | 63 | | 70 | 66 | 63 | 61 |
| 7 | 80 | 70 | 64 | 59 | 79 | 70 | 64 | 59 | 68 | 63 | 59 | | 67 | 62 | 59 | | 66 | 62 | 58 | 57 |
| 8 | 76 | 66 | 60 | 55 | 75 | 65 | 59 | 55 | 64 | 59 | 55 | | 63 | 58 | 55 | | 62 | 58 | 54 | 53 |
| 9 | 72 | 62 | 56 | 51 | 71 | 62 | 55 | 51 | 61 | 55 | 51 | | 60 | 55 | 51 | | 59 | 54 | 51 | 49 |
| 10 | 69 | 58 | 52 | 48 | 68 | 58 | 52 | 48 | 57 | 52 | 48 | | 56 | 51 | 48 | | 56 | 51 | 48 | 46 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|------|
| | 0° |
| 0° | 3624 |
| 5° | 3506 |
| 10° | 3322 |
| 15° | 3178 |
| 20° | 3052 |
| 25° | 2933 |
| 30° | 2801 |
| 35° | 1962 |
| 40° | 617 |
| 45° | 299 |
| 50° | 223 |
| 55° | 215 |
| 60° | 200 |
| 65° | 186 |
| 70° | 173 |
| 75° | 162 |
| 80° | 151 |
| 85° | 142 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 299 cd/sqm

TEST NUMBER: P867262

CATALOG NUMBER: PRLX-2004-L-930-15L-L-X-X-GREY-X

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 66.1 | 8.6 |
| 10°-20° | 175.3 | 22.9 |
| 20°-30° | 247.9 | 32.4 |
| 30°-40° | 188.8 | 24.6 |
| 40°-50° | 38.0 | 5.0 |
| 50°-60° | 22.3 | 2.9 |
| 60°-70° | 15.8 | 2.1 |
| 70°-80° | 9.0 | 1.2 |
| 80°-90° | 2.8 | 0.4 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 489.3 | 63.9 |
| 0°-40° | 678.0 | 88.5 |
| 0°-60° | 738.3 | 96.4 |
| 0°-90° | 765.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 765.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 734 | |
| 5° | 708 | 66 |
| 15° | 622 | 175 |
| 25° | 539 | 248 |
| 35° | 326 | 189 |
| 45° | 43 | 38 |
| 55° | 25 | 22 |
| 65° | 16 | 16 |
| 75° | 8 | 9 |
| 85° | 2 | 3 |
| 90° | 0 | |

TEST NUMBER: P867262

CATALOG NUMBER: PRLX-2004-L-930-15L-L-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|-------|
| 0° | 734.5 |
| 2.5° | 729.0 |
| 5° | 707.9 |
| 7.5° | 684.1 |
| 10° | 663.1 |
| 12.5° | 642.9 |
| 15° | 622.2 |
| 17.5° | 602.4 |
| 20° | 581.3 |
| 22.5° | 559.9 |
| 25° | 538.8 |
| 27.5° | 517.4 |
| 30° | 491.6 |
| 32.5° | 436.9 |
| 35° | 325.7 |
| 37.5° | 180.1 |
| 40° | 95.8 |
| 42.5° | 63.4 |
| 45° | 42.9 |
| 47.5° | 30.9 |
| 50° | 29.1 |
| 52.5° | 27.3 |
| 55° | 25.0 |
| 57.5° | 22.6 |
| 60° | 20.3 |
| 62.5° | 18.0 |
| 65° | 15.9 |
| 67.5° | 14.0 |
| 70° | 12.0 |
| 72.5° | 10.2 |
| 75° | 8.5 |
| 77.5° | 6.9 |
| 80° | 5.3 |
| 82.5° | 3.9 |
| 85° | 2.5 |
| 87.5° | 1.2 |
| 90° | 0.0 |

TEST NUMBER: P867262
 CATALOG NUMBER: PRLX-2004-L-930-15L-L-X-X-GREY-X

CIE UGR TABLE:

| Reflectances: | | | | | | | | | | | |
|-----------------|------|------------------|------|------|------|------|----------------|------|------|------|------|
| Ceiling | | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 | 0.7 | 0.7 | 0.5 | 0.5 | 0.3 |
| Wall | | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 | 0.5 | 0.3 | 0.5 | 0.3 | 0.3 |
| Reference plane | | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 | 0.2 |
| Room dimensions | | Viewed crosswise | | | | | Viewed endwise | | | | |
| X=2H | Y=2H | 1.46 | 2.51 | 1.82 | 2.82 | 3.13 | 1.46 | 2.51 | 1.82 | 2.82 | 3.13 |
| | 3H | 3.02 | 3.95 | 3.40 | 4.28 | 4.65 | 3.02 | 3.95 | 3.40 | 4.28 | 4.65 |
| | 4H | 3.61 | 4.48 | 4.02 | 4.83 | 5.22 | 3.61 | 4.48 | 4.02 | 4.83 | 5.22 |
| | 6H | 4.06 | 4.85 | 4.48 | 5.23 | 5.62 | 4.06 | 4.85 | 4.48 | 5.23 | 5.62 |
| | 8H | 4.22 | 4.96 | 4.65 | 5.35 | 5.76 | 4.22 | 4.96 | 4.65 | 5.35 | 5.76 |
| | 12H | 4.32 | 5.03 | 4.75 | 5.41 | 5.84 | 4.32 | 5.03 | 4.75 | 5.41 | 5.84 |
| 4H | 2H | 1.92 | 2.78 | 2.32 | 3.13 | 3.52 | 1.92 | 2.78 | 2.32 | 3.13 | 3.52 |
| | 3H | 3.69 | 4.40 | 4.11 | 4.81 | 5.21 | 3.69 | 4.40 | 4.11 | 4.81 | 5.21 |
| | 4H | 4.41 | 5.04 | 4.85 | 5.46 | 5.91 | 4.41 | 5.04 | 4.85 | 5.46 | 5.91 |
| | 6H | 4.99 | 5.53 | 5.46 | 5.98 | 6.45 | 4.99 | 5.53 | 5.46 | 5.98 | 6.45 |
| | 8H | 5.19 | 5.69 | 5.66 | 6.14 | 6.62 | 5.19 | 5.69 | 5.66 | 6.14 | 6.62 |
| | 12H | 5.34 | 5.77 | 5.83 | 6.26 | 6.74 | 5.34 | 5.77 | 5.83 | 6.26 | 6.74 |
| 8H | 4H | 4.63 | 5.13 | 5.11 | 5.58 | 6.06 | 4.63 | 5.13 | 5.11 | 5.58 | 6.06 |
| | 6H | 5.35 | 5.75 | 5.85 | 6.25 | 6.73 | 5.35 | 5.75 | 5.85 | 6.25 | 6.73 |
| | 8H | 5.63 | 5.99 | 6.16 | 6.51 | 7.01 | 5.63 | 5.99 | 6.16 | 6.51 | 7.01 |
| | 12H | 5.87 | 6.18 | 6.39 | 6.68 | 7.26 | 5.87 | 6.18 | 6.39 | 6.68 | 7.26 |
| 12H | 4H | 4.63 | 5.07 | 5.12 | 5.56 | 6.03 | 4.63 | 5.07 | 5.12 | 5.56 | 6.03 |
| | 6H | 5.38 | 5.74 | 5.91 | 6.26 | 6.76 | 5.38 | 5.74 | 5.91 | 6.26 | 6.76 |
| | 8H | 5.73 | 6.04 | 6.25 | 6.54 | 7.12 | 5.73 | 6.04 | 6.25 | 6.54 | 7.12 |