

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866838

Luminaire Tested: PRLX-2001-L-935-67L-L-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866838
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-78)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-L-935-67L-L-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 4
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5588.4 lumens
Efficiency: N/A
Efficacy: 110.9 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.27
Luminous Opening: Circular (Dia: 1.58' x H: 0')
CIE Type: Direct

Input Watts (W): 50.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866838

CATALOG NUMBER: PRLX-2001-L-935-67L-L-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P866838

CATALOG NUMBER: PRLX-2001-L-935-67L-L-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94	93	91	90
2	104	97	92	87	101	95	91	86	92	88	84		89	86	83		86	83	81	79
3	96	88	81	76	94	86	80	75	83	78	74		81	76	73		78	75	71	69
4	89	79	72	66	87	78	71	66	75	70	65		73	68	64		71	67	63	61
5	83	72	64	58	81	71	63	58	69	62	57		67	61	57		65	60	56	54
6	77	65	57	52	75	64	57	52	63	56	51		61	55	51		60	54	50	49
7	72	60	52	46	70	59	51	46	57	51	46		56	50	46		55	49	45	44
8	67	55	47	42	65	54	47	42	53	46	41		52	46	41		51	45	41	39
9	63	50	43	38	61	50	43	38	49	42	38		48	42	37		47	41	37	36
10	59	47	39	35	58	46	39	35	45	39	34		44	38	34		44	38	34	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	15555
5°	15511
10°	15342
15°	15109
20°	14827
25°	14505
30°	14096
35°	13577
40°	12946
45°	12157
50°	11170
55°	8626
60°	4170
65°	1573
70°	620
75°	682
80°	778
85°	884

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 12157 cd/sqm

TEST NUMBER: P866838

CATALOG NUMBER: PRLX-2001-L-935-67L-L-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	267.8	4.8
10°-20°	752.1	13.5
20°-30°	1106.3	19.8
30°-40°	1270.5	22.7
40°-50°	1211.1	21.7
50°-60°	781.9	14.0
60°-70°	150.2	2.7
70°-80°	33.8	0.6
80°-90°	14.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2126.2	38.0
0°-40°	3396.7	60.8
0°-60°	5389.8	96.4
0°-90°	5588.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5588.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2845	
5°	2826	268
15°	2670	752
25°	2405	1106
35°	2034	1271
45°	1572	1211
55°	905	782
65°	122	150
75°	32	34
85°	14	15
90°	0	

TEST NUMBER: P866838

CATALOG NUMBER: PRLX-2001-L-935-67L-L-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	2845.3
2.5°	2841.8
5°	2826.5
7.5°	2800.7
10°	2763.7
12.5°	2719.6
15°	2669.6
17.5°	2612.0
20°	2548.6
22.5°	2478.6
25°	2404.6
27.5°	2322.9
30°	2233.0
32.5°	2136.6
35°	2034.4
37.5°	1928.0
40°	1814.0
42.5°	1699.4
45°	1572.5
47.5°	1447.3
50°	1313.4
52.5°	1140.0
55°	905.0
57.5°	630.5
60°	381.4
62.5°	218.6
65°	121.6
67.5°	63.5
70°	38.8
72.5°	35.3
75°	32.3
77.5°	28.8
80°	24.7
82.5°	20.0
85°	14.1
87.5°	7.1
90°	0.0



TEST NUMBER: P866838
 CATALOG NUMBER: PRLX-2001-L-935-67L-L-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.44	18.84	17.80	19.15	19.47	17.44	18.84	17.80	19.15	19.47
	3H	17.36	18.60	17.74	18.93	19.29	17.36	18.60	17.74	18.93	19.29
	4H	17.32	18.46	17.72	18.81	19.20	17.32	18.46	17.72	18.81	19.20
	6H	17.27	18.32	17.69	18.69	19.09	17.27	18.32	17.69	18.69	19.09
	8H	17.25	18.25	17.68	18.64	19.04	17.25	18.25	17.68	18.64	19.04
	12H	17.22	18.18	17.66	18.56	18.99	17.22	18.18	17.66	18.56	18.99
4H	2H	17.32	18.47	17.72	18.82	19.20	17.32	18.47	17.72	18.82	19.20
	3H	17.26	18.18	17.67	18.59	18.99	17.26	18.18	17.67	18.59	18.99
	4H	17.21	18.03	17.65	18.45	18.90	17.21	18.03	17.65	18.45	18.90
	6H	17.19	17.90	17.65	18.34	18.81	17.19	17.90	17.65	18.34	18.81
	8H	17.16	17.82	17.63	18.27	18.74	17.16	17.82	17.63	18.27	18.74
	12H	17.14	17.73	17.63	18.21	18.69	17.14	17.73	17.63	18.21	18.69
8H	4H	17.10	17.76	17.57	18.21	18.68	17.10	17.76	17.57	18.21	18.68
	6H	17.07	17.62	17.57	18.11	18.59	17.07	17.62	17.57	18.11	18.59
	8H	17.05	17.55	17.57	18.06	18.55	17.05	17.55	17.57	18.06	18.55
	12H	17.05	17.50	17.56	17.99	18.56	17.05	17.50	17.56	17.99	18.56
12H	4H	17.06	17.65	17.55	18.13	18.61	17.06	17.65	17.55	18.13	18.61
	6H	17.02	17.51	17.54	18.03	18.52	17.02	17.51	17.54	18.03	18.52
	8H	17.02	17.47	17.54	17.96	18.53	17.02	17.47	17.54	17.96	18.53