

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867273

Luminaire Tested: PRLX-2004-L-930-32L-G-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867273
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-930-32L-G-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS,
BELL WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 622.2 lumens
Efficiency: N/A
Efficacy: 23.8 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.17
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867273

CATALOG NUMBER: PRLX-2004-L-930-32L-G-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P867273

CATALOG NUMBER: PRLX-2004-L-930-32L-G-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	74		80	76	73	71
4	91	81	74	69	89	80	73	68	78	72	67		75	70	67		73	69	66	64
5	85	74	67	61	83	73	66	61	71	65	60		69	64	60		68	63	59	57
6	79	68	61	55	77	67	60	55	65	59	55		64	58	54		62	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49		59	53	49		58	53	49	47
8	69	58	50	45	68	57	50	45	56	50	45		55	49	45		54	49	45	43
9	65	54	46	42	64	53	46	42	52	46	41		51	45	41		50	45	41	39
10	62	50	43	38	60	49	43	38	48	42	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1808
5°	1810
10°	1805
15°	1787
20°	1759
25°	1722
30°	1643
35°	1477
40°	1262
45°	1009
50°	732
55°	450
60°	254
65°	216
70°	192
75°	173
80°	156
85°	142

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1009 cd/sqm

TEST NUMBER: P867273

CATALOG NUMBER: PRLX-2004-L-930-32L-G-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.7	5.6
10°-20°	98.6	15.8
20°-30°	145.1	23.3
30°-40°	152.3	24.5
40°-50°	111.2	17.9
50°-60°	49.0	7.9
60°-70°	18.7	3.0
70°-80°	9.7	1.6
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	278.4	44.7
0°-40°	430.7	69.2
0°-60°	590.9	95.0
0°-90°	622.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	622.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	366	
5°	366	35
15°	350	99
25°	316	145
35°	245	152
45°	145	111
55°	52	49
65°	18	19
75°	9	10
85°	2	3
90°	0	

TEST NUMBER: P867273

CATALOG NUMBER: PRLX-2004-L-930-32L-G-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	366.4
2.5°	366.1
5°	365.5
7.5°	363.6
10°	360.3
12.5°	355.6
15°	349.8
17.5°	343.1
20°	335.1
22.5°	326.5
25°	316.3
27.5°	304.7
30°	288.4
32.5°	268.5
35°	245.3
37.5°	221.2
40°	196.0
42.5°	170.3
45°	144.6
47.5°	119.2
50°	95.4
52.5°	73.0
55°	52.3
57.5°	35.4
60°	25.7
62.5°	21.8
65°	18.5
67.5°	15.8
70°	13.3
72.5°	11.1
75°	9.1
77.5°	7.2
80°	5.5
82.5°	4.1
85°	2.5
87.5°	1.1
90°	0.0

TEST NUMBER: P867273
 CATALOG NUMBER: PRLX-2004-L-930-32L-G-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.89	6.19	5.26	6.50	6.82	4.89	6.19	5.26	6.50	6.82
	3H	5.78	6.93	6.16	7.26	7.62	5.78	6.93	6.16	7.26	7.62
	4H	6.13	7.20	6.53	7.55	7.93	6.13	7.20	6.53	7.55	7.93
	6H	6.39	7.37	6.80	7.74	8.14	6.39	7.37	6.80	7.74	8.14
	8H	6.48	7.41	6.91	7.80	8.21	6.48	7.41	6.91	7.80	8.21
	12H	6.54	7.42	6.97	7.81	8.24	6.54	7.42	6.97	7.81	8.24
4H	2H	5.11	6.18	5.52	6.54	6.92	5.11	6.18	5.52	6.54	6.92
	3H	6.22	7.09	6.63	7.50	7.90	6.22	7.09	6.63	7.50	7.90
	4H	6.69	7.47	7.12	7.89	8.33	6.69	7.47	7.12	7.89	8.33
	6H	7.07	7.74	7.53	8.19	8.65	7.07	7.74	7.53	8.19	8.65
	8H	7.20	7.83	7.67	8.28	8.75	7.20	7.83	7.67	8.28	8.75
	12H	7.30	7.85	7.79	8.34	8.81	7.30	7.85	7.79	8.34	8.81
8H	4H	6.82	7.45	7.29	7.90	8.37	6.82	7.45	7.29	7.90	8.37
	6H	7.31	7.82	7.81	8.31	8.80	7.31	7.82	7.81	8.31	8.80
	8H	7.51	7.97	8.03	8.48	8.98	7.51	7.97	8.03	8.48	8.98
	12H	7.67	8.08	8.19	8.58	9.15	7.67	8.08	8.19	8.58	9.15
12H	4H	6.82	7.37	7.30	7.85	8.33	6.82	7.37	7.30	7.85	8.33
	6H	7.32	7.78	7.84	8.30	8.79	7.32	7.78	7.84	8.30	8.79
	8H	7.57	7.98	8.09	8.48	9.05	7.57	7.98	8.09	8.48	9.05