

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867291

Luminaire Tested: PRLX-2004-L-930-67L-G-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867291
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-72)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-930-67L-G-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS,
BELL WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 4
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3805.5 lumens
Efficiency: N/A
Efficacy: 75.5 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.22
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 50.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867291

CATALOG NUMBER: PRLX-2004-L-930-67L-G-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P867291

CATALOG NUMBER: PRLX-2004-L-930-67L-G-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	98	107	103	100	97	99	96	94	95	93	91	92	90	88	86
2	101	94	88	82	99	92	86	81	88	84	80	85	81	78	82	79	76	74
3	93	84	76	70	91	82	75	70	79	73	68	76	71	67	74	70	66	64
4	86	75	67	61	84	74	66	60	71	65	60	69	63	59	67	62	58	56
5	80	68	59	53	78	67	59	53	65	58	52	63	57	52	61	56	51	49
6	74	62	53	47	72	61	53	47	59	52	47	57	51	46	56	50	46	44
7	69	56	48	42	67	55	48	42	54	47	42	53	46	42	51	46	41	39
8	64	52	44	38	63	51	43	38	50	43	38	49	42	38	47	42	37	36
9	60	48	40	35	59	47	40	35	46	39	34	45	39	34	44	38	34	32
10	57	44	37	32	56	44	36	32	43	36	32	42	36	31	41	35	31	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8648
5°	8664
10°	8648
15°	8608
20°	8555
25°	8381
30°	8003
35°	7430
40°	6743
45°	6020
50°	5291
55°	4569
60°	3962
65°	3639
70°	3397
75°	3187
80°	3006
85°	2830

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 6020 cd/sqm

TEST NUMBER: P867291

CATALOG NUMBER: PRLX-2004-L-930-67L-G-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	166.2	4.4
10°-20°	475.5	12.5
20°-30°	705.7	18.5
30°-40°	768.6	20.2
40°-50°	666.4	17.5
50°-60°	478.9	12.6
60°-70°	310.6	8.2
70°-80°	177.7	4.7
80°-90°	55.7	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1347.5	35.4
0°-40°	2116.1	55.6
0°-60°	3261.4	85.7
0°-90°	3805.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3805.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1753	
5°	1749	166
15°	1685	476
25°	1540	706
35°	1234	769
45°	863	666
55°	531	479
65°	312	311
75°	167	178
85°	50	56
90°	0	

TEST NUMBER: P867291

CATALOG NUMBER: PRLX-2004-L-930-67L-G-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	1752.8
2.5°	1752.8
5°	1749.4
7.5°	1740.3
10°	1726.1
12.5°	1706.8
15°	1685.2
17.5°	1660.1
20°	1629.4
22.5°	1590.2
25°	1539.6
27.5°	1478.1
30°	1404.8
32.5°	1322.3
35°	1233.6
37.5°	1140.3
40°	1047.0
42.5°	954.9
45°	862.8
47.5°	775.8
50°	689.3
52.5°	609.7
55°	531.2
57.5°	460.1
60°	401.5
62.5°	353.8
65°	311.7
67.5°	271.9
70°	235.5
72.5°	200.2
75°	167.2
77.5°	135.9
80°	105.8
82.5°	77.3
85°	50.0
87.5°	24.5
90°	0.0



TEST NUMBER: P867291
 CATALOG NUMBER: PRLX-2004-L-930-67L-G-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.25	17.75	16.61	18.06	18.37	16.25	17.75	16.61	18.06	18.37
	3H	17.76	19.11	18.14	19.43	19.80	17.76	19.11	18.14	19.43	19.80
	4H	18.36	19.62	18.76	19.97	20.35	18.36	19.62	18.76	19.97	20.35
	6H	18.84	20.00	19.25	20.37	20.76	18.84	20.00	19.25	20.37	20.76
	8H	19.01	20.12	19.43	20.51	20.91	19.01	20.12	19.43	20.51	20.91
	12H	19.13	20.19	19.56	20.57	21.00	19.13	20.19	19.56	20.57	21.00
4H	2H	16.75	18.01	17.15	18.36	18.74	16.75	18.01	17.15	18.36	18.74
	3H	18.50	19.55	18.91	19.95	20.35	18.50	19.55	18.91	19.95	20.35
	4H	19.24	20.18	19.67	20.60	21.04	19.24	20.18	19.67	20.60	21.04
	6H	19.85	20.67	20.31	21.12	21.58	19.85	20.67	20.31	21.12	21.58
	8H	20.08	20.84	20.54	21.29	21.76	20.08	20.84	20.54	21.29	21.76
	12H	20.25	20.94	20.73	21.42	21.89	20.25	20.94	20.73	21.42	21.89
8H	4H	19.51	20.28	19.98	20.73	21.19	19.51	20.28	19.98	20.73	21.19
	6H	20.26	20.90	20.76	21.39	21.87	20.26	20.90	20.76	21.39	21.87
	8H	20.57	21.14	21.08	21.65	22.14	20.57	21.14	21.08	21.65	22.14
	12H	20.83	21.33	21.34	21.83	22.39	20.83	21.33	21.34	21.83	22.39
12H	4H	19.54	20.23	20.02	20.71	21.18	19.54	20.23	20.02	20.71	21.18
	6H	20.32	20.89	20.83	21.40	21.89	20.32	20.89	20.83	21.40	21.89
	8H	20.68	21.19	21.19	21.68	22.25	20.68	21.19	21.19	21.68	22.25