

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866881

Luminaire Tested: PRLX-2001-L-940-15L-G-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866881
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-65)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-L-940-15L-G-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS,
TAPERED DRUM WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 1
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 569.8 lumens
Efficiency: N/A
Efficacy: 34.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.51
Luminous Opening: Circular (Dia: 1.58' x H: 0')
CIE Type: Direct

Input Watts (W): 16.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866881

CATALOG NUMBER: PRLX-2001-L-940-15L-G-X-X-BRSS-X

Luminous Intensity Polar Plot



TEST NUMBER: P866881

CATALOG NUMBER: PRLX-2001-L-940-15L-G-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	108	103	99	95	106	101	97	93	97	93	90		93	90	88		89	87	85	83
2	98	90	82	76	95	88	81	76	84	79	74		81	76	72		78	74	70	68
3	89	78	70	63	87	77	69	62	74	67	61		71	65	60		68	63	59	57
4	81	69	60	53	79	67	59	52	65	58	52		63	56	51		60	55	50	48
5	74	61	52	45	72	60	51	45	58	50	44		56	49	44		54	48	43	41
6	69	55	46	39	67	54	45	39	52	44	38		50	43	38		49	43	38	36
7	63	50	40	34	62	49	40	34	47	39	34		46	39	34		44	38	33	31
8	59	45	36	30	57	44	36	30	43	35	30		42	35	30		40	34	30	28
9	55	41	33	27	53	41	33	27	39	32	27		38	32	27		37	31	27	25
10	51	38	30	24	50	37	30	24	36	29	24		35	29	24		34	28	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	937
5°	941
10°	945
15°	950
20°	959
25°	970
30°	987
35°	1014
40°	1051
45°	1075
50°	1077
55°	1063
60°	1037
65°	993
70°	929
75°	843
80°	749
85°	608

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 47.5°
 Luminance: 1080 cd/sqm

TEST NUMBER: P866881

CATALOG NUMBER: PRLX-2001-L-940-15L-G-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	16.3	2.9
10°-20°	47.5	8.3
20°-30°	74.3	13.0
30°-40°	95.4	16.7
40°-50°	106.9	18.8
50°-60°	99.5	17.5
60°-70°	75.9	13.3
70°-80°	42.6	7.5
80°-90°	11.4	2.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	138.1	24.2
0°-40°	233.5	41.0
0°-60°	439.9	77.2
0°-90°	569.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	569.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	171	
5°	171	16
15°	168	47
25°	161	74
35°	152	95
45°	139	107
55°	112	100
65°	77	76
75°	40	43
85°	10	11
90°	0	

TEST NUMBER: P866881

CATALOG NUMBER: PRLX-2001-L-940-15L-G-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	171.4
2.5°	171.6
5°	171.4
7.5°	171.2
10°	170.3
12.5°	169.2
15°	167.9
17.5°	166.4
20°	164.8
22.5°	162.9
25°	160.8
27.5°	158.6
30°	156.4
32.5°	154.3
35°	152.0
37.5°	149.8
40°	147.3
42.5°	143.9
45°	139.0
47.5°	133.5
50°	126.6
52.5°	119.3
55°	111.5
57.5°	103.5
60°	94.8
62.5°	85.9
65°	76.8
67.5°	67.5
70°	58.1
72.5°	49.1
75°	39.9
77.5°	31.6
80°	23.8
82.5°	16.2
85°	9.7
87.5°	4.2
90°	0.0



TEST NUMBER: P866881
 CATALOG NUMBER: PRLX-2001-L-940-15L-G-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.62	14.30	12.98	14.62	14.93	12.62	14.30	12.98	14.62	14.93
	3H	14.40	15.93	14.78	16.25	16.61	14.40	15.93	14.78	16.25	16.61
	4H	15.04	16.49	15.44	16.83	17.21	15.04	16.49	15.44	16.83	17.21
	6H	15.51	16.85	15.92	17.21	17.60	15.51	16.85	15.92	17.21	17.60
	8H	15.65	16.93	16.08	17.32	17.72	15.65	16.93	16.08	17.32	17.72
	12H	15.75	16.97	16.18	17.35	17.78	15.75	16.97	16.18	17.35	17.78
4H	2H	13.26	14.70	13.66	15.05	15.42	13.26	14.70	13.66	15.05	15.42
	3H	15.26	16.47	15.67	16.86	17.26	15.26	16.47	15.67	16.86	17.26
	4H	16.02	17.12	16.45	17.53	17.97	16.02	17.12	16.45	17.53	17.97
	6H	16.62	17.58	17.07	18.02	18.47	16.62	17.58	17.07	18.02	18.47
	8H	16.80	17.70	17.26	18.14	18.61	16.80	17.70	17.26	18.14	18.61
	12H	16.94	17.75	17.42	18.22	18.69	16.94	17.75	17.42	18.22	18.69
8H	4H	16.33	17.23	16.79	17.67	18.13	16.33	17.23	16.79	17.67	18.13
	6H	17.04	17.79	17.53	18.27	18.75	17.04	17.79	17.53	18.27	18.75
	8H	17.29	17.97	17.80	18.47	18.96	17.29	17.97	17.80	18.47	18.96
	12H	17.49	18.09	18.00	18.58	19.14	17.49	18.09	18.00	18.58	19.14
12H	4H	16.36	17.17	16.84	17.65	18.12	16.36	17.17	16.84	17.65	18.12
	6H	17.09	17.76	17.60	18.27	18.75	17.09	17.76	17.60	18.27	18.75
	8H	17.40	18.00	17.91	18.49	19.04	17.40	18.00	17.91	18.49	19.04