

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867301

Luminaire Tested: PRLX-2004-L-935-100L-L-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867301
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-85)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-935-100L-L-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,
BELL WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 6
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5242.6 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 0.99
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 79.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867301

CATALOG NUMBER: PRLX-2004-L-935-100L-L-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P867301

CATALOG NUMBER: PRLX-2004-L-935-100L-L-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92
2	106	101	96	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77
4	95	87	80	76	93	85	80	75	83	78	74	81	77	74	79	76	73	71
5	90	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	66
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61
7	80	70	64	59	79	69	63	59	68	63	58	67	62	58	66	61	58	56
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52
9	72	62	55	51	71	61	55	51	60	55	51	59	54	51	58	54	50	49
10	68	58	52	48	67	58	52	48	57	51	47	56	51	47	55	50	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	24153
5°	23333
10°	22194
15°	21333
20°	20556
25°	19831
30°	18873
35°	13690
40°	4865
45°	2141
50°	1481
55°	1461
60°	1379
65°	1298
70°	1219
75°	1153
80°	1088
85°	1008

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2141 cd/sqm

TEST NUMBER: P867301

CATALOG NUMBER: PRLX-2004-L-935-100L-L-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	440.8	8.4
10°-20°	1176.2	22.4
20°-30°	1674.4	31.9
30°-40°	1327.7	25.3
40°-50°	278.2	5.3
50°-60°	150.8	2.9
60°-70°	110.5	2.1
70°-80°	64.1	1.2
80°-90°	20.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3291.4	62.8
0°-40°	4619.1	88.1
0°-60°	5048.1	96.3
0°-90°	5242.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5242.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	4895	
5°	4711	441
15°	4177	1176
25°	3643	1674
35°	2273	1328
45°	307	278
55°	170	151
65°	111	110
75°	60	64
85°	18	20
90°	0	

TEST NUMBER: P867301

CATALOG NUMBER: PRLX-2004-L-935-100L-L-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	4895.4
2.5°	4846.4
5°	4711.2
7.5°	4566.2
10°	4430.1
12.5°	4303.8
15°	4176.6
17.5°	4048.5
20°	3915.0
22.5°	3781.6
25°	3642.8
27.5°	3500.5
30°	3312.8
32.5°	2967.6
35°	2272.9
37.5°	1396.6
40°	755.3
42.5°	461.7
45°	306.9
47.5°	223.3
50°	193.0
52.5°	183.3
55°	169.9
57.5°	154.8
60°	139.7
62.5°	125.4
65°	111.2
67.5°	97.9
70°	84.5
72.5°	72.1
75°	60.5
77.5°	48.9
80°	38.3
82.5°	27.6
85°	17.8
87.5°	8.9
90°	0.0

TEST NUMBER: P867301

CATALOG NUMBER: PRLX-2004-L-935-100L-L-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.14	9.20	8.50	9.51	9.82	8.14	9.20	8.50	9.51	9.82
	3H	9.77	10.70	10.15	11.04	11.40	9.77	10.70	10.15	11.04	11.40
	4H	10.40	11.26	10.80	11.62	12.01	10.40	11.26	10.80	11.62	12.01
	6H	10.87	11.67	11.29	12.04	12.44	10.87	11.67	11.29	12.04	12.44
	8H	11.04	11.78	11.47	12.18	12.59	11.04	11.78	11.47	12.18	12.59
	12H	11.14	11.86	11.58	12.24	12.67	11.14	11.86	11.58	12.24	12.67
4H	2H	8.63	9.50	9.04	9.85	10.24	8.63	9.50	9.04	9.85	10.24
	3H	10.47	11.18	10.88	11.59	11.99	10.47	11.18	10.88	11.59	11.99
	4H	11.22	11.86	11.66	12.28	12.73	11.22	11.86	11.66	12.28	12.73
	6H	11.83	12.38	12.30	12.83	13.30	11.83	12.38	12.30	12.83	13.30
	8H	12.04	12.55	12.52	13.00	13.47	12.04	12.55	12.52	13.00	13.47
	12H	12.19	12.63	12.68	13.12	13.60	12.19	12.63	12.68	13.12	13.60
8H	4H	11.46	11.96	11.93	12.41	12.89	11.46	11.96	11.93	12.41	12.89
	6H	12.21	12.61	12.72	13.11	13.60	12.21	12.61	12.72	13.11	13.60
	8H	12.50	12.86	13.03	13.38	13.88	12.50	12.86	13.03	13.38	13.88
	12H	12.75	13.06	13.27	13.56	14.14	12.75	13.06	13.27	13.56	14.14
12H	4H	11.46	11.90	11.95	12.39	12.87	11.46	11.90	11.95	12.39	12.87
	6H	12.25	12.61	12.78	13.13	13.63	12.25	12.61	12.78	13.13	13.63
	8H	12.60	12.92	13.12	13.41	13.99	12.60	12.92	13.12	13.41	13.99