

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867322

Luminaire Tested: PRLX-2004-L-935-133L-G-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867322
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-74)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-935-133L-G-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS,
BELL WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 8
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2628.4 lumens
Efficiency: N/A
Efficacy: 23.5 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.15
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 111.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867322

CATALOG NUMBER: PRLX-2004-L-935-133L-G-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P867322

CATALOG NUMBER: PRLX-2004-L-935-133L-G-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	85	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	81	74	69	89	80	74	69	78	72	68		76	71	67		74	70	66	64
5	85	75	67	62	83	73	67	62	72	66	61		70	64	60		68	63	60	58
6	79	68	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	51	73	62	55	50	61	55	50		60	54	50		58	53	49	48
8	70	58	51	46	68	58	51	46	56	50	46		55	50	45		54	49	45	44
9	66	54	47	42	64	54	47	42	53	46	42		52	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39		48	42	39		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	7860
5°	7866
10°	7838
15°	7735
20°	7601
25°	7421
30°	7046
35°	6272
40°	5295
45°	4166
50°	2936
55°	1712
60°	1035
65°	891
70°	791
75°	703
80°	642
85°	606

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4166 cd/sqm

TEST NUMBER: P867322

CATALOG NUMBER: PRLX-2004-L-935-133L-G-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.9	5.7
10°-20°	426.8	16.2
20°-30°	625.1	23.8
30°-40°	646.6	24.6
40°-50°	459.2	17.5
50°-60°	191.1	7.3
60°-70°	77.2	2.9
70°-80°	39.7	1.5
80°-90°	11.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1202.7	45.8
0°-40°	1849.4	70.4
0°-60°	2499.6	95.1
0°-90°	2628.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2628.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1593	
5°	1588	151
15°	1514	427
25°	1363	625
35°	1041	647
45°	597	459
55°	199	191
65°	76	77
75°	37	40
85°	11	12
90°	0	

TEST NUMBER: P867322

CATALOG NUMBER: PRLX-2004-L-935-133L-G-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	1593.1
2.5°	1591.9
5°	1588.3
7.5°	1580.0
10°	1564.5
12.5°	1541.8
15°	1514.4
17.5°	1483.4
20°	1447.7
22.5°	1408.4
25°	1363.1
27.5°	1311.9
30°	1236.8
32.5°	1146.2
35°	1041.4
37.5°	933.0
40°	822.2
42.5°	709.0
45°	597.0
47.5°	487.3
50°	382.5
52.5°	288.3
55°	199.0
57.5°	132.3
60°	104.9
62.5°	90.6
65°	76.3
67.5°	65.5
70°	54.8
72.5°	45.3
75°	36.9
77.5°	29.8
80°	22.6
82.5°	16.7
85°	10.7
87.5°	4.8
90°	0.0



TEST NUMBER: P867322
 CATALOG NUMBER: PRLX-2004-L-935-133L-G-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.10	10.39	9.46	10.70	11.01	9.10	10.39	9.46	10.70	11.01
	3H	10.17	11.30	10.55	11.63	12.00	10.17	11.30	10.55	11.63	12.00
	4H	10.56	11.62	10.96	11.97	12.35	10.56	11.62	10.96	11.97	12.35
	6H	10.86	11.83	11.28	12.21	12.60	10.86	11.83	11.28	12.21	12.60
	8H	10.97	11.89	11.40	12.28	12.68	10.97	11.89	11.40	12.28	12.68
	12H	11.04	11.91	11.47	12.30	12.73	11.04	11.91	11.47	12.30	12.73
4H	2H	9.41	10.46	9.81	10.82	11.20	9.41	10.46	9.81	10.82	11.20
	3H	10.69	11.55	11.10	11.96	12.36	10.69	11.55	11.10	11.96	12.36
	4H	11.20	11.97	11.64	12.39	12.83	11.20	11.97	11.64	12.39	12.83
	6H	11.63	12.29	12.09	12.74	13.20	11.63	12.29	12.09	12.74	13.20
	8H	11.77	12.39	12.24	12.84	13.31	11.77	12.39	12.24	12.84	13.31
	12H	11.88	12.43	12.37	12.91	13.39	11.88	12.43	12.37	12.91	13.39
8H	4H	11.36	11.97	11.83	12.42	12.89	11.36	11.97	11.83	12.42	12.89
	6H	11.89	12.39	12.39	12.89	13.37	11.89	12.39	12.39	12.89	13.37
	8H	12.11	12.56	12.63	13.08	13.57	12.11	12.56	12.63	13.08	13.57
	12H	12.29	12.70	12.81	13.19	13.76	12.29	12.70	12.81	13.19	13.76
12H	4H	11.35	11.90	11.84	12.38	12.86	11.35	11.90	11.84	12.38	12.86
	6H	11.91	12.36	12.43	12.88	13.37	11.91	12.36	12.43	12.88	13.37
	8H	12.18	12.58	12.69	13.08	13.65	12.18	12.58	12.69	13.08	13.65