

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867330

Luminaire Tested: PRLX-2004-L-935-15L-G-X-X-GREY-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P867330  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-74)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-L-935-15L-G-X-X-GREY-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS,  
BELL WITH GRAY INTERIOR SHADE.  
LIGHT LEVEL 1  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 297.2 lumens  
Efficiency: N/A  
Efficacy: 18.1 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.15  
Luminous Opening: Circular (Dia: 1.67' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 16.4  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P867330

CATALOG NUMBER: PRLX-2004-L-935-15L-G-X-X-GREY-X

### Luminous Intensity Polar Plot





TEST NUMBER: P867330

CATALOG NUMBER: PRLX-2004-L-935-15L-G-X-X-GREY-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	85	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	81	74	69	89	80	74	69	78	72	68		76	71	67		74	70	66	64
5	85	75	67	62	83	73	67	62	72	66	61		70	64	60		68	63	60	58
6	79	68	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	51	73	62	55	50	61	55	50		60	54	50		58	53	49	48
8	70	58	51	46	68	58	51	46	56	50	46		55	50	45		54	49	45	44
9	66	54	47	42	64	54	47	42	53	46	42		52	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	39		48	42	39		47	42	38	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	889
5°	889
10°	886
15°	874
20°	859
25°	839
30°	796
35°	709
40°	599
45°	471
50°	332
55°	194
60°	117
65°	100
70°	89
75°	80
80°	74
85°	68

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 471 cd/sqm

TEST NUMBER: P867330

CATALOG NUMBER: PRLX-2004-L-935-15L-G-X-X-GREY-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	17.1	5.7
10°-20°	48.2	16.2
20°-30°	70.7	23.8
30°-40°	73.1	24.6
40°-50°	51.9	17.5
50°-60°	21.6	7.3
60°-70°	8.7	2.9
70°-80°	4.5	1.5
80°-90°	1.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	136.0	45.8
0°-40°	209.1	70.4
0°-60°	282.6	95.1
0°-90°	297.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	297.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	180	
5°	180	17
15°	171	48
25°	154	71
35°	118	73
45°	68	52
55°	22	22
65°	9	9
75°	4	5
85°	1	1
90°	0	

TEST NUMBER: P867330

CATALOG NUMBER: PRLX-2004-L-935-15L-G-X-X-GREY-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	180.1
2.5°	180.0
5°	179.6
7.5°	178.6
10°	176.9
12.5°	174.3
15°	171.2
17.5°	167.7
20°	163.7
22.5°	159.2
25°	154.1
27.5°	148.3
30°	139.8
32.5°	129.6
35°	117.7
37.5°	105.5
40°	93.0
42.5°	80.2
45°	67.5
47.5°	55.1
50°	43.2
52.5°	32.6
55°	22.5
57.5°	15.0
60°	11.9
62.5°	10.2
65°	8.6
67.5°	7.4
70°	6.2
72.5°	5.1
75°	4.2
77.5°	3.4
80°	2.6
82.5°	1.9
85°	1.2
87.5°	0.5
90°	0.0



TEST NUMBER: P867330  
 CATALOG NUMBER: PRLX-2004-L-935-15L-G-X-X-GREY-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	1.55	2.83	1.91	3.15	3.46	1.55	2.83	1.91	3.15	3.46
	3H	2.61	3.74	2.99	4.07	4.44	2.61	3.74	2.99	4.07	4.44
	4H	3.00	4.06	3.41	4.41	4.79	3.00	4.06	3.41	4.41	4.79
	6H	3.31	4.28	3.73	4.65	5.05	3.31	4.28	3.73	4.65	5.05
	8H	3.42	4.34	3.85	4.73	5.13	3.42	4.34	3.85	4.73	5.13
	12H	3.49	4.36	3.92	4.75	5.18	3.49	4.36	3.92	4.75	5.18
4H	2H	1.85	2.90	2.25	3.26	3.64	1.85	2.90	2.25	3.26	3.64
	3H	3.13	3.99	3.54	4.39	4.79	3.13	3.99	3.54	4.39	4.79
	4H	3.64	4.41	4.08	4.83	5.27	3.64	4.41	4.08	4.83	5.27
	6H	4.08	4.74	4.54	5.18	5.65	4.08	4.74	4.54	5.18	5.65
	8H	4.22	4.84	4.69	5.29	5.76	4.22	4.84	4.69	5.29	5.76
	12H	4.33	4.88	4.82	5.36	5.84	4.33	4.88	4.82	5.36	5.84
8H	4H	3.80	4.42	4.27	4.86	5.33	3.80	4.42	4.27	4.86	5.33
	6H	4.34	4.85	4.85	5.35	5.83	4.34	4.85	4.85	5.35	5.83
	8H	4.56	5.02	5.08	5.53	6.03	4.56	5.02	5.08	5.53	6.03
	12H	4.75	5.15	5.26	5.64	6.22	4.75	5.15	5.26	5.64	6.22
12H	4H	3.79	4.34	4.28	4.82	5.30	3.79	4.34	4.28	4.82	5.30
	6H	4.36	4.82	4.89	5.33	5.83	4.36	4.82	4.89	5.33	5.83
	8H	4.63	5.04	5.15	5.53	6.11	4.63	5.04	5.15	5.53	6.11