

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865923

Luminaire Tested: PRLX-2001-M-927-35L-L-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865923
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-46)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-M-927-35L-L-U-S-X-X-WHHR-X
Description: PRENATALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 4
Light Source: 2700K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3272.7 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.31
Luminous Opening: Circular (Dia: 1.27' x H: 0')
CIE Type: Direct

Input Watts (W): 30
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865923

CATALOG NUMBER: PRLX-2001-M-927-35L-L-U-S-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P865923

CATALOG NUMBER: PRLX-2001-M-927-35L-L-U-S-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51
6	75	63	55	49	73	62	54	48	60	53	48	58	52	48	57	52	47	45
7	70	57	49	43	68	56	49	43	55	48	43	54	47	43	52	47	42	41
8	65	52	44	39	64	52	44	39	50	44	39	49	43	38	48	42	38	37
9	61	48	41	35	59	48	40	35	47	40	35	46	39	35	45	39	35	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	12894
5°	12837
10°	12695
15°	12499
20°	12278
25°	12040
30°	11791
35°	11527
40°	11235
45°	10871
50°	10341
55°	7831
60°	4206
65°	2711
70°	2732
75°	2882
80°	2996
85°	3028

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 10871 cd/sqm

TEST NUMBER: P865923

CATALOG NUMBER: PRLX-2001-M-927-35L-L-U-S-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.8	4.4
10°-20°	401.1	12.3
20°-30°	592.6	18.1
30°-40°	695.8	21.3
40°-50°	697.5	21.3
50°-60°	467.1	14.3
60°-70°	150.0	4.6
70°-80°	91.8	2.8
80°-90°	34.0	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1136.5	34.7
0°-40°	1832.3	56.0
0°-60°	2996.9	91.6
0°-90°	3272.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3272.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1520	
5°	1507	143
15°	1423	401
25°	1286	593
35°	1113	696
45°	906	698
55°	529	467
65°	135	150
75°	88	92
85°	31	34
90°	0	

TEST NUMBER: P865923

CATALOG NUMBER: PRLX-2001-M-927-35L-L-U-S-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	1519.5
2.5°	1516.8
5°	1507.0
7.5°	1492.8
10°	1473.3
12.5°	1451.1
15°	1422.7
17.5°	1393.4
20°	1359.6
22.5°	1325.0
25°	1285.9
27.5°	1246.8
30°	1203.3
32.5°	1158.9
35°	1112.7
37.5°	1064.8
40°	1014.2
42.5°	962.6
45°	905.8
47.5°	848.1
50°	783.3
52.5°	683.8
55°	529.3
57.5°	375.6
60°	247.8
62.5°	174.9
65°	135.0
67.5°	119.0
70°	110.1
72.5°	99.5
75°	87.9
77.5°	74.6
80°	61.3
82.5°	47.1
85°	31.1
87.5°	16.0
90°	0.0

TEST NUMBER: P865923

CATALOG NUMBER: PRLX-2001-M-927-35L-L-U-S-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.16	18.64	17.53	18.95	19.27	17.16	18.64	17.53	18.95	19.27
	3H	17.64	18.95	18.02	19.28	19.64	17.64	18.95	18.02	19.28	19.64
	4H	17.96	19.19	18.36	19.54	19.92	17.96	19.19	18.36	19.54	19.92
	6H	18.29	19.42	18.70	19.79	20.18	18.29	19.42	18.70	19.79	20.18
	8H	18.43	19.50	18.86	19.89	20.29	18.43	19.50	18.86	19.89	20.29
	12H	18.54	19.56	18.97	19.94	20.37	18.54	19.56	18.97	19.94	20.37
4H	2H	17.20	18.42	17.60	18.77	19.15	17.20	18.42	17.60	18.77	19.15
	3H	17.91	18.91	18.32	19.31	19.71	17.91	18.91	18.32	19.31	19.71
	4H	18.38	19.28	18.81	19.69	20.13	18.38	19.28	18.81	19.69	20.13
	6H	18.88	19.66	19.34	20.10	20.56	18.88	19.66	19.34	20.10	20.56
	8H	19.09	19.82	19.55	20.26	20.73	19.09	19.82	19.55	20.26	20.73
	12H	19.26	19.91	19.74	20.39	20.86	19.26	19.91	19.74	20.39	20.86
8H	4H	18.54	19.27	19.01	19.72	20.19	18.54	19.27	19.01	19.72	20.19
	6H	19.18	19.78	19.67	20.27	20.75	19.18	19.78	19.67	20.27	20.75
	8H	19.47	20.02	19.99	20.53	21.02	19.47	20.02	19.99	20.53	21.02
	12H	19.74	20.23	20.25	20.72	21.29	19.74	20.23	20.25	20.72	21.29
12H	4H	18.56	19.21	19.04	19.69	20.16	18.56	19.21	19.04	19.69	20.16
	6H	19.22	19.77	19.74	20.28	20.77	19.22	19.77	19.74	20.28	20.77
	8H	19.58	20.07	20.09	20.56	21.13	19.58	20.07	20.09	20.56	21.13