

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867337

Luminaire Tested: PRLX-2004-L-935-32L-G-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867337
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-935-32L-G-X-X-BRSS-X
Description: PRENATALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, GLOBE LENS,
BELL WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 642.8 lumens
Efficiency: N/A
Efficacy: 24.6 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.17
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 26.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867337

CATALOG NUMBER: PRLX-2004-L-935-32L-G-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P867337

CATALOG NUMBER: PRLX-2004-L-935-32L-G-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	74		80	76	73	71
4	91	81	74	69	89	80	73	68	78	72	67		75	70	67		73	69	66	64
5	85	74	67	61	83	73	66	61	71	65	60		69	64	60		68	63	59	57
6	79	68	61	55	77	67	60	55	65	59	55		64	58	54		62	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49		59	53	49		58	53	49	47
8	69	58	50	45	68	57	50	45	56	50	45		55	49	45		54	49	45	43
9	65	54	46	42	64	53	46	42	52	46	41		51	45	41		50	45	41	39
10	62	50	43	38	60	49	43	38	48	42	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1867
5°	1871
10°	1865
15°	1846
20°	1818
25°	1779
30°	1698
35°	1526
40°	1305
45°	1042
50°	757
55°	464
60°	262
65°	223
70°	198
75°	179
80°	162
85°	147

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1042 cd/sqm

TEST NUMBER: P867337

CATALOG NUMBER: PRLX-2004-L-935-32L-G-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	35.9	5.6
10°-20°	101.9	15.8
20°-30°	149.9	23.3
30°-40°	157.4	24.5
40°-50°	114.9	17.9
50°-60°	50.6	7.9
60°-70°	19.3	3.0
70°-80°	10.0	1.6
80°-90°	3.0	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	287.7	44.7
0°-40°	445.1	69.2
0°-60°	610.6	95.0
0°-90°	642.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	642.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	378	
5°	378	36
15°	361	102
25°	327	150
35°	253	157
45°	149	115
55°	54	51
65°	19	19
75°	9	10
85°	3	3
90°	0	

TEST NUMBER: P867337

CATALOG NUMBER: PRLX-2004-L-935-32L-G-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	378.5
2.5°	378.3
5°	377.7
7.5°	375.7
10°	372.3
12.5°	367.4
15°	361.4
17.5°	354.5
20°	346.3
22.5°	337.4
25°	326.8
27.5°	314.8
30°	298.0
32.5°	277.4
35°	253.4
37.5°	228.6
40°	202.6
42.5°	176.0
45°	149.4
47.5°	123.1
50°	98.6
52.5°	75.4
55°	54.0
57.5°	36.6
60°	26.6
62.5°	22.6
65°	19.1
67.5°	16.3
70°	13.7
72.5°	11.4
75°	9.4
77.5°	7.4
80°	5.7
82.5°	4.3
85°	2.6
87.5°	1.1
90°	0.0

TEST NUMBER: P867337
 CATALOG NUMBER: PRLX-2004-L-935-32L-G-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.01	6.31	5.37	6.62	6.94	5.01	6.31	5.37	6.62	6.94
	3H	5.89	7.04	6.27	7.37	7.73	5.89	7.04	6.27	7.37	7.73
	4H	6.24	7.31	6.64	7.66	8.04	6.24	7.31	6.64	7.66	8.04
	6H	6.50	7.48	6.91	7.85	8.25	6.50	7.48	6.91	7.85	8.25
	8H	6.59	7.52	7.02	7.91	8.32	6.59	7.52	7.02	7.91	8.32
	12H	6.65	7.54	7.08	7.92	8.35	6.65	7.54	7.08	7.92	8.35
4H	2H	5.23	6.30	5.64	6.65	7.04	5.23	6.30	5.64	6.65	7.04
	3H	6.33	7.20	6.74	7.61	8.01	6.33	7.20	6.74	7.61	8.01
	4H	6.80	7.57	7.23	7.99	8.44	6.80	7.57	7.23	7.99	8.44
	6H	7.18	7.85	7.64	8.30	8.76	7.18	7.85	7.64	8.30	8.76
	8H	7.32	7.94	7.79	8.39	8.86	7.32	7.94	7.79	8.39	8.86
	12H	7.42	7.97	7.90	8.45	8.93	7.42	7.97	7.90	8.45	8.93
8H	4H	6.93	7.56	7.40	8.00	8.47	6.93	7.56	7.40	8.00	8.47
	6H	7.41	7.93	7.92	8.42	8.90	7.41	7.93	7.92	8.42	8.90
	8H	7.62	8.08	8.14	8.60	9.09	7.62	8.08	8.14	8.60	9.09
	12H	7.79	8.20	8.31	8.70	9.27	7.79	8.20	8.31	8.70	9.27
12H	4H	6.92	7.48	7.41	7.96	8.43	6.92	7.48	7.41	7.96	8.43
	6H	7.43	7.89	7.95	8.41	8.90	7.43	7.89	7.95	8.41	8.90
	8H	7.69	8.10	8.20	8.59	9.17	7.69	8.10	8.20	8.59	9.17