

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867342

Luminaire Tested: PRLX-2004-L-935-48L-L-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867342
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-86)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-935-48L-L-X-X-GREY-X
Description: PRENATALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS, BELL WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 3
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2564.9 lumens
Efficiency: N/A
Efficacy: 68.4 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.98
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 37.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867342

CATALOG NUMBER: PRLX-2004-L-935-48L-L-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P867342

CATALOG NUMBER: PRLX-2004-L-935-48L-L-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100		100	98	97		96	95	94	92
2	107	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	101	94	88	84	99	92	87	83	89	85	82		87	83	80		85	82	79	77
4	95	87	81	76	93	86	80	76	83	79	75		81	77	74		79	76	73	71
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		75	71	68	66
6	85	75	69	64	83	74	68	64	73	68	64		71	67	63		70	66	63	61
7	80	70	64	59	79	70	64	59	68	63	59		67	62	59		66	62	58	57
8	76	66	60	55	75	65	59	55	64	59	55		63	58	55		62	58	54	53
9	72	62	56	51	71	62	55	51	61	55	51		60	55	51		59	54	51	49
10	69	58	52	48	68	58	52	48	57	52	48		56	51	48		56	51	48	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	12136
5°	11741
10°	11127
15°	10644
20°	10221
25°	9822
30°	9379
35°	6570
40°	2067
45°	1003
50°	748
55°	721
60°	672
65°	622
70°	580
75°	541
80°	509
85°	470

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1003 cd/sqm

TEST NUMBER: P867342

CATALOG NUMBER: PRLX-2004-L-935-48L-L-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.4	8.6
10°-20°	587.0	22.9
20°-30°	830.1	32.4
30°-40°	632.1	24.6
40°-50°	127.1	5.0
50°-60°	74.5	2.9
60°-70°	53.0	2.1
70°-80°	30.2	1.2
80°-90°	9.3	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1638.5	63.9
0°-40°	2270.7	88.5
0°-60°	2472.3	96.4
0°-90°	2564.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2564.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2460	
5°	2371	221
15°	2084	587
25°	1804	830
35°	1091	632
45°	144	127
55°	84	75
65°	53	53
75°	28	30
85°	8	9
90°	0	

TEST NUMBER: P867342

CATALOG NUMBER: PRLX-2004-L-935-48L-L-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

0°	
0°	2459.7
2.5°	2441.4
5°	2370.6
7.5°	2291.2
10°	2220.9
12.5°	2153.2
15°	2083.8
17.5°	2017.4
20°	1946.6
22.5°	1875.0
25°	1804.3
27.5°	1732.7
30°	1646.2
32.5°	1463.3
35°	1090.8
37.5°	603.0
40°	320.9
42.5°	212.2
45°	143.7
47.5°	103.5
50°	97.4
52.5°	91.3
55°	83.8
57.5°	75.5
60°	68.1
62.5°	60.3
65°	53.3
67.5°	46.7
70°	40.2
72.5°	34.1
75°	28.4
77.5°	23.1
80°	17.9
82.5°	13.1
85°	8.3
87.5°	3.9
90°	0.0

TEST NUMBER: P867342
 CATALOG NUMBER: PRLX-2004-L-935-48L-L-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.64	6.69	6.01	7.00	7.32	5.64	6.69	6.01	7.00	7.32
	3H	7.21	8.13	7.59	8.47	8.84	7.21	8.13	7.59	8.47	8.84
	4H	7.80	8.66	8.20	9.01	9.40	7.80	8.66	8.20	9.01	9.40
	6H	8.25	9.04	8.67	9.42	9.81	8.25	9.04	8.67	9.42	9.81
	8H	8.41	9.15	8.84	9.54	9.95	8.41	9.15	8.84	9.54	9.95
	12H	8.51	9.22	8.94	9.60	10.03	8.51	9.22	8.94	9.60	10.03
4H	2H	6.11	6.97	6.51	7.32	7.71	6.11	6.97	6.51	7.32	7.71
	3H	7.88	8.59	8.30	9.00	9.40	7.88	8.59	8.30	9.00	9.40
	4H	8.60	9.23	9.04	9.65	10.10	8.60	9.23	9.04	9.65	10.10
	6H	9.18	9.73	9.65	10.17	10.65	9.18	9.73	9.65	10.17	10.65
	8H	9.39	9.89	9.86	10.34	10.81	9.39	9.89	9.86	10.34	10.81
	12H	9.53	9.97	10.02	10.46	10.93	9.53	9.97	10.02	10.46	10.93
8H	4H	8.82	9.32	9.29	9.77	10.25	8.82	9.32	9.29	9.77	10.25
	6H	9.54	9.94	10.05	10.45	10.93	9.54	9.94	10.05	10.45	10.93
	8H	9.83	10.19	10.36	10.71	11.21	9.83	10.19	10.36	10.71	11.21
	12H	10.07	10.38	10.59	10.88	11.46	10.07	10.38	10.59	10.88	11.46
12H	4H	8.82	9.26	9.31	9.75	10.22	8.82	9.26	9.31	9.75	10.22
	6H	9.58	9.94	10.11	10.46	10.96	9.58	9.94	10.11	10.46	10.96
	8H	9.93	10.24	10.45	10.74	11.32	9.93	10.24	10.45	10.74	11.32