

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865952

Luminaire Tested: PRLX-2001-M-927-75L-L-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865952
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-49)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-M-927-75L-L-U-S-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 8
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5256.1 lumens
Efficiency: N/A
Efficacy: 75.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Circular (Dia: 1.27' x H: 0')
CIE Type: Direct

Input Watts (W): 69.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865952

CATALOG NUMBER: PRLX-2001-M-927-75L-L-U-S-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P865952

CATALOG NUMBER: PRLX-2001-M-927-75L-L-U-S-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	86	90	86	84	87	84	82	80
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71
4	90	80	73	67	88	79	72	67	76	71	66	74	69	65	72	68	64	63
5	83	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	61	55	52	50
7	72	60	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	45
8	68	56	48	43	66	55	48	43	54	47	42	52	47	42	51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37
10	59	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	23448
5°	23359
10°	23055
15°	22636
20°	22134
25°	21595
30°	20996
35°	20306
40°	19541
45°	18681
50°	17561
55°	12388
60°	3909
65°	267
70°	189
75°	187
80°	186
85°	185

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 18681 cd/sqm

TEST NUMBER: P865952

CATALOG NUMBER: PRLX-2001-M-927-75L-L-U-S-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	259.6	4.9
10°-20°	725.9	13.8
20°-30°	1061.6	20.2
30°-40°	1225.3	23.3
40°-50°	1199.1	22.8
50°-60°	719.4	13.7
60°-70°	56.1	1.1
70°-80°	6.5	0.1
80°-90°	2.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2047.1	38.9
0°-40°	3272.5	62.3
0°-60°	5190.9	98.8
0°-90°	5256.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5256.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2763	
5°	2742	260
15°	2577	726
25°	2306	1062
35°	1960	1225
45°	1557	1199
55°	837	719
65°	13	56
75°	6	7
85°	2	3
90°	0	

TEST NUMBER: P865952

CATALOG NUMBER: PRLX-2001-M-927-75L-L-U-S-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	2763.1
2.5°	2759.3
5°	2742.2
7.5°	2713.6
10°	2675.6
12.5°	2631.8
15°	2576.6
17.5°	2517.6
20°	2451.0
22.5°	2380.6
25°	2306.4
27.5°	2226.5
30°	2142.7
32.5°	2053.3
35°	1960.1
37.5°	1864.9
40°	1764.0
42.5°	1667.0
45°	1556.6
47.5°	1446.3
50°	1330.2
52.5°	1141.8
55°	837.3
57.5°	492.9
60°	230.3
62.5°	91.3
65°	13.3
67.5°	7.6
70°	7.6
72.5°	7.6
75°	5.7
77.5°	5.7
80°	3.8
82.5°	3.8
85°	1.9
87.5°	1.9
90°	0.0



TEST NUMBER: P865952
 CATALOG NUMBER: PRLX-2001-M-927-75L-L-U-S-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	17.43	18.80	17.79	19.11	19.43	17.43	18.80	17.79	19.11	19.43
	3H	17.31	18.51	17.68	18.84	19.20	17.31	18.51	17.68	18.84	19.20
	4H	17.24	18.35	17.64	18.71	19.09	17.24	18.35	17.64	18.71	19.09
	6H	17.16	18.19	17.58	18.56	18.95	17.16	18.19	17.58	18.56	18.95
	8H	17.12	18.09	17.55	18.48	18.89	17.12	18.09	17.55	18.48	18.89
	12H	17.08	18.01	17.51	18.39	18.82	17.08	18.01	17.51	18.39	18.82
4H	2H	17.24	18.35	17.64	18.71	19.09	17.24	18.35	17.64	18.71	19.09
	3H	17.12	18.01	17.53	18.42	18.82	17.12	18.01	17.53	18.42	18.82
	4H	17.03	17.83	17.47	18.25	18.69	17.03	17.83	17.47	18.25	18.69
	6H	16.96	17.64	17.42	18.09	18.55	16.96	17.64	17.42	18.09	18.55
	8H	16.90	17.54	17.37	17.99	18.46	16.90	17.54	17.37	17.99	18.46
	12H	16.85	17.42	17.34	17.90	18.38	16.85	17.42	17.34	17.90	18.38
8H	4H	16.90	17.54	17.37	17.98	18.45	16.90	17.54	17.37	17.98	18.45
	6H	16.79	17.32	17.29	17.82	18.30	16.79	17.32	17.29	17.82	18.30
	8H	16.72	17.20	17.25	17.72	18.21	16.72	17.20	17.25	17.72	18.21
	12H	16.67	17.11	17.19	17.60	18.17	16.67	17.11	17.19	17.60	18.17
12H	4H	16.85	17.41	17.33	17.90	18.37	16.85	17.41	17.33	17.90	18.37
	6H	16.72	17.20	17.24	17.72	18.21	16.72	17.20	17.24	17.72	18.21
	8H	16.67	17.11	17.19	17.60	18.17	16.67	17.11	17.19	17.60	18.17