

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867382

Luminaire Tested: PRLX-2004-L-940-133L-L-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867382
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-86)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-940-133L-L-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,
BELL WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 8
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7306.6 lumens
Efficiency: N/A
Efficacy: 65.4 lumens/watt
Spacing Criteria (0/90/45): 1.02 / 1.02 / 0.98
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 111.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867382

CATALOG NUMBER: PRLX-2004-L-940-133L-L-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P867382

CATALOG NUMBER: PRLX-2004-L-940-133L-L-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	101	94	88	84	99	92	87	83	89	85	82	87	83	80	85	82	79	77
4	95	87	81	76	93	86	80	76	83	79	75	81	77	74	79	76	73	71
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	74	68	64	73	68	64	71	67	63	70	66	63	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53
9	72	62	56	51	71	62	55	51	61	55	51	60	55	51	59	54	51	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	56	51	48	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	34571
5°	33447
10°	31696
15°	30320
20°	29116
25°	27981
30°	26717
35°	18715
40°	5889
45°	2856
50°	2129
55°	2054
60°	1915
65°	1772
70°	1650
75°	1542
80°	1449
85°	1336

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2856 cd/sqm

TEST NUMBER: P867382

CATALOG NUMBER: PRLX-2004-L-940-133L-L-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	630.8	8.6
10°-20°	1672.0	22.9
20°-30°	2364.9	32.4
30°-40°	1800.8	24.6
40°-50°	362.0	5.0
50°-60°	212.3	2.9
60°-70°	151.1	2.1
70°-80°	86.1	1.2
80°-90°	26.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4667.7	63.9
0°-40°	6468.5	88.5
0°-60°	7042.8	96.4
0°-90°	7306.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7306.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7007	
5°	6753	631
15°	5936	1672
25°	5140	2365
35°	3107	1801
45°	409	362
55°	239	212
65°	152	151
75°	81	86
85°	24	27
90°	0	

TEST NUMBER: P867382

CATALOG NUMBER: PRLX-2004-L-940-133L-L-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	7007.0
2.5°	6954.8
5°	6753.3
7.5°	6526.9
10°	6326.6
12.5°	6133.8
15°	5936.0
17.5°	5746.9
20°	5545.4
22.5°	5341.4
25°	5139.9
27.5°	4935.9
30°	4689.6
32.5°	4168.4
35°	3107.3
37.5°	1717.9
40°	914.3
42.5°	604.5
45°	409.3
47.5°	294.8
50°	277.4
52.5°	260.0
55°	238.8
57.5°	215.2
60°	194.1
62.5°	171.7
65°	151.8
67.5°	133.1
70°	114.4
72.5°	97.0
75°	80.9
77.5°	65.9
80°	51.0
82.5°	37.3
85°	23.6
87.5°	11.2
90°	0.0

TEST NUMBER: P867382

CATALOG NUMBER: PRLX-2004-L-940-133L-L-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.28	10.33	9.65	10.64	10.96	9.28	10.33	9.65	10.64	10.96
	3H	10.84	11.77	11.23	12.11	12.47	10.84	11.77	11.23	12.11	12.47
	4H	11.44	12.30	11.84	12.65	13.04	11.44	12.30	11.84	12.65	13.04
	6H	11.89	12.68	12.31	13.06	13.45	11.89	12.68	12.31	13.06	13.45
	8H	12.05	12.79	12.48	13.18	13.59	12.05	12.79	12.48	13.18	13.59
	12H	12.15	12.86	12.58	13.24	13.67	12.15	12.86	12.58	13.24	13.67
4H	2H	9.75	10.61	10.15	10.96	11.35	9.75	10.61	10.15	10.96	11.35
	3H	11.52	12.23	11.93	12.63	13.04	11.52	12.23	11.93	12.63	13.04
	4H	12.23	12.87	12.67	13.29	13.74	12.23	12.87	12.67	13.29	13.74
	6H	12.82	13.36	13.29	13.81	14.29	12.82	13.36	13.29	13.81	14.29
	8H	13.02	13.53	13.50	13.98	14.45	13.02	13.53	13.50	13.98	14.45
	12H	13.17	13.61	13.66	14.09	14.57	13.17	13.61	13.66	14.09	14.57
8H	4H	12.46	12.96	12.93	13.41	13.88	12.46	12.96	12.93	13.41	13.88
	6H	13.18	13.58	13.69	14.08	14.57	13.18	13.58	13.69	14.08	14.57
	8H	13.47	13.83	14.00	14.35	14.84	13.47	13.83	14.00	14.35	14.84
	12H	13.71	14.02	14.23	14.51	15.09	13.71	14.02	14.23	14.51	15.09
12H	4H	12.46	12.89	12.95	13.38	13.86	12.46	12.89	12.95	13.38	13.86
	6H	13.22	13.58	13.75	14.10	14.59	13.22	13.58	13.75	14.10	14.59
	8H	13.57	13.88	14.09	14.38	14.95	13.57	13.88	14.09	14.38	14.95