

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865971

Luminaire Tested: PRLX-2001-M-930-15L-L-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P865971
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-46)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-M-930-15L-L-U-S-X-X-WHHR-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH WHITE INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1470.2 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.31
Luminous Opening: Circular (Dia: 1.27' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P865971

CATALOG NUMBER: PRLX-2001-M-930-15L-L-U-S-X-X-WHHR-X

Luminous Intensity Polar Plot





TEST NUMBER: P865971

CATALOG NUMBER: PRLX-2001-M-930-15L-L-U-S-X-X-WHHR-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51
6	75	63	55	49	73	62	54	48	60	53	48	58	52	48	57	52	47	45
7	70	57	49	43	68	56	49	43	55	48	43	54	47	43	52	47	42	41
8	65	52	44	39	64	52	44	39	50	44	39	49	43	38	48	42	38	37
9	61	48	41	35	59	48	40	35	47	40	35	46	39	35	45	39	35	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	30

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	5793
5°	5767
10°	5704
15°	5615
20°	5516
25°	5409
30°	5297
35°	5179
40°	5047
45°	4883
50°	4646
55°	3518
60°	1889
65°	1217
70°	1228
75°	1295
80°	1344
85°	1363

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4883 cd/sqm

TEST NUMBER: P865971

CATALOG NUMBER: PRLX-2001-M-930-15L-L-U-S-X-X-WHHR-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.1	4.4
10°-20°	180.2	12.3
20°-30°	266.2	18.1
30°-40°	312.6	21.3
40°-50°	313.4	21.3
50°-60°	209.9	14.3
60°-70°	67.4	4.6
70°-80°	41.2	2.8
80°-90°	15.3	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	510.6	34.7
0°-40°	823.1	56.0
0°-60°	1346.4	91.6
0°-90°	1470.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1470.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	683	
5°	677	64
15°	639	180
25°	578	266
35°	500	313
45°	407	313
55°	238	210
65°	61	67
75°	40	41
85°	14	15
90°	0	

TEST NUMBER: P865971

CATALOG NUMBER: PRLX-2001-M-930-15L-L-U-S-X-X-WHHR-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	682.6
2.5°	681.4
5°	677.0
7.5°	670.6
10°	661.9
12.5°	651.9
15°	639.1
17.5°	626.0
20°	610.8
22.5°	595.2
25°	577.7
27.5°	560.1
30°	540.6
32.5°	520.6
35°	499.9
37.5°	478.3
40°	455.6
42.5°	432.5
45°	406.9
47.5°	381.0
50°	351.9
52.5°	307.2
55°	237.8
57.5°	168.8
60°	111.3
62.5°	78.6
65°	60.6
67.5°	53.5
70°	49.5
72.5°	44.7
75°	39.5
77.5°	33.5
80°	27.5
82.5°	21.1
85°	14.0
87.5°	7.2
90°	0.0



TEST NUMBER: P865971
 CATALOG NUMBER: PRLX-2001-M-930-15L-L-U-S-X-X-WHHR-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.38	15.86	14.75	16.17	16.49	14.38	15.86	14.75	16.17	16.49
	3H	14.87	16.18	15.24	16.50	16.87	14.87	16.18	15.24	16.50	16.87
	4H	15.19	16.41	15.59	16.76	17.14	15.19	16.41	15.59	16.76	17.14
	6H	15.51	16.64	15.93	17.01	17.40	15.51	16.64	15.93	17.01	17.40
	8H	15.65	16.72	16.08	17.11	17.51	15.65	16.72	16.08	17.11	17.51
	12H	15.76	16.78	16.19	17.16	17.59	15.76	16.78	16.19	17.16	17.59
4H	2H	14.42	15.64	14.82	15.99	16.37	14.42	15.64	14.82	15.99	16.37
	3H	15.13	16.13	15.54	16.53	16.93	15.13	16.13	15.54	16.53	16.93
	4H	15.60	16.50	16.04	16.92	17.36	15.60	16.50	16.04	16.92	17.36
	6H	16.10	16.88	16.56	17.32	17.78	16.10	16.88	16.56	17.32	17.78
	8H	16.31	17.04	16.77	17.48	17.95	16.31	17.04	16.77	17.48	17.95
	12H	16.48	17.13	16.96	17.61	18.08	16.48	17.13	16.96	17.61	18.08
8H	4H	15.77	16.49	16.23	16.94	17.41	15.77	16.49	16.23	16.94	17.41
	6H	16.40	17.00	16.89	17.49	17.97	16.40	17.00	16.89	17.49	17.97
	8H	16.69	17.24	17.21	17.75	18.24	16.69	17.24	17.21	17.75	18.24
	12H	16.96	17.45	17.47	17.94	18.51	16.96	17.45	17.47	17.94	18.51
12H	4H	15.78	16.43	16.26	16.91	17.38	15.78	16.43	16.26	16.91	17.38
	6H	16.44	16.99	16.96	17.50	17.99	16.44	16.99	16.96	17.50	17.99
	8H	16.80	17.29	17.31	17.78	18.35	16.80	17.29	17.31	17.78	18.35