

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P867404

Luminaire Tested: PRLX-2004-L-940-48L-L-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P867404
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-87)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-L-940-48L-L-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, LARGE LIGHT ENGINE, FLAT LENS,
BELL WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 3
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2251.6 lumens
Efficiency: N/A
Efficacy: 60.0 lumens/watt
Spacing Criteria (0/90/45): 1.05 / 1.05 / 0.98
Luminous Opening: Circular (Dia: 1.67' x H: 0')
CIE Type: Direct

Input Watts (W): 37.5
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P867404

CATALOG NUMBER: PRLX-2004-L-940-48L-L-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P867404

CATALOG NUMBER: PRLX-2004-L-940-48L-L-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	111	108	106	111	108	106	104	104	103	101		101	99	98		97	96	95	93
2	108	103	99	95	106	101	97	94	98	95	92		95	92	90		92	90	88	87
3	102	96	91	87	100	94	90	86	92	88	85		89	86	83		87	84	82	81
4	97	89	84	80	95	88	83	79	86	82	78		84	80	77		82	79	76	75
5	92	84	78	73	90	83	77	73	81	76	72		79	75	72		78	74	71	70
6	87	78	72	68	86	78	72	68	76	71	67		75	70	67		73	69	66	65
7	83	74	68	63	82	73	67	63	72	66	63		70	66	62		69	65	62	61
8	79	69	63	59	78	69	63	59	68	62	59		66	62	58		65	61	58	57
9	75	65	59	55	74	65	59	55	64	59	55		63	58	55		62	58	54	53
10	71	61	56	52	70	61	55	52	60	55	51		59	55	51		59	54	51	50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	11437
5°	11133
10°	10616
15°	10208
20°	9845
25°	9500
30°	9093
35°	6134
40°	1480
45°	378
50°	133
55°	126
60°	117
65°	106
70°	98
75°	95
80°	91
85°	79

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 378 cd/sqm

TEST NUMBER: P867404

CATALOG NUMBER: PRLX-2004-L-940-48L-L-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	210.4	9.3
10°-20°	562.9	25.0
20°-30°	802.5	35.6
30°-40°	587.3	26.1
40°-50°	59.4	2.6
50°-60°	13.1	0.6
60°-70°	9.1	0.4
70°-80°	5.3	0.2
80°-90°	1.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1575.8	70.0
0°-40°	2163.1	96.1
0°-60°	2235.6	99.3
0°-90°	2251.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2251.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2318	
5°	2248	210
15°	1998	563
25°	1745	803
35°	1018	587
45°	54	59
55°	15	13
65°	9	9
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P867404

CATALOG NUMBER: PRLX-2004-L-940-48L-L-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	2318.1
2.5°	2302.1
5°	2247.9
7.5°	2182.2
10°	2118.9
12.5°	2058.7
15°	1998.5
17.5°	1937.9
20°	1875.0
22.5°	1809.8
25°	1745.1
27.5°	1677.1
30°	1596.0
32.5°	1409.5
35°	1018.4
37.5°	517.9
40°	229.8
42.5°	121.7
45°	54.2
47.5°	19.1
50°	17.3
52.5°	16.0
55°	14.6
57.5°	13.2
60°	11.9
62.5°	10.5
65°	9.1
67.5°	7.7
70°	6.8
72.5°	5.9
75°	5.0
77.5°	4.1
80°	3.2
82.5°	2.3
85°	1.4
87.5°	0.9
90°	0.0



TEST NUMBER: P867404
 CATALOG NUMBER: PRLX-2004-L-940-48L-L-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
4H	2H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	3H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
8H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	12H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
12H	4H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	6H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00
	8H	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00	0.00