

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866429

Luminaire Tested: PRLX-2004-M-927-35L-G-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866429  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-43)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-M-927-35L-G-U-S-X-X-BRSS-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,  
BELL WITH BRASS INTERIOR SHADE.  
LIGHT LEVEL 4  
Light Source: 2700K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 662.1 lumens  
Efficiency: N/A  
Efficacy: 22.1 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.14  
Luminous Opening: Circular (Dia: 1.31' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 30  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866429

CATALOG NUMBER: PRLX-2004-M-927-35L-G-U-S-X-X-BRSS-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866429

CATALOG NUMBER: PRLX-2004-M-927-35L-G-U-S-X-X-BRSS-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90
2	105	99	94	89	102	97	92	88	93	90	86	90	87	84	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	75	81	77	74	72
4	91	82	75	70	89	81	74	70	79	73	69	76	72	68	74	70	67	65
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53
7	75	64	57	52	74	63	56	51	62	56	51	60	55	51	59	54	50	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	46	55	50	46	45
9	66	55	48	43	65	54	48	43	53	47	43	52	47	43	51	46	43	41
10	63	51	44	40	62	51	44	40	50	44	40	49	43	39	48	43	39	38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3299
5°	3297
10°	3286
15°	3262
20°	3203
25°	3126
30°	2977
35°	2614
40°	2139
45°	1589
50°	1022
55°	555
60°	411
65°	350
70°	309
75°	274
80°	243
85°	246

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1589 cd/sqm

TEST NUMBER: P866429

CATALOG NUMBER: PRLX-2004-M-927-35L-G-U-S-X-X-BRSS-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	39.2	5.9
10°-20°	111.5	16.8
20°-30°	163.4	24.7
30°-40°	166.8	25.2
40°-50°	109.0	16.5
50°-60°	40.6	6.1
60°-70°	18.9	2.8
70°-80°	9.7	1.5
80°-90°	3.1	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	314.0	47.4
0°-40°	480.9	72.6
0°-60°	630.4	95.2
0°-90°	662.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	662.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	415	
5°	413	39
15°	396	111
25°	356	163
35°	269	167
45°	141	109
55°	40	41
65°	19	19
75°	9	10
85°	3	3
90°	0	

TEST NUMBER: P866429

CATALOG NUMBER: PRLX-2004-M-927-35L-G-U-S-X-X-BRSS-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	414.7
2.5°	413.8
5°	412.9
7.5°	410.3
10°	406.7
12.5°	402.3
15°	396.1
17.5°	388.1
20°	378.3
22.5°	367.7
25°	356.1
27.5°	342.8
30°	324.1
32.5°	299.3
35°	269.1
37.5°	238.0
40°	206.0
42.5°	173.2
45°	141.2
47.5°	111.0
50°	82.6
52.5°	58.6
55°	40.0
57.5°	30.2
60°	25.8
62.5°	22.2
65°	18.6
67.5°	16.0
70°	13.3
72.5°	11.5
75°	8.9
77.5°	7.1
80°	5.3
82.5°	4.4
85°	2.7
87.5°	1.8
90°	0.0

TEST NUMBER: P866429  
 CATALOG NUMBER: PRLX-2004-M-927-35L-G-U-S-X-X-BRSS-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.35	6.61	5.72	6.92	7.24	5.35	6.61	5.72	6.92	7.24
	3H	6.55	7.66	6.93	7.99	8.35	6.55	7.66	6.93	7.99	8.35
	4H	6.98	8.02	7.39	8.37	8.75	6.98	8.02	7.39	8.37	8.75
	6H	7.29	8.24	7.71	8.61	9.00	7.29	8.24	7.71	8.61	9.00
	8H	7.42	8.31	7.85	8.70	9.11	7.42	8.31	7.85	8.70	9.11
	12H	7.51	8.36	7.94	8.74	9.18	7.51	8.36	7.94	8.74	9.18
4H	2H	5.72	6.75	6.12	7.10	7.49	5.72	6.75	6.12	7.10	7.49
	3H	7.13	7.97	7.55	8.38	8.78	7.13	7.97	7.55	8.38	8.78
	4H	7.68	8.43	8.11	8.85	9.29	7.68	8.43	8.11	8.85	9.29
	6H	8.10	8.74	8.56	9.19	9.66	8.10	8.74	8.56	9.19	9.66
	8H	8.27	8.88	8.74	9.32	9.80	8.27	8.88	8.74	9.32	9.80
	12H	8.41	8.94	8.89	9.42	9.90	8.41	8.94	8.89	9.42	9.90
8H	4H	7.84	8.44	8.31	8.89	9.36	7.84	8.44	8.31	8.89	9.36
	6H	8.37	8.86	8.87	9.36	9.84	8.37	8.86	8.87	9.36	9.84
	8H	8.63	9.07	9.15	9.59	10.08	8.63	9.07	9.15	9.59	10.08
	12H	8.85	9.24	9.37	9.74	10.31	8.85	9.24	9.37	9.74	10.31
12H	4H	7.83	8.37	8.32	8.85	9.33	7.83	8.37	8.32	8.85	9.33
	6H	8.39	8.84	8.92	9.35	9.85	8.39	8.84	8.92	9.35	9.85
	8H	8.71	9.10	9.23	9.60	10.17	8.71	9.10	9.23	9.60	10.17