

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866083

Luminaire Tested: PRLX-2001-M-935-75L-L-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866083  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-46)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-M-935-75L-L-U-S-X-X-WHHR-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,  
TAPERED DRUM WITH WHITE INTERIOR SHADE.  
LIGHT LEVEL 8  
Light Source: 3500K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7500.0 lumens  
Efficiency: N/A  
Efficacy: 107.6 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.31  
Luminous Opening: Circular (Dia: 1.27' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 69.7  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.333 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866083

CATALOG NUMBER: PRLX-2001-M-935-75L-L-U-S-X-X-WHHR-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866083

CATALOG NUMBER: PRLX-2001-M-935-75L-L-U-S-X-X-WHHR-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	104	101	98	100	98	95	96	94	92	93	91	90	88
2	102	95	89	84	100	93	88	83	90	85	82	87	83	80	84	81	78	76
3	94	85	78	72	92	84	77	72	81	75	71	78	73	69	76	72	68	66
4	87	77	69	63	85	75	68	62	73	67	62	71	65	61	69	64	60	58
5	81	69	61	55	79	68	60	55	66	59	54	64	58	54	62	57	53	51
6	75	63	55	49	73	62	54	48	60	53	48	58	52	48	57	52	47	45
7	70	57	49	43	68	56	49	43	55	48	43	54	47	43	52	47	42	41
8	65	52	44	39	64	52	44	39	50	44	39	49	43	38	48	42	38	37
9	61	48	41	35	59	48	40	35	47	40	35	46	39	35	45	39	35	33
10	57	45	37	32	56	44	37	32	43	37	32	42	36	32	41	36	32	30

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	29550
5°	29420
10°	29093
15°	28643
20°	28138
25°	27593
30°	27021
35°	26418
40°	25747
45°	24913
50°	23697
55°	17946
60°	9637
65°	6211
70°	6262
75°	6607
80°	6861
85°	6932

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 24913 cd/sqm

TEST NUMBER: P866083

CATALOG NUMBER: PRLX-2001-M-935-75L-L-U-S-X-X-WHHR-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	327.2	4.4
10°-20°	919.3	12.3
20°-30°	1358.0	18.1
30°-40°	1594.6	21.3
40°-50°	1598.5	21.3
50°-60°	1070.5	14.3
60°-70°	343.8	4.6
70°-80°	210.3	2.8
80°-90°	77.8	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2604.5	34.7
0°-40°	4199.1	56.0
0°-60°	6868.1	91.6
0°-90°	7500.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7500.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3482	
5°	3454	327
15°	3260	919
25°	2947	1358
35°	2550	1595
45°	2076	1599
55°	1213	1070
65°	309	344
75°	202	210
85°	71	78
90°	0	

TEST NUMBER: P866083

CATALOG NUMBER: PRLX-2001-M-935-75L-L-U-S-X-X-WHHR-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3482.2
2.5°	3476.1
5°	3453.7
7.5°	3421.1
10°	3376.3
12.5°	3325.5
15°	3260.3
17.5°	3193.2
20°	3115.8
22.5°	3036.5
25°	2946.9
27.5°	2857.4
30°	2757.6
32.5°	2655.9
35°	2550.1
37.5°	2440.2
40°	2324.2
42.5°	2206.1
45°	2075.9
47.5°	1943.6
50°	1795.0
52.5°	1567.1
55°	1213.0
57.5°	860.9
60°	567.8
62.5°	400.9
65°	309.3
67.5°	272.7
70°	252.4
72.5°	227.9
75°	201.5
77.5°	171.0
80°	140.4
82.5°	107.9
85°	71.2
87.5°	36.6
90°	0.0



TEST NUMBER: P866083

CATALOG NUMBER: PRLX-2001-M-935-75L-L-U-S-X-X-WHHR-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	20.04	21.52	20.41	21.83	22.15	20.04	21.52	20.41	21.83	22.15
	3H	20.52	21.84	20.90	22.16	22.53	20.52	21.84	20.90	22.16	22.53
	4H	20.85	22.07	21.25	22.42	22.80	20.85	22.07	21.25	22.42	22.80
	6H	21.17	22.30	21.59	22.67	23.06	21.17	22.30	21.59	22.67	23.06
	8H	21.31	22.38	21.74	22.77	23.18	21.31	22.38	21.74	22.77	23.18
	12H	21.42	22.44	21.85	22.83	23.25	21.42	22.44	21.85	22.83	23.25
4H	2H	20.08	21.30	20.48	21.65	22.03	20.08	21.30	20.48	21.65	22.03
	3H	20.79	21.79	21.20	22.19	22.59	20.79	21.79	21.20	22.19	22.59
	4H	21.26	22.16	21.70	22.58	23.02	21.26	22.16	21.70	22.58	23.02
	6H	21.76	22.54	22.22	22.98	23.45	21.76	22.54	22.22	22.98	23.45
	8H	21.97	22.70	22.44	23.14	23.61	21.97	22.70	22.44	23.14	23.61
	12H	22.14	22.79	22.63	23.27	23.75	22.14	22.79	22.63	23.27	23.75
8H	4H	21.43	22.15	21.89	22.60	23.07	21.43	22.15	21.89	22.60	23.07
	6H	22.06	22.66	22.56	23.16	23.63	22.06	22.66	22.56	23.16	23.63
	8H	22.35	22.90	22.87	23.41	23.90	22.35	22.90	22.87	23.41	23.90
	12H	22.62	23.11	23.13	23.60	24.17	22.62	23.11	23.13	23.60	24.17
12H	4H	21.44	22.09	21.92	22.57	23.04	21.44	22.09	21.92	22.57	23.04
	6H	22.10	22.65	22.62	23.16	23.65	22.10	22.65	22.62	23.16	23.65
	8H	22.46	22.95	22.97	23.44	24.01	22.46	22.95	22.97	23.44	24.01