

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866483

Luminaire Tested: PRLX-2004-M-930-15L-L-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866483  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-54)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-M-930-15L-L-U-S-X-X-WHHR-X  
Description: PRENATALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,  
BELL WITH WHITE INTERIOR SHADE.  
LIGHT LEVEL 2  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1418.4 lumens  
Efficiency: N/A  
Efficacy: 101.3 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05  
Luminous Opening: Circular (Dia: 1.31' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866483

CATALOG NUMBER: PRLX-2004-M-930-15L-L-U-S-X-X-WHHR-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866483

CATALOG NUMBER: PRLX-2004-M-930-15L-L-U-S-X-X-WHHR-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	103	100	108	105	101	98	100	98	95	97	94	92	93	91	90	88
2	103	96	90	85	100	94	89	84	91	86	83	87	84	81	85	82	79	77
3	95	87	80	74	93	85	79	74	82	77	72	80	75	71	77	73	70	68
4	89	79	71	66	87	77	71	65	75	69	64	73	68	64	71	66	63	61
5	83	72	64	59	81	71	64	58	69	63	58	67	62	57	65	61	57	55
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	61	55	51	50
7	73	61	53	48	71	60	53	48	59	52	48	57	52	47	56	51	47	45
8	68	57	49	44	67	56	49	44	55	48	44	54	48	43	52	47	43	42
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38
10	61	49	42	37	60	49	42	37	48	41	37	47	41	37	46	41	37	35

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	7287
5°	7080
10°	6846
15°	6677
20°	6543
25°	6391
30°	6208
35°	5161
40°	2905
45°	2186
50°	2099
55°	1986
60°	1873
65°	1781
70°	1717
75°	1669
80°	1626
85°	1607

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2186 cd/sqm

TEST NUMBER: P866483

CATALOG NUMBER: PRLX-2004-M-930-15L-L-U-S-X-X-WHHR-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.4	5.9
10°-20°	228.7	16.1
20°-30°	335.2	23.6
30°-40°	313.2	22.1
40°-50°	158.8	11.2
50°-60°	128.2	9.0
60°-70°	94.3	6.6
70°-80°	57.4	4.0
80°-90°	19.2	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	647.3	45.6
0°-40°	960.5	67.7
0°-60°	1247.6	88.0
0°-90°	1418.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1418.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	916	
5°	886	83
15°	811	229
25°	728	335
35°	531	313
45°	194	159
55°	143	128
65°	95	94
75°	54	57
85°	18	19
90°	0	

TEST NUMBER: P866483

CATALOG NUMBER: PRLX-2004-M-930-15L-L-U-S-X-X-WHHR-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	916.0
2.5°	908.4
5°	886.5
7.5°	866.5
10°	847.4
12.5°	829.0
15°	810.7
17.5°	792.3
20°	772.8
22.5°	751.6
25°	728.1
27.5°	704.1
30°	675.8
32.5°	631.1
35°	531.4
37.5°	387.4
40°	279.7
42.5°	225.4
45°	194.3
47.5°	181.5
50°	169.6
52.5°	156.4
55°	143.2
57.5°	130.5
60°	117.7
62.5°	106.5
65°	94.6
67.5°	84.2
70°	73.8
72.5°	63.8
75°	54.3
77.5°	44.7
80°	35.5
82.5°	26.3
85°	17.6
87.5°	8.8
90°	0.0



TEST NUMBER: P866483  
 CATALOG NUMBER: PRLX-2004-M-930-15L-L-U-S-X-X-WHHR-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.78	14.14	13.15	14.45	14.76	12.78	14.14	13.15	14.45	14.76
	3H	14.52	15.74	14.90	16.06	16.43	14.52	15.74	14.90	16.06	16.43
	4H	15.23	16.37	15.64	16.72	17.10	15.23	16.37	15.64	16.72	17.10
	6H	15.81	16.85	16.22	17.22	17.62	15.81	16.85	16.22	17.22	17.62
	8H	16.02	17.01	16.45	17.40	17.81	16.02	17.01	16.45	17.40	17.81
	12H	16.18	17.13	16.61	17.51	17.94	16.18	17.13	16.61	17.51	17.94
4H	2H	13.34	14.47	13.74	14.82	15.21	13.34	14.47	13.74	14.82	15.21
	3H	15.31	16.26	15.73	16.66	17.06	15.31	16.26	15.73	16.66	17.06
	4H	16.16	17.01	16.60	17.43	17.87	16.16	17.01	16.60	17.43	17.87
	6H	16.88	17.62	17.34	18.06	18.53	16.88	17.62	17.34	18.06	18.53
	8H	17.15	17.84	17.62	18.28	18.75	17.15	17.84	17.62	18.28	18.75
	12H	17.36	17.97	17.85	18.46	18.93	17.36	17.97	17.85	18.46	18.93
8H	4H	16.47	17.16	16.94	17.60	18.07	16.47	17.16	16.94	17.60	18.07
	6H	17.34	17.91	17.84	18.40	18.88	17.34	17.91	17.84	18.40	18.88
	8H	17.70	18.21	18.22	18.72	19.21	17.70	18.21	18.22	18.72	19.21
	12H	18.02	18.46	18.53	18.96	19.53	18.02	18.46	18.53	18.96	19.53
12H	4H	16.50	17.11	16.99	17.59	18.07	16.50	17.11	16.99	17.59	18.07
	6H	17.41	17.92	17.93	18.43	18.92	17.41	17.92	17.93	18.43	18.92
	8H	17.84	18.28	18.35	18.78	19.35	17.84	18.28	18.35	18.78	19.35