

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866104

Luminaire Tested: PRLX-2001-M-940-25L-L-U-S-X-X-BLAK-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866104
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-49)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-M-940-25L-L-U-S-X-X-BLAK-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH BLACK INTERIOR SHADE.
LIGHT LEVEL 3
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1983.2 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.27
Luminous Opening: Circular (Dia: 1.27' x H: 0')
CIE Type: Direct

Input Watts (W): 21.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.5 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866104

CATALOG NUMBER: PRLX-2001-M-940-25L-L-U-S-X-X-BLAK-X

Luminous Intensity Polar Plot





TEST NUMBER: P866104

CATALOG NUMBER: PRLX-2001-M-940-25L-L-U-S-X-X-BLAK-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	103	109	106	103	101	102	100	98	98	97	95	95	93	92	90
2	104	98	93	88	102	96	91	87	93	89	86	90	86	84	87	84	82	80
3	97	88	82	77	95	87	81	76	84	79	75	82	77	74	79	76	73	71
4	90	80	73	67	88	79	72	67	76	71	66	74	69	65	72	68	64	63
5	83	73	65	60	82	72	65	59	70	63	59	68	62	58	66	61	58	56
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	61	55	52	50
7	72	60	53	47	71	60	52	47	58	52	47	57	51	47	56	50	46	45
8	68	56	48	43	66	55	48	43	54	47	42	52	47	42	51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39	49	43	38	48	42	38	37
10	59	47	40	35	58	47	40	35	46	40	35	45	39	35	44	39	35	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	8847
5°	8813
10°	8699
15°	8541
20°	8352
25°	8148
30°	7922
35°	7661
40°	7373
45°	7048
50°	6626
55°	4674
60°	1475
65°	100
70°	72
75°	72
80°	68
85°	68

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7048 cd/sqm

TEST NUMBER: P866104

CATALOG NUMBER: PRLX-2001-M-940-25L-L-U-S-X-X-BLAK-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.0	4.9
10°-20°	273.9	13.8
20°-30°	400.6	20.2
30°-40°	462.3	23.3
40°-50°	452.4	22.8
50°-60°	271.4	13.7
60°-70°	21.2	1.1
70°-80°	2.5	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	772.4	38.9
0°-40°	1234.7	62.3
0°-60°	1958.6	98.8
0°-90°	1983.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1983.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1042	
5°	1035	98
15°	972	274
25°	870	401
35°	740	462
45°	587	452
55°	316	271
65°	5	21
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P866104

CATALOG NUMBER: PRLX-2001-M-940-25L-L-U-S-X-X-BLAK-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	1042.5
2.5°	1041.1
5°	1034.6
7.5°	1023.9
10°	1009.5
12.5°	993.0
15°	972.2
17.5°	949.9
20°	924.8
22.5°	898.2
25°	870.2
27.5°	840.1
30°	808.5
32.5°	774.7
35°	739.5
37.5°	703.6
40°	665.6
42.5°	629.0
45°	587.3
47.5°	545.7
50°	501.9
52.5°	430.8
55°	315.9
57.5°	186.0
60°	86.9
62.5°	34.5
65°	5.0
67.5°	2.9
70°	2.9
72.5°	2.9
75°	2.2
77.5°	2.2
80°	1.4
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0



TEST NUMBER: P866104
 CATALOG NUMBER: PRLX-2001-M-940-25L-L-U-S-X-X-BLAK-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.04	15.42	14.41	15.73	16.04	14.04	15.42	14.41	15.73	16.04
	3H	13.92	15.12	14.30	15.45	15.82	13.92	15.12	14.30	15.45	15.82
	4H	13.85	14.97	14.25	15.32	15.70	13.85	14.97	14.25	15.32	15.70
	6H	13.78	14.80	14.19	15.17	15.56	13.78	14.80	14.19	15.17	15.56
	8H	13.74	14.71	14.17	15.10	15.50	13.74	14.71	14.17	15.10	15.50
	12H	13.70	14.62	14.13	15.00	15.43	13.70	14.62	14.13	15.00	15.43
4H	2H	13.85	14.97	14.25	15.32	15.70	13.85	14.97	14.25	15.32	15.70
	3H	13.73	14.63	14.15	15.03	15.43	13.73	14.63	14.15	15.03	15.43
	4H	13.65	14.44	14.08	14.86	15.31	13.65	14.44	14.08	14.86	15.31
	6H	13.57	14.25	14.03	14.70	15.17	13.57	14.25	14.03	14.70	15.17
	8H	13.51	14.15	13.98	14.60	15.07	13.51	14.15	13.98	14.60	15.07
	12H	13.47	14.03	13.95	14.52	14.99	13.47	14.03	13.95	14.52	14.99
8H	4H	13.51	14.15	13.98	14.60	15.07	13.51	14.15	13.98	14.60	15.07
	6H	13.41	13.93	13.91	14.43	14.91	13.41	13.93	13.91	14.43	14.91
	8H	13.34	13.82	13.86	14.33	14.83	13.34	13.82	13.86	14.33	14.83
	12H	13.29	13.72	13.80	14.21	14.78	13.29	13.72	13.80	14.21	14.78
12H	4H	13.46	14.03	13.95	14.51	14.99	13.46	14.03	13.95	14.51	14.99
	6H	13.34	13.82	13.86	14.33	14.82	13.34	13.82	13.86	14.33	14.82
	8H	13.29	13.72	13.80	14.21	14.78	13.29	13.72	13.80	14.21	14.78