

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866145

Luminaire Tested: PRLX-2001-M-940-75L-L-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866145
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-47)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2001-M-940-75L-L-U-S-X-X-BRSS-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, FLAT LENS,
TAPERED DRUM WITH BRASS INTERIOR SHADE.
LIGHT LEVEL 8
Light Source: 4000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6377.9 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.27
Luminous Opening: Circular (Dia: 1.27' x H: 0')
CIE Type: Direct

Input Watts (W): 69.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866145

CATALOG NUMBER: PRLX-2001-M-940-75L-L-U-S-X-X-BRSS-X

Luminous Intensity Polar Plot





TEST NUMBER: P866145

CATALOG NUMBER: PRLX-2001-M-940-75L-L-U-S-X-X-BRSS-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	92	90
2	104	97	92	88	101	96	91	87	92	88	85	89	86	83	86	83	81	79
3	96	88	81	76	94	86	80	75	83	78	74	81	76	73	78	75	72	70
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62
5	83	72	64	59	81	71	64	58	69	63	58	67	61	57	65	60	57	55
6	77	65	58	52	75	65	57	52	63	56	51	61	56	51	60	55	51	49
7	72	60	52	47	70	59	52	47	58	51	46	56	50	46	55	50	46	44
8	67	55	47	42	66	54	47	42	53	46	42	52	46	42	51	45	41	40
9	63	51	43	38	62	50	43	38	49	42	38	48	42	38	47	42	38	36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	35	44	38	34	33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	28223
5°	28055
10°	27619
15°	27023
20°	26338
25°	25675
30°	24906
35°	24078
40°	23218
45°	22180
50°	20873
55°	14915
60°	5557
65°	1470
70°	1444
75°	1554
80°	1686
85°	1675

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22180 cd/sqm

TEST NUMBER: P866145

CATALOG NUMBER: PRLX-2001-M-940-75L-L-U-S-X-X-BRSS-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	311.6	4.9
10°-20°	866.5	13.6
20°-30°	1261.6	19.8
30°-40°	1453.1	22.8
40°-50°	1423.6	22.3
50°-60°	874.1	13.7
60°-70°	119.0	1.9
70°-80°	49.8	0.8
80°-90°	18.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2439.7	38.3
0°-40°	3892.8	61.0
0°-60°	6190.5	97.1
0°-90°	6377.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6377.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3326	
5°	3294	312
15°	3076	867
25°	2742	1262
35°	2324	1453
45°	1848	1424
55°	1008	874
65°	73	119
75°	47	50
85°	17	19
90°	0	

TEST NUMBER: P866145

CATALOG NUMBER: PRLX-2001-M-940-75L-L-U-S-X-X-BRSS-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	3325.8
2.5°	3319.3
5°	3293.5
7.5°	3254.7
10°	3205.2
12.5°	3147.0
15°	3075.9
17.5°	3002.7
20°	2916.5
22.5°	2832.5
25°	2742.1
27.5°	2643.0
30°	2541.7
32.5°	2434.0
35°	2324.2
37.5°	2210.0
40°	2095.9
42.5°	1975.2
45°	1848.2
47.5°	1718.9
50°	1581.1
52.5°	1359.2
55°	1008.1
57.5°	626.8
60°	327.4
62.5°	159.4
65°	73.2
67.5°	60.3
70°	58.2
72.5°	53.9
75°	47.4
77.5°	40.9
80°	34.5
82.5°	25.8
85°	17.2
87.5°	8.6
90°	0.0



TEST NUMBER: P866145
 CATALOG NUMBER: PRLX-2001-M-940-75L-L-U-S-X-X-BRSS-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	18.43	19.82	18.79	20.14	20.45	18.43	19.82	18.79	20.14	20.45
	3H	18.37	19.60	18.75	19.92	20.29	18.37	19.60	18.75	19.92	20.29
	4H	18.35	19.49	18.75	19.84	20.22	18.35	19.49	18.75	19.84	20.22
	6H	18.34	19.38	18.75	19.75	20.14	18.34	19.38	18.75	19.75	20.14
	8H	18.32	19.31	18.75	19.70	20.11	18.32	19.31	18.75	19.70	20.11
	12H	18.31	19.25	18.74	19.64	20.07	18.31	19.25	18.74	19.64	20.07
4H	2H	18.26	19.40	18.67	19.76	20.14	18.26	19.40	18.67	19.76	20.14
	3H	18.24	19.16	18.65	19.56	19.96	18.24	19.16	18.65	19.56	19.96
	4H	18.24	19.05	18.67	19.47	19.92	18.24	19.05	18.67	19.47	19.92
	6H	18.26	18.97	18.72	19.41	19.88	18.26	18.97	18.72	19.41	19.88
	8H	18.26	18.92	18.72	19.36	19.83	18.26	18.92	18.72	19.36	19.83
	12H	18.25	18.84	18.74	19.32	19.80	18.25	18.84	18.74	19.32	19.80
8H	4H	18.15	18.81	18.62	19.26	19.73	18.15	18.81	18.62	19.26	19.73
	6H	18.19	18.73	18.69	19.23	19.71	18.19	18.73	18.69	19.23	19.71
	8H	18.20	18.70	18.72	19.21	19.70	18.20	18.70	18.72	19.21	19.70
	12H	18.22	18.67	18.73	19.16	19.73	18.22	18.67	18.73	19.16	19.73
12H	4H	18.11	18.70	18.60	19.18	19.65	18.11	18.70	18.60	19.18	19.65
	6H	18.14	18.64	18.66	19.15	19.64	18.14	18.64	18.66	19.15	19.64
	8H	18.18	18.63	18.70	19.12	19.69	18.18	18.63	18.70	19.12	19.69