

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866502

Luminaire Tested: PRLX-2004-M-930-45L-G-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866502
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-M-930-45L-G-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,
BELL WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 5
Light Source: 3000K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 880.4 lumens
Efficiency: N/A
Efficacy: 22.7 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.14
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 38.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866502

CATALOG NUMBER: PRLX-2004-M-930-45L-G-U-S-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P866502

CATALOG NUMBER: PRLX-2004-M-930-45L-G-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	105	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	91	82	75	70	89	81	75	70	79	73	69	77	72	68	75	71	67	65
5	86	75	68	63	84	74	68	63	72	67	62	71	65	61	69	64	61	59
6	80	69	62	57	78	68	62	57	67	61	56	65	60	56	64	59	55	54
7	75	64	57	52	74	63	56	52	62	56	51	61	55	51	59	54	51	49
8	71	59	52	47	69	59	52	47	57	51	47	56	51	47	55	50	46	45
9	67	55	48	43	65	55	48	43	54	47	43	53	47	43	52	46	43	41
10	63	51	45	40	62	51	44	40	50	44	40	49	44	40	48	43	40	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4408
5°	4416
10°	4400
15°	4357
20°	4276
25°	4181
30°	3992
35°	3488
40°	2834
45°	2114
50°	1363
55°	698
60°	533
65°	450
70°	419
75°	369
80°	330
85°	329

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2114 cd/sqm

TEST NUMBER: P866502

CATALOG NUMBER: PRLX-2004-M-930-45L-G-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.5	6.0
10°-20°	149.0	16.9
20°-30°	218.5	24.8
30°-40°	222.4	25.3
40°-50°	144.5	16.4
50°-60°	52.8	6.0
60°-70°	24.4	2.8
70°-80°	12.8	1.5
80°-90°	3.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	420.0	47.7
0°-40°	642.4	73.0
0°-60°	839.6	95.4
0°-90°	880.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	880.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	554	
5°	553	52
15°	529	149
25°	476	219
35°	359	222
45°	188	144
55°	50	53
65°	24	24
75°	12	13
85°	4	4
90°	0	

TEST NUMBER: P866502

CATALOG NUMBER: PRLX-2004-M-930-45L-G-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	554.1
2.5°	554.1
5°	552.9
7.5°	549.4
10°	544.6
12.5°	538.6
15°	529.0
17.5°	518.2
20°	505.1
22.5°	491.9
25°	476.3
27.5°	458.4
30°	434.5
32.5°	398.6
35°	359.1
37.5°	317.2
40°	272.9
42.5°	229.8
45°	187.9
47.5°	146.0
50°	110.1
52.5°	76.6
55°	50.3
57.5°	39.5
60°	33.5
62.5°	28.7
65°	23.9
67.5°	20.3
70°	18.0
72.5°	14.4
75°	12.0
77.5°	9.6
80°	7.2
82.5°	4.8
85°	3.6
87.5°	1.2
90°	0.0



TEST NUMBER: P866502
 CATALOG NUMBER: PRLX-2004-M-930-45L-G-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.23	7.49	6.60	7.80	8.11	6.23	7.49	6.60	7.80	8.11
	3H	7.41	8.52	7.79	8.85	9.22	7.41	8.52	7.79	8.85	9.22
	4H	7.86	8.89	8.26	9.24	9.62	7.86	8.89	8.26	9.24	9.62
	6H	8.19	9.13	8.61	9.51	9.90	8.19	9.13	8.61	9.51	9.90
	8H	8.28	9.18	8.71	9.57	9.97	8.28	9.18	8.71	9.57	9.97
	12H	8.35	9.21	8.79	9.59	10.02	8.35	9.21	8.79	9.59	10.02
4H	2H	6.58	7.61	6.98	7.96	8.34	6.58	7.61	6.98	7.96	8.34
	3H	7.99	8.83	8.41	9.24	9.64	7.99	8.83	8.41	9.24	9.64
	4H	8.56	9.30	8.99	9.72	10.17	8.56	9.30	8.99	9.72	10.17
	6H	9.01	9.65	9.48	10.10	10.57	9.01	9.65	9.48	10.10	10.57
	8H	9.14	9.74	9.61	10.19	10.66	9.14	9.74	9.61	10.19	10.66
	12H	9.25	9.78	9.74	10.26	10.74	9.25	9.78	9.74	10.26	10.74
8H	4H	8.73	9.33	9.20	9.78	10.25	8.73	9.33	9.20	9.78	10.25
	6H	9.29	9.78	9.80	10.28	10.76	9.29	9.78	9.80	10.28	10.76
	8H	9.48	9.92	10.00	10.44	10.93	9.48	9.92	10.00	10.44	10.93
	12H	9.67	10.06	10.19	10.56	11.13	9.67	10.06	10.19	10.56	11.13
12H	4H	8.73	9.26	9.22	9.74	10.22	8.73	9.26	9.22	9.74	10.22
	6H	9.31	9.75	9.83	10.26	10.76	9.31	9.75	9.83	10.26	10.76
	8H	9.54	9.93	10.06	10.43	11.00	9.54	9.93	10.06	10.43	11.00