

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866503

Luminaire Tested: PRLX-2004-M-930-45L-G-U-S-X-X-WHHR-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P866503  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-42)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2004-M-930-45L-G-U-S-X-X-WHHR-X  
Description: PRENATALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,  
BELL WITH WHITE INTERIOR SHADE.  
LIGHT LEVEL 5  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2699.6 lumens  
Efficiency: N/A  
Efficacy: 69.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.2  
Luminous Opening: Circular (Dia: 1.31' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 38.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P866503

CATALOG NUMBER: PRLX-2004-M-930-45L-G-U-S-X-X-WHHR-X

### Luminous Intensity Polar Plot





TEST NUMBER: P866503

CATALOG NUMBER: PRLX-2004-M-930-45L-G-U-S-X-X-WHHR-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	102	99	107	104	100	97	99	97	94	96	93	91	92	90	89	87
2	101	94	88	83	99	92	87	82	89	84	80	86	82	78	83	79	77	75
3	94	84	77	71	91	83	76	70	80	74	69	77	72	68	75	70	67	65
4	87	76	68	62	84	74	67	61	72	66	60	70	64	60	68	63	59	57
5	80	69	60	54	78	67	60	54	65	59	53	64	58	53	62	57	52	50
6	75	62	54	48	73	61	54	48	60	53	48	58	52	47	57	51	47	45
7	70	57	49	43	68	56	49	43	55	48	43	53	47	43	52	47	42	40
8	65	53	45	39	64	52	44	39	51	44	39	49	43	39	48	43	38	37
9	61	49	41	36	60	48	41	36	47	40	35	46	40	35	45	39	35	33
10	57	45	38	33	56	45	37	33	44	37	32	43	37	32	42	36	32	31

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	10226
5°	10256
10°	10278
15°	10262
20°	10224
25°	10107
30°	9577
35°	8683
40°	7682
45°	6665
50°	5674
55°	4764
60°	4247
65°	3942
70°	3703
75°	3532
80°	3400
85°	3277

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 6665 cd/sqm



TEST NUMBER: P866503

CATALOG NUMBER: PRLX-2004-M-930-45L-G-U-S-X-X-WHHR-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.2	4.5
10°-20°	351.7	13.0
20°-30°	525.7	19.5
30°-40°	558.0	20.7
40°-50°	458.3	17.0
50°-60°	313.5	11.6
60°-70°	208.4	7.7
70°-80°	122.0	4.5
80°-90°	39.8	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	999.7	37.0
0°-40°	1557.6	57.7
0°-60°	2329.4	86.3
0°-90°	2699.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2699.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1285	
5°	1284	122
15°	1246	352
25°	1151	526
35°	894	558
45°	592	458
55°	344	314
65°	209	208
75°	115	122
85°	36	40
90°	0	

TEST NUMBER: P866503

CATALOG NUMBER: PRLX-2004-M-930-45L-G-U-S-X-X-WHHR-X

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1285.4
2.5°	1285.4
5°	1284.2
7.5°	1279.4
10°	1272.3
12.5°	1261.5
15°	1245.9
17.5°	1229.2
20°	1207.6
22.5°	1183.7
25°	1151.4
27.5°	1102.3
30°	1042.5
32.5°	974.2
35°	894.0
37.5°	817.4
40°	739.7
42.5°	664.3
45°	592.4
47.5°	526.6
50°	458.4
52.5°	397.4
55°	343.5
57.5°	301.6
60°	266.9
62.5°	237.0
65°	209.4
67.5°	183.1
70°	159.2
72.5°	136.4
75°	114.9
77.5°	94.6
80°	74.2
82.5°	55.1
85°	35.9
87.5°	18.0
90°	0.0



TEST NUMBER: P866503  
 CATALOG NUMBER: PRLX-2004-M-930-45L-G-U-S-X-X-WHHR-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	16.21	17.68	16.57	17.99	18.31	16.21	17.68	16.57	17.99	18.31
	3H	17.79	19.11	18.17	19.44	19.80	17.79	19.11	18.17	19.44	19.80
	4H	18.43	19.67	18.83	20.01	20.39	18.43	19.67	18.83	20.01	20.39
	6H	18.95	20.09	19.36	20.46	20.85	18.95	20.09	19.36	20.46	20.85
	8H	19.14	20.23	19.57	20.62	21.02	19.14	20.23	19.57	20.62	21.02
	12H	19.28	20.32	19.71	20.71	21.14	19.28	20.32	19.71	20.71	21.14
4H	2H	16.73	17.97	17.13	18.32	18.70	16.73	17.97	17.13	18.32	18.70
	3H	18.55	19.58	18.96	19.98	20.38	18.55	19.58	18.96	19.98	20.38
	4H	19.33	20.26	19.76	20.67	21.11	19.33	20.26	19.76	20.67	21.11
	6H	20.00	20.80	20.46	21.25	21.71	20.00	20.80	20.46	21.25	21.71
	8H	20.25	21.00	20.71	21.44	21.91	20.25	21.00	20.71	21.44	21.91
	12H	20.44	21.11	20.92	21.59	22.06	20.44	21.11	20.92	21.59	22.06
8H	4H	19.62	20.38	20.09	20.82	21.29	19.62	20.38	20.09	20.82	21.29
	6H	20.43	21.05	20.93	21.55	22.02	20.43	21.05	20.93	21.55	22.02
	8H	20.77	21.33	21.28	21.84	22.33	20.77	21.33	21.28	21.84	22.33
	12H	21.06	21.55	21.57	22.05	22.61	21.06	21.55	21.57	22.05	22.61
12H	4H	19.66	20.33	20.14	20.81	21.28	19.66	20.33	20.14	20.81	21.28
	6H	20.49	21.05	21.01	21.57	22.05	20.49	21.05	21.01	21.57	22.05
	8H	20.90	21.39	21.41	21.88	22.45	20.90	21.39	21.41	21.88	22.45