

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P865457

Luminaire Tested: PRLX-2001-S-930-05L-L-U-S-X-X-BRSS-X

Issue Date: 8/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P865457  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-16)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 8/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: Prenalux  
Catalog Number: PRLX-2001-S-930-05L-L-U-S-X-X-BRSS-X  
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, SMALL LIGHT ENGINE, FLAT LENS, TAPERED DRUM WITH BRASS INTERIOR SHADE.  
LIGHT LEVEL 1  
Light Source: 3000K CCT, 90 CRI LEDS  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 404.6 lumens  
Efficiency: N/A  
Efficacy: 65.3 lumens/watt  
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.28  
Luminous Opening: Circular (Dia: 0.92' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 6.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: 0.5 HR  
Operation Time: 3 HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P865457

CATALOG NUMBER: PRLX-2001-S-930-05L-L-U-S-X-X-BRSS-X

### Luminous Intensity Polar Plot





TEST NUMBER: P865457

CATALOG NUMBER: PRLX-2001-S-930-05L-L-U-S-X-X-BRSS-X

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89
2	103	96	91	86	101	94	89	85	91	87	83	88	84	81	85	82	80	78
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68
4	88	77	70	64	86	76	69	64	74	68	63	72	66	62	70	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52
6	75	63	55	50	74	62	55	49	61	54	49	59	53	49	58	52	48	46
7	70	58	50	44	68	57	49	44	56	49	44	54	48	43	53	47	43	41
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	35	45	39	35	34
10	57	45	38	33	56	45	37	33	44	37	32	43	37	32	42	36	32	31

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	3149
5°	3140
10°	3105
15°	3043
20°	2985
25°	2908
30°	2833
35°	2736
40°	2640
45°	2542
50°	2433
55°	2224
60°	1579
65°	602
70°	143
75°	139
80°	160
85°	243

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2542 cd/sqm

TEST NUMBER: P865457

CATALOG NUMBER: PRLX-2001-S-930-05L-L-U-S-X-X-BRSS-X

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	18.2	4.5
10°-20°	50.8	12.6
20°-30°	74.5	18.4
30°-40°	86.0	21.2
40°-50°	84.9	21.0
50°-60°	67.8	16.8
60°-70°	19.2	4.7
70°-80°	2.2	0.6
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	143.5	35.5
0°-40°	229.5	56.7
0°-60°	382.2	94.5
0°-90°	404.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	404.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	193	
5°	192	18
15°	180	51
25°	162	75
35°	137	86
45°	110	85
55°	78	68
65°	16	19
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P865457

CATALOG NUMBER: PRLX-2001-S-930-05L-L-U-S-X-X-BRSS-X

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	193.1
2.5°	193.1
5°	191.8
7.5°	189.7
10°	187.5
12.5°	184.1
15°	180.2
17.5°	176.3
20°	172.0
22.5°	167.2
25°	161.6
27.5°	156.4
30°	150.4
32.5°	143.9
35°	137.4
37.5°	130.9
40°	124.0
42.5°	117.1
45°	110.2
47.5°	102.8
50°	95.9
52.5°	88.1
55°	78.2
57.5°	65.7
60°	48.4
62.5°	30.2
65°	15.6
67.5°	6.9
70°	3.0
72.5°	2.2
75°	2.2
77.5°	1.7
80°	1.7
82.5°	1.3
85°	1.3
87.5°	0.4
90°	0.0



TEST NUMBER: P865457

CATALOG NUMBER: PRLX-2001-S-930-05L-L-U-S-X-X-BRSS-X

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.64	16.10	15.01	16.42	16.73	14.64	16.10	15.01	16.42	16.73
	3H	14.57	15.86	14.95	16.18	16.55	14.57	15.86	14.95	16.18	16.55
	4H	14.51	15.71	14.91	16.06	16.44	14.51	15.71	14.91	16.06	16.44
	6H	14.45	15.55	14.87	15.92	16.31	14.45	15.55	14.87	15.92	16.31
	8H	14.42	15.47	14.85	15.86	16.26	14.42	15.47	14.85	15.86	16.26
	12H	14.39	15.39	14.83	15.77	16.20	14.39	15.39	14.83	15.77	16.20
4H	2H	14.57	15.77	14.97	16.12	16.50	14.57	15.77	14.97	16.12	16.50
	3H	14.51	15.48	14.92	15.88	16.28	14.51	15.48	14.92	15.88	16.28
	4H	14.44	15.31	14.88	15.72	16.16	14.44	15.31	14.88	15.72	16.16
	6H	14.39	15.14	14.85	15.58	16.04	14.39	15.14	14.85	15.58	16.04
	8H	14.35	15.05	14.82	15.49	15.96	14.35	15.05	14.82	15.49	15.96
	12H	14.33	14.94	14.81	15.43	15.90	14.33	14.94	14.81	15.43	15.90
8H	4H	14.33	15.02	14.80	15.47	15.94	14.33	15.02	14.80	15.47	15.94
	6H	14.26	14.83	14.76	15.33	15.81	14.26	14.83	14.76	15.33	15.81
	8H	14.22	14.74	14.74	15.25	15.74	14.22	14.74	14.74	15.25	15.74
	12H	14.20	14.67	14.72	15.16	15.73	14.20	14.67	14.72	15.16	15.73
12H	4H	14.29	14.91	14.77	15.39	15.86	14.29	14.91	14.77	15.39	15.86
	6H	14.20	14.72	14.72	15.23	15.72	14.20	14.72	14.72	15.23	15.72
	8H	14.18	14.64	14.69	15.14	15.71	14.18	14.64	14.69	15.14	15.71