

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: PrentaLux

Report Number: P866542

Luminaire Tested: PRLX-2004-M-935-15L-G-U-S-X-X-GREY-X

Issue Date: 8/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P866542
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2304-993-44)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 8/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: Prenalux
Catalog Number: PRLX-2004-M-935-15L-G-U-S-X-X-GREY-X
Description: PRENTALUX 3D PRINTED PENDANT LED LUMINAIRE, MEDIUM LIGHT ENGINE, GLOBE LENS,
BELL WITH GRAY INTERIOR SHADE.
LIGHT LEVEL 2
Light Source: 3500K CCT, 90 CRI LEDS
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 299.4 lumens
Efficiency: N/A
Efficacy: 21.4 lumens/watt
Spacing Criteria (0/90/45): 1.17 / 1.17 / 1.14
Luminous Opening: Circular (Dia: 1.31' x H: 0')
CIE Type: Direct

Input Watts (W): 14
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: 0.333 HR
Operation Time: 3 HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P866542

CATALOG NUMBER: PRLX-2004-M-935-15L-G-U-S-X-X-GREY-X

Luminous Intensity Polar Plot





TEST NUMBER: P866542

CATALOG NUMBER: PRLX-2004-M-935-15L-G-U-S-X-X-GREY-X

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	105	103	109	106	104	101	102	100	98		98	97	95		95	94	92	90
2	105	99	94	89	102	97	92	88	94	90	86		90	87	85		88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81	77	74	73
4	91	82	75	70	89	81	75	70	79	73	69		77	72	68		75	71	67	65
5	86	75	68	63	84	74	68	63	72	67	62		71	65	61		69	64	61	59
6	80	69	62	57	78	68	62	57	67	61	56		65	60	56		64	59	55	54
7	75	64	57	52	74	63	56	52	62	56	51		61	55	51		59	54	51	49
8	71	59	52	47	69	59	52	47	57	51	47		56	51	47		55	50	46	45
9	67	55	48	43	65	55	48	43	54	47	43		53	47	43		52	46	43	41
10	63	51	45	40	62	51	44	40	50	44	40		49	44	40		48	43	40	38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1500
5°	1502
10°	1496
15°	1482
20°	1455
25°	1422
30°	1358
35°	1186
40°	964
45°	719
50°	463
55°	237
60°	181
65°	152
70°	142
75°	126
80°	110
85°	110

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 719 cd/sqm

TEST NUMBER: P866542

CATALOG NUMBER: PRLX-2004-M-935-15L-G-U-S-X-X-GREY-X

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.9	6.0
10°-20°	50.7	16.9
20°-30°	74.3	24.8
30°-40°	75.6	25.3
40°-50°	49.1	16.4
50°-60°	17.9	6.0
60°-70°	8.3	2.8
70°-80°	4.4	1.5
80°-90°	1.2	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	142.8	47.7
0°-40°	218.5	73.0
0°-60°	285.6	95.4
0°-90°	299.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	299.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	188	
5°	188	18
15°	180	51
25°	162	74
35°	122	76
45°	64	49
55°	17	18
65°	8	8
75°	4	4
85°	1	1
90°	0	

TEST NUMBER: P866542

CATALOG NUMBER: PRLX-2004-M-935-15L-G-U-S-X-X-GREY-X

CANDELA DISTRIBUTION (FULL):

	0°
0°	188.5
2.5°	188.5
5°	188.1
7.5°	186.8
10°	185.2
12.5°	183.2
15°	179.9
17.5°	176.2
20°	171.8
22.5°	167.3
25°	162.0
27.5°	155.9
30°	147.8
32.5°	135.5
35°	122.1
37.5°	107.9
40°	92.8
42.5°	78.2
45°	63.9
47.5°	49.7
50°	37.4
52.5°	26.1
55°	17.1
57.5°	13.4
60°	11.4
62.5°	9.8
65°	8.1
67.5°	6.9
70°	6.1
72.5°	4.9
75°	4.1
77.5°	3.3
80°	2.4
82.5°	1.6
85°	1.2
87.5°	0.4
90°	0.0

TEST NUMBER: P866542
 CATALOG NUMBER: PRLX-2004-M-935-15L-G-U-S-X-X-GREY-X

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	2.47	3.72	2.83	4.04	4.35	2.47	3.72	2.83	4.04	4.35
	3H	3.65	4.76	4.03	5.09	5.46	3.65	4.76	4.03	5.09	5.46
	4H	4.10	5.13	4.50	5.48	5.87	4.10	5.13	4.50	5.48	5.87
	6H	4.44	5.38	4.85	5.75	6.15	4.44	5.38	4.85	5.75	6.15
	8H	4.52	5.42	4.96	5.81	6.21	4.52	5.42	4.96	5.81	6.21
	12H	4.59	5.44	5.02	5.83	6.26	4.59	5.44	5.02	5.83	6.26
4H	2H	2.81	3.84	3.22	4.19	4.58	2.81	3.84	3.22	4.19	4.58
	3H	4.23	5.07	4.64	5.47	5.88	4.23	5.07	4.64	5.47	5.88
	4H	4.80	5.55	5.24	5.97	6.41	4.80	5.55	5.24	5.97	6.41
	6H	5.26	5.90	5.72	6.35	6.82	5.26	5.90	5.72	6.35	6.82
	8H	5.38	5.98	5.85	6.42	6.90	5.38	5.98	5.85	6.42	6.90
	12H	5.48	6.01	5.97	6.50	6.97	5.48	6.01	5.97	6.50	6.97
8H	4H	4.98	5.58	5.45	6.03	6.50	4.98	5.58	5.45	6.03	6.50
	6H	5.54	6.02	6.04	6.52	7.00	5.54	6.02	6.04	6.52	7.00
	8H	5.71	6.15	6.24	6.67	7.16	5.71	6.15	6.24	6.67	7.16
	12H	5.90	6.29	6.42	6.78	7.36	5.90	6.29	6.42	6.78	7.36
12H	4H	4.98	5.50	5.46	5.99	6.46	4.98	5.50	5.46	5.99	6.46
	6H	5.55	5.99	6.07	6.50	7.00	5.55	5.99	6.07	6.50	7.00
	8H	5.78	6.16	6.29	6.66	7.23	5.78	6.16	6.29	6.66	7.23